



Smart Halogen Downlight – a reliable way to make your merchandise stand out

Smart Halogen Downlight QBS020

Shop owners opening a new outlet or refurbishing their current installation and contractors looking for attractive propositions for their customers (small/non-chain retailers) now have the ideal solution for impactful, yet affordable accent lighting. Our Smart Halogen Downlight offers customers a choice of different shapes to suit different functions, and the professional finish lends the luminaire an air of contemporary sophistication. Thanks to its robust housing, the Smart Halogen Downlight is a long-lasting solution. Quality clips ensure ease of installation.

优点

- Affordable yet highly effective accent-lighting solution
- Safe and durable
- Wide choice for customers; contemporary sophistication

特点

- Robust housing
- Different shapes to suit different functions
- Professional finish
- Good-quality clips for easy installation

Smart Halogen Downlight QBS020

应用

- Retail – sales areas, shop windows
- Offices – exhibition and highlight areas
- Hospitality and cruise ships – corridors, service areas, reception areas, lobbies, lounges, restaurants, cabins
- Healthcare – corridors, reception areas, waiting areas
- Airports – arrival/departure halls, corridors, waiting areas, service desks, shops

规格

類型	壓鑄鋁版本，適用 MR11 燈具類型： - QBS020、022：固定式 - QBS021：可調整 壓鑄鋁版本，適用 MR16 燈具類型： - QBS023、026、QBS040~046：固定式 - QBS024、025、027~029、QBS047：可調整 鑄造鋁版本，適用 MR16 燈具類型： - QBS030、032：固定式 - QBS031：可旋轉	燈具位置	垂直
光源	鹵素： - 1 個 ESSENTIAL 1CT / GU4 / 20、35 W - 1 個 ESSENTIAL 封閉式 1CT / GU5.3 / 20、50 W	光分佈	直射 (D)
燈具光束角	30°、36°	變壓器	12 V (未隨附)
內附燈具	否	材質	QBS020~029、QBS040~047 版本： - 壓鑄鋁 QBS030~032 版本： - 鑄造鋁
		色彩	QBS020~029、QBS040~047 版本： - 白色與灰色 QBS030~032 版本： - 銀
		安裝	以彈簧扣件的方式固定
		保養	可直接取出燈具
		主要應用	零售業、時尚業、旅館服務業

