



智能卤素射灯 —— 一种 使您的商品脱颖而出的可 靠方法

智能卤素射灯 QBS020

商店业主或许想开设一家新的店面，或者想重新整修现有的设施；承包商或许在千方百计地为其客户（小型/非连锁零售商）提出富有吸引力的建议。如今，他们终于有了理想的解决方案，一种可带来绝佳效果、又价格合理的重要照明。我们推出的“智能卤素射灯”可为客户提供各种不同的外形选择，满足客户形形色色的功能要求，此外，经专业处理的饰面为灯具增添了不少现代高科技的气息。鉴于其坚固的灯罩，该智能卤素射灯无疑是一项经久耐用的解决方案。高品质的固定夹可确保安装的便捷性。

优点

- 实惠又高效的重点照明解决方案
- 安全耐用
- 为客户提供与时俱进的广泛选择

特点

- 结构坚固
- 不同的外形以适应不同功能
- 专业涂层
- 品质精良易于安装

应用

- 零售商店 – 销售区域、商店橱窗
- 办公室 – 展览与加亮区域
- 酒店与邮轮 – 走廊、服务区、接待区、大堂、休息室、餐厅、船舱
- 医疗保健 – 走廊、接待区、等候区
- 机场 – 抵达/离境厅、走廊、候机厅、服务台、商店

规格

智能卤素射灯 QBS020

产品类型	Die-cast aluminum versions and for MR11 lamp types:
	- QBS020, 022: fixed
	- QBS021: adjustable
	Die-cast aluminum versions and for MR16 lamp types:
	- QBS023, 026, QBS040~046: fixed
	- QBS024, 025, 027~029, QBS047: adjustable
	Cast aluminum versions and for MR16 lamp types:
光源	Halogen:
	- 1 x ESSENTIAL 1CT / GU4 / 20, 35 W
	- 1 x ESSENTIAL Closed 1CT / GU5.3 / 20, 50 W
光束角	30°, 36°
包括光源	No

灯管位置	Vertical
光源分布	Direct (D)
变压器	12 V (not included)
材质	QBS020~029, QBS040~047 versions:
	- Die-cast aluminum
	QBS030~032 versions:
颜色	- Cast aluminum
	QBS020~029, QBS040~047 versions:
	- White and grey
	QBS030~032 versions:
	- Silver
安装	Fixation by means of spring fasteners
维护	Direct lamp access
主要应用	Retail, fashion, hospitality

Versions



Smart Halogen Downlight QBS029
adjustable luminaire

