



Zadora – free to create

Zadora, fixed

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Οφέλη

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Fixed downlights with beam widths of 8°, 24°, 36° or 60° to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Χαρακτηριστικά

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths

Εφαρμογή

- Office
- Retail

Zadora, fixed

Versions



QB5570 - MASTER Line ES 50 mm - 45 W

