



Zadora – free to create

Zadora Cardanic

Zadora is a range of recessed downlights for MASTERLine 35 and 50 mm dichroic halogen lamps (with beams of 8°, 24°, 36° and 60°) and Twistline Alu lamps. It is available in fixed and adjustable versions, the latter offering 30° orientation from the vertical. Zadora downlights are also available in ready-to-install kit versions. Maintenance is made easy by direct lamp access.

Vantaggi

- Halogen accent lighting with the high power of MASTERLine 35 mm and 50 mm dichroic lamps
- Fixed downlights with beam widths of 8°, 24°, 36° or 60° to create exactly the right decorative or accent effects
- Also available in complete, ready-to-install kit versions

Caratteristiche

- Available in fixed and adjustable versions
- MASTERLine 35 mm and 50 mm dichroic lamps and Twistline Alu lamps
- Wide choice of beam widths

Applicazione

- Office
- Retail

Zadora Cardanic

Versions



Zadora QBS570, incasso fisso con lampada alogena



Zadora QBS570, incasso fisso con lampada alogena

Condizioni di applicazione

Intervallo temperatura ambiente	Da -10 a +35 °C
---------------------------------	-----------------

Approvazione e applicazione

Codice protezione impatti meccanici	IK03
-------------------------------------	------

Codice di protezione ingresso	IP20
-------------------------------	------

Funzionamento e parte elettrica

Tensione in ingresso	12 V
----------------------	------

Informazioni generali

Attacco	GU5.3
---------	-------

Classe di protezione IEC	Classe di isolamento II
--------------------------	-------------------------

Unità elettrica/alimentatore	-
------------------------------	---

Potenza della lampada	45 W
-----------------------	------

Numero di sorgenti luminose	1
-----------------------------	---

Meccanica e corpo

Order Code	Full Product Name	Colore
57323699	QBS570 1xHAL-MR50-45W 12V BR ALU	Alluminio ALU
57325099	QBS570 1xHAL-MR50-45W 12V BR MAT	Finitura opaca MAT

