



CoreLine Panel – the clear choice for LED

CoreLine panel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy savings of up to 40% compared to functional TL-D luminaires
- Uniform surface of light

Features

- Integrated LED technology
- Slim square housing
- Choice of two color temperatures: 3000 and 4000 K
- Non-Office Compliant (NOC) version and Office Compliant version (OC) available


Application

- Offices
- Retail
- Healthcare

CoreLine panel

Versions

RC132V G5 31_36_43S940 PSD
W30L120 OC



CoreLine panel Gen 5- rectangular
Office Compliant

RC132V G5 31_36_43S _840 PSU
W60L60 OC_SPP



RC132V G5 31_36_43S _840 PSD
W60L60 OC_SPP



RC132V G5 29_34_40S _830 PSU
W60L60 OC_SPP





RC132V G5 31_36_43S _840 PSU
W60L60 NOC_SPP











RC132V G5 29_34_40S _830 PSD
W60L60 OC_SPP




Dimensional drawing




Dimensional drawing



Dimensional drawing




Dimensional drawing




CoreLine panel

Dimensional drawing




Product details


Coreline panel G5 PSD connector closed



CoreLine panel Gen 5 -On/off (PSU) driver & Quick Connector




Coreline panel G5_ PSD connector Start_Step 1



CoreLine panel G5- 60x60 front of pack



CoreLine Panel Gen 5 - Multilumen driver



Coreline panel G5 backside PSD driver




CoreLine panel

Product details




Coreline panel G5 backside PSU driver




Coreline panel G5 PSU driver




Coreline panel G5_ PSD connector
Wired_Step 3



CoreLine Panel G5 30x120 OC
Front of pack




Coreline panel G5_ PSD connector
Closed_Step 4



Coreline panel G5 Recessed
Ceiling



Coreline panel G5 optical cover




Coreline panel G5_ PSD connector
Open_Step 2




Coreline panel G5 PSD driver
Lumenswitch

CoreLine panel

Product details



Coreline panel G5 PSD connector
open



Coreline panel G5_ PSD connector
Finished_Step 5



Coreline panel G5 side angle

CoreLine panel

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Protection class IEC	Safety class II
Mech. impact protection code	IK03

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Suitable for random switching	Yes
-------------------------------	-----

General Information

Order Code	Full Product Name	Embedded control	Product family code
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	Interact SNS210 sensor	RC132V
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	Interact SNS210 sensor	RC132V
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	-	-
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-	RC132V
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	-	RC132V
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-	RC132V
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	-	RC132V
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-	-
95007800	RC132V G5 36S/840 PSU W30L120 OC	-	-
95012200	RC132V G5 34S/830 PSD W30L120 OC	-	-
95013900	RC132V G5 36S/840 PSD W30L120 OC	-	-
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-	-
95371000	RC132V G5 36S/840 WIA W30L120 OC	-	-
95016000	RC132V G5 36S/940 PSU W30L120 OC	-	-
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-	-
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	-	-
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-	-
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-	-
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	-	RC132V
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-	RC132V
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCEL3	-	RC132V
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-	RC132V
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	-	RC132V
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	-	RC132V
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	-	RC132V
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	-	RC132V
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	-	RC132V
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-	-
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-	-
95004700	RC132V G5 34S/830 PSU W60L60 OC	-	-
95005400	RC132V G5 36S/840 PSU W60L60 OC	-	-
95008500	RC132V G5 34S/830 PSD W60L60 OC	-	-
95009200	RC132V G5 36S/840 PSD W60L60 OC	-	-
95010800	RC132V G5 48S/840 PSD W60L60 OC	-	-
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-	-
95015300	RC132V G5 36S/940 PSU W60L60 OC	-	-
95017700	RC132V G5 36S/940 PSD W60L60 OC	-	-
95018400	RC132V G5 43S/940 PSD W60L60 OC	-	-
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-	-
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-	-
95366600	RC132V G5 34S/830 WIA W60L60 OC	-	-
95367300	RC132V G5 36S/840 WIA W60L60 OC	-	-
95368000	RC132V G5 43S/840 WIA W60L60 OC	-	-
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-	-
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-	-
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	-	-

Light Technical (1/2)

CoreLine panel

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	-	4000 K	≥80	119 lm/W
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	-	3000 K	≥80	111 lm/W
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	All-in, Multi Lumen	4000 K	≥90	107 lm/W
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-	4000 K	≥80	106 lm/W
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	-	4000 K	≥80	106 lm/W
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-	4000 K	≥80	106 lm/W
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	-	4000 K	≥80	107 lm/W
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-	4000 K	≥80	125 lm/W
95007800	RC132V G5 36S/840 PSU W30L120 OC	-	4000 K	≥80	125 lm/W
95012200	RC132V G5 34S/830 PSD W30L120 OC	-	3000 K	≥80	120 lm/W
95013900	RC132V G5 36S/840 PSD W30L120 OC	-	4000 K	≥80	125 lm/W
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-	4000 K	≥80	125 lm/W
95371000	RC132V G5 36S/840 WIA W30L120 OC	-	4000 K	≥80	125 lm/W
95016000	RC132V G5 36S/940 PSU W30L120 OC	-	4000 K	≥90	104 lm/W
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	All-in, Multi Lumen	4000 K	≥80	125 lm/W
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	All-in, Multi Lumen	4000 K	≥80	125 lm/W
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	All-in, Multi Lumen	3000 K	≥80	120 lm/W
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	All-in, Multi Lumen	4000 K	≥80	125 lm/W
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	-	4000 K	≥80	106 lm/W
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-	4000 K	≥80	106 lm/W

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	All-in, Multi Lumen	4000 K	≥80	107 lm/W
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-	4000 K	≥80	106 lm/W
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	-	3000 K	≥80	100 lm/W
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	-	4000 K	≥80	107 lm/W
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	-	4000 K	≥80	107 lm/W
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	-	4000 K	≥80	128 lm/W
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	-	4000 K	≥80	128 lm/W
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-	3000 K	≥80	120 lm/W
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-	4000 K	≥80	125 lm/W
95004700	RC132V G5 34S/830 PSU W60L60 OC	-	3000 K	≥80	120 lm/W
95005400	RC132V G5 36S/840 PSU W60L60 OC	-	4000 K	≥80	125 lm/W
95008500	RC132V G5 34S/830 PSD W60L60 OC	-	3000 K	≥80	120 lm/W
95009200	RC132V G5 36S/840 PSD W60L60 OC	-	4000 K	≥80	125 lm/W
95010800	RC132V G5 48S/840 PSD W60L60 OC	-	4000 K	≥80	120 lm/W
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-	4000 K	≥90	104 lm/W
95015300	RC132V G5 36S/940 PSU W60L60 OC	-	4000 K	≥90	104 lm/W
95017700	RC132V G5 36S/940 PSD W60L60 OC	-	4000 K	≥90	104 lm/W
95018400	RC132V G5 43S/940 PSD W60L60 OC	-	4000 K	≥90	107 lm/W
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-	3000 K	≥80	120 lm/W
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-	4000 K	≥80	125 lm/W
95366600	RC132V G5 34S/830 WIA W60L60 OC	-	3000 K	≥80	120 lm/W
95367300	RC132V G5 36S/840 WIA W60L60 OC	-	4000 K	≥80	125 lm/W

CoreLine panel

Order Code	Full Product Name	All-in Type	Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)
			(Nom)	(CRI)	(Nom)
95368000	RC132V G5 43S/840 WIA W60L60 OC	-	4000 K	≥80	125 lm/W
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-	4000 K	≥80	125 lm/W
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-	4000 K	≥80	125 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	4,300 lm	Beam angle 90°
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	4,000 lm	Beam angle 90°
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	3,100 lm	Beam angle 90°
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	3,600 lm	Beam angle 90°
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	3,600 lm	Beam angle 90°
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	3,600 lm	Beam angle 120°
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	3,600 lm	Beam angle 90°
95003000	RC132V G5 36S/840 PSU W30L120 NOC	3,600 lm	Beam angle 120°
95007800	RC132V G5 36S/840 PSU W30L120 OC	3,600 lm	Beam angle 90°
95012200	RC132V G5 34S/830 PSD W30L120 OC	3,400 lm	Beam angle 90°
95013900	RC132V G5 36S/840 PSD W30L120 OC	3,600 lm	Beam angle 90°
95365900	RC132V G5 36S/840 WIA W30L120 NOC	3,600 lm	Beam angle 120°
95371000	RC132V G5 36S/840 WIA W30L120 OC	3,600 lm	Beam angle 90°
95016000	RC132V G5 36S/940 PSU W30L120 OC	3,600 lm	Beam angle 90°
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	3,100 lm	Beam angle 90°
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	3,100 lm	Beam angle 90°
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	2,900 lm	Beam angle 90°
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	3,100 lm	Beam angle 120°
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	3,600 lm	Beam angle 90°
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	3,600 lm	Beam angle 90°
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	3,100 lm	Beam angle 90°
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	3,600 lm	Beam angle 120°

Order Code	Full Product Name	All-in Type	Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)
			(Nom)	(CRI)	(Nom)
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	All-in, Multi Lumen	3000 K	≥80	120 lm/W

Order Code	Full Product Name	Luminous Flux	Optic type
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	3,400 lm	Beam angle 90°
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	3,600 lm	Beam angle 90°
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	3,600 lm	Beam angle 120°
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	4,300 lm	Beam angle 120°
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	4,300 lm	Beam angle 90°
94999700	RC132V G5 34S/830 PSU W60L60 NOC	3,400 lm	Beam angle 120°
95000900	RC132V G5 36S/840 PSU W60L60 NOC	3,600 lm	Beam angle 120°
95004700	RC132V G5 34S/830 PSU W60L60 OC	3,400 lm	Beam angle 90°
95005400	RC132V G5 36S/840 PSU W60L60 OC	3,600 lm	Beam angle 90°
95008500	RC132V G5 34S/830 PSD W60L60 OC	3,400 lm	Beam angle 90°
95009200	RC132V G5 36S/840 PSD W60L60 OC	3,600 lm	Beam angle 90°
95010800	RC132V G5 48S/840 PSD W60L60 OC	4,800 lm	Beam angle 90°
95014600	RC132V G5 36S/940 PSU W60L60 NOC	3,600 lm	Beam angle 120°
95015300	RC132V G5 36S/940 PSU W60L60 OC	3,600 lm	Beam angle 90°
95017700	RC132V G5 36S/940 PSD W60L60 OC	3,600 lm	Beam angle 90°
95018400	RC132V G5 43S/940 PSD W60L60 OC	4,300 lm	Beam angle 90°
95363500	RC132V G5 34S/830 WIA W60L60 NOC	3,400 lm	Beam angle 120°
95364200	RC132V G5 36S/840 WIA W60L60 NOC	3,600 lm	Beam angle 120°
95366600	RC132V G5 34S/830 WIA W60L60 OC	3,400 lm	Beam angle 90°
95367300	RC132V G5 36S/840 WIA W60L60 OC	3,600 lm	Beam angle 90°
95368000	RC132V G5 43S/840 WIA W60L60 OC	4,300 lm	Beam angle 90°
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	3,600 lm	Beam angle 90°
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	3,600 lm	Beam angle 90°
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	2,900 lm	Beam angle 90°

Operating and Electrical

CoreLine panel

Order Code	Full Product Name	Power Consumption
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	36 W
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	36 W
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	40 W
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	34 W
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	34 W
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	34 W
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	34 W
95003000	RC132V G5 36S/840 PSU W30L120 NOC	28.5 W
95007800	RC132V G5 36S/840 PSU W30L120 OC	28.5 W
95012200	RC132V G5 34S/830 PSD W30L120 OC	28.5 W
95013900	RC132V G5 36S/840 PSD W30L120 OC	28.5 W
95365900	RC132V G5 36S/840 WIA W30L120 NOC	28.5 W
95371000	RC132V G5 36S/840 WIA W30L120 OC	28.5 W
95016000	RC132V G5 36S/940 PSU W30L120 OC	34.5 W
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	34.5 W
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	34.5 W
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	34.5 W
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	34.5 W
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	34 W
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	34 W
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	40 W
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	34 W
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	34 W

Order Code	Full Product Name	Power Consumption
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	34 W
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	34 W
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	34 W
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	34 W
94999700	RC132V G5 34S/830 PSU W60L60 NOC	28.5 W
95000900	RC132V G5 36S/840 PSU W60L60 NOC	28.5 W
95004700	RC132V G5 34S/830 PSU W60L60 OC	28.5 W
95005400	RC132V G5 36S/840 PSU W60L60 OC	28.5 W
95008500	RC132V G5 34S/830 PSD W60L60 OC	28.5 W
95009200	RC132V G5 36S/840 PSD W60L60 OC	28.5 W
95010800	RC132V G5 48S/840 PSD W60L60 OC	40 W
95014600	RC132V G5 36S/940 PSU W60L60 NOC	34.5 W
95015300	RC132V G5 36S/940 PSU W60L60 OC	34.5 W
95017700	RC132V G5 36S/940 PSD W60L60 OC	34.5 W
95018400	RC132V G5 43S/940 PSD W60L60 OC	40 W
95363500	RC132V G5 34S/830 WIA W60L60 NOC	28.5 W
95364200	RC132V G5 36S/840 WIA W60L60 NOC	28.5 W
95366600	RC132V G5 34S/830 WIA W60L60 OC	28.5 W
95367300	RC132V G5 36S/840 WIA W60L60 OC	28.5 W
95368000	RC132V G5 43S/840 WIA W60L60 OC	34.5 W
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	28.5 W
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	28.5 W
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	34.5 W

Temperature

Order Code	Full Product Name	Ambient temperature range
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	0 to +35 °C
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	0 to +35 °C
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	-10 to +40 °C
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	0 to +35 °C
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	0 to +35 °C
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	0 to +35 °C
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	0 to +35 °C
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-10 to +40 °C
95007800	RC132V G5 36S/840 PSU W30L120 OC	-10 to +40 °C
95012200	RC132V G5 34S/830 PSD W30L120 OC	-10 to +40 °C
95013900	RC132V G5 36S/840 PSD W30L120 OC	-10 to +40 °C
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-10 to +40 °C
95371000	RC132V G5 36S/840 WIA W30L120 OC	-10 to +40 °C
95016000	RC132V G5 36S/940 PSU W30L120 OC	-10 to +40 °C
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-10 to +40 °C
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	-10 to +40 °C
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-10 to +40 °C
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-10 to +40 °C
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	0 to +35 °C
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	0 to +35 °C
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	0 to +35 °C
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	0 to +35 °C

Order Code	Full Product Name	Ambient temperature range
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	0 to +35 °C
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	0 to +35 °C
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	0 to +35 °C
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	0 to +35 °C
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	0 to +35 °C
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-10 to +40 °C
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-10 to +40 °C
95004700	RC132V G5 34S/830 PSU W60L60 OC	-10 to +40 °C
95005400	RC132V G5 36S/840 PSU W60L60 OC	-10 to +40 °C
95008500	RC132V G5 34S/830 PSD W60L60 OC	-10 to +40 °C
95009200	RC132V G5 36S/840 PSD W60L60 OC	-10 to +40 °C
95010800	RC132V G5 48S/840 PSD W60L60 OC	-10 to +40 °C
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-10 to +40 °C
95015300	RC132V G5 36S/940 PSU W60L60 OC	-10 to +40 °C
95017700	RC132V G5 36S/940 PSD W60L60 OC	-10 to +40 °C
95018400	RC132V G5 43S/940 PSD W60L60 OC	-10 to +40 °C
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-10 to +40 °C
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-10 to +40 °C
95366600	RC132V G5 34S/830 WIA W60L60 OC	-10 to +40 °C
95367300	RC132V G5 36S/840 WIA W60L60 OC	-10 to +40 °C
95368000	RC132V G5 43S/840 WIA W60L60 OC	-10 to +40 °C
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-10 to +40 °C
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-10 to +40 °C
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	-10 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable	Order Code	Full Product Name	Dimmable
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	Yes	01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	Yes
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	Yes	01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	Yes
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	Yes	01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	Yes
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	No	01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	Yes
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	Yes	94999700	RC132V G5 34S/830 PSU W60L60 NOC	No
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	No	95000900	RC132V G5 36S/840 PSU W60L60 NOC	No
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	Yes	95004700	RC132V G5 34S/830 PSU W60L60 OC	No
95003000	RC132V G5 36S/840 PSU W30L120 NOC	No	95005400	RC132V G5 36S/840 PSU W60L60 OC	No
95007800	RC132V G5 36S/840 PSU W30L120 OC	No	95008500	RC132V G5 34S/830 PSD W60L60 OC	Yes
95012200	RC132V G5 34S/830 PSD W30L120 OC	Yes	95009200	RC132V G5 36S/840 PSD W60L60 OC	Yes
95013900	RC132V G5 36S/840 PSD W30L120 OC	Yes	95010800	RC132V G5 48S/840 PSD W60L60 OC	Yes
95365900	RC132V G5 36S/840 WIA W30L120 NOC	Yes	95014600	RC132V G5 36S/940 PSU W60L60 NOC	No
95371000	RC132V G5 36S/840 WIA W30L120 OC	Yes	95015300	RC132V G5 36S/940 PSU W60L60 OC	No
95016000	RC132V G5 36S/940 PSU W30L120 OC	No	95017700	RC132V G5 36S/940 PSD W60L60 OC	Yes
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	No	95018400	RC132V G5 43S/940 PSD W60L60 OC	Yes
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	Yes	95363500	RC132V G5 34S/830 WIA W60L60 NOC	Yes
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	No	95364200	RC132V G5 36S/840 WIA W60L60 NOC	Yes
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	No	95366600	RC132V G5 34S/830 WIA W60L60 OC	Yes
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	Yes	95367300	RC132V G5 36S/840 WIA W60L60 OC	Yes
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	No	95368000	RC132V G5 43S/840 WIA W60L60 OC	Yes
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	Yes	95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	Yes
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	No	95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	Yes
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	Yes	95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	Yes

Approval and Application

Order Code	Full Product Name	Ingress protection code	Order Code	Full Product Name	Ingress protection code
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	IP20	01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	IP20/44
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	IP20	01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	IP20/44
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	IP20/44	01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	IP20/44
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	IP20/44	01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	IP20/44
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	IP20/44	94999700	RC132V G5 34S/830 PSU W60L60 NOC	IP20/44
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	IP20/44	95000900	RC132V G5 36S/840 PSU W60L60 NOC	IP20/44
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	IP20/44	95004700	RC132V G5 34S/830 PSU W60L60 OC	IP20/44
95003000	RC132V G5 36S/840 PSU W30L120 NOC	IP20/44	95005400	RC132V G5 36S/840 PSU W60L60 OC	IP20/44
95007800	RC132V G5 36S/840 PSU W30L120 OC	IP20/44	95008500	RC132V G5 34S/830 PSD W60L60 OC	IP20/44
95012200	RC132V G5 34S/830 PSD W30L120 OC	IP20/44	95009200	RC132V G5 36S/840 PSD W60L60 OC	IP20/44
95013900	RC132V G5 36S/840 PSD W30L120 OC	IP20/44	95010800	RC132V G5 48S/840 PSD W60L60 OC	IP20/44
95365900	RC132V G5 36S/840 WIA W30L120 NOC	IP20/44	95014600	RC132V G5 36S/940 PSU W60L60 NOC	IP20/44
95371000	RC132V G5 36S/840 WIA W30L120 OC	IP20/44	95015300	RC132V G5 36S/940 PSU W60L60 OC	IP20/44
95016000	RC132V G5 36S/940 PSU W30L120 OC	IP20/44	95017700	RC132V G5 36S/940 PSD W60L60 OC	IP20/44
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	IP20/44	95018400	RC132V G5 43S/940 PSD W60L60 OC	IP20/44
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	IP20/44	95363500	RC132V G5 34S/830 WIA W60L60 NOC	IP20/44
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	IP20/44	95364200	RC132V G5 36S/840 WIA W60L60 NOC	IP20/44
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	IP20/44	95366600	RC132V G5 34S/830 WIA W60L60 OC	IP20/44
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	IP20/44	95367300	RC132V G5 36S/840 WIA W60L60 OC	IP20/44
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	IP20/44	95368000	RC132V G5 43S/840 WIA W60L60 OC	IP20/44
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	IP20/44	95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	IP20/44
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	IP20/44	95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	IP20/44
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	IP20/44	95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	IP20/44

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	(0.38, 0.38) SDCM≤3
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	(0.38, 0.38) SDCM≤3
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	(0.38, 0.38) SDCM≤3
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	(0.38, 0.38) SDCM≤3
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
95003000	RC132V G5 36S/840 PSU W30L120 NOC	(0.38, 0.38) SDCM≤3
95007800	RC132V G5 36S/840 PSU W30L120 OC	(0.38, 0.38) SDCM≤3
95012200	RC132V G5 34S/830 PSD W30L120 OC	(0.43, 0.40) SDCM≤3
95013900	RC132V G5 36S/840 PSD W30L120 OC	(0.38, 0.38) SDCM≤3
95365900	RC132V G5 36S/840 WIA W30L120 NOC	(0.38, 0.38) SDCM≤3
95371000	RC132V G5 36S/840 WIA W30L120 OC	(0.38, 0.38) SDCM≤3
95016000	RC132V G5 36S/940 PSU W30L120 OC	(0.38, 0.38) SDCM≤3
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	(0.43, 0.40) SDCM≤3
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	(0.38, 0.38) SDCM≤3
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	(0.43, 0.40) SDCM≤3

Order Code	Full Product Name	Initial chromaticity
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
94999700	RC132V G5 34S/830 PSU W60L60 NOC	(0.43, 0.40) SDCM≤3
95000900	RC132V G5 36S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
95004700	RC132V G5 34S/830 PSU W60L60 OC	(0.43, 0.40) SDCM≤3
95005400	RC132V G5 36S/840 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95008500	RC132V G5 34S/830 PSD W60L60 OC	(0.43, 0.40) SDCM≤3
95009200	RC132V G5 36S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95010800	RC132V G5 48S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95014600	RC132V G5 36S/940 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
95015300	RC132V G5 36S/940 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95017700	RC132V G5 36S/940 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95018400	RC132V G5 43S/940 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95363500	RC132V G5 34S/830 WIA W60L60 NOC	(0.43, 0.40) SDCM≤3
95364200	RC132V G5 36S/840 WIA W60L60 NOC	(0.38, 0.38) SDCM≤3
95366600	RC132V G5 34S/830 WIA W60L60 OC	(0.43, 0.40) SDCM≤3
95367300	RC132V G5 36S/840 WIA W60L60 OC	(0.38, 0.38) SDCM≤3
95368000	RC132V G5 43S/840 WIA W60L60 OC	(0.38, 0.38) SDCM≤3
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	(0.38, 0.38) SDCM≤3
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	(0.38, 0.38) SDCM≤3
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	(0.43, 0.40) SDCM≤3

Application Conditions

Order Code	Full Product Name	Maximum dim level
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	-
01398800	RC132V G5 40S/830 SIA W60L60 OC IA4	-
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	3%
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	3%
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	1%
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-
95007800	RC132V G5 36S/840 PSU W30L120 OC	-
95012200	RC132V G5 34S/830 PSD W30L120 OC	3%
95013900	RC132V G5 36S/840 PSD W30L120 OC	3%
95365900	RC132V G5 36S/840 WIA W30L120 NOC	1%
95371000	RC132V G5 36S/840 WIA W30L120 OC	1%
95016000	RC132V G5 36S/940 PSU W30L120 OC	-
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	3%
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	3%
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	3%
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	3%

Order Code	Full Product Name	Maximum dim level
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	1%
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	1%
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	1%
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	1%
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-
95004700	RC132V G5 34S/830 PSU W60L60 OC	-
95005400	RC132V G5 36S/840 PSU W60L60 OC	-
95008500	RC132V G5 34S/830 PSD W60L60 OC	3%
95009200	RC132V G5 36S/840 PSD W60L60 OC	3%
95010800	RC132V G5 48S/840 PSD W60L60 OC	3%
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-
95015300	RC132V G5 36S/940 PSU W60L60 OC	-
95017700	RC132V G5 36S/940 PSD W60L60 OC	3%
95018400	RC132V G5 43S/940 PSD W60L60 OC	3%
95363500	RC132V G5 34S/830 WIA W60L60 NOC	1%
95364200	RC132V G5 36S/840 WIA W60L60 NOC	1%
95366600	RC132V G5 34S/830 WIA W60L60 OC	1%
95367300	RC132V G5 36S/840 WIA W60L60 OC	1%
95368000	RC132V G5 43S/840 WIA W60L60 OC	1%
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	1%
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	3%
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	3%

