



CoreLine Panel – the clear choice for LED

CoreLine panel

Whether for a new building or renovation of an existing space, customers want lighting solutions that provide quality of light and substantial energy and maintenance savings. The new CoreLine Panel range of LED products can be used to replace functional luminaires in general lighting applications. Both Non-Office Compliant (NOC) version and Office Compliant version (OC) are now available. The process of selecting, installing and maintaining is so easy – it's a simple switch.

Benefits

- Enables a simple switch from basic conventional luminaires to LED luminaires
- Energy savings of up to 40% compared to functional TL-D luminaires
- Uniform surface of light

Features



- Integrated LED technology
- Slim square housing
- Choice of two color temperatures: 3000 and 4000 K
- Non-Office Compliant (NOC) version and Office Compliant version (OC) available

Application

- Offices
- Retail
- Healthcare

CoreLine panel

Versions

	CoreLine panel G5 SIA with Sensor front side	 	RC132V G5 31_36_43S940 PSD W30L120 OC
	CoreLine panel G5_BN W62L62		CoreLine panel All-in W60L60
	CoreLine panel Gen 5- rectangular Office Compliant	 	RC132V G5 31_36_43S_840 PSU W60L60 OC_SPP
 	RC132V G5 31_36_43S_840 PSD W60L60 OC_SPP	 	RC132V G5 29_34_40S_830 PSU W60L60 OC_SPP
 	RC132V G5 31_36_43S_840 PSU W60L60 NOC_SPP		CoreLine panel G5_BN W60L60


CoreLine panel

Versions


RC132V G5 29_34_40S _830 PSD
W60L60 OC_SPP











Dimensional drawing




Dimensional drawing











Dimensional drawing




Dimensional drawing









Dimensional drawing



Dimensional drawing




Dimensional drawing



Product details




DC plug




Coreline panel G5 PSD connector closed

CoreLine panel

Product details




CoreLine panel Gen 5 -On/off
(PSU) driver & Quick Connector



Coreline panel G5_ PSD connector
Start_Step 1



CoreLine panel G5- 60x60 front of
pack




CoreLine Panel Gen 5 - Multilumen
driver



Coreline panel G5 backside PSD
driver




Coreline panel G5 backside PSU
driver



Coreline panel G5 PSU driver




Coreline panel G5_ PSD connector
Wired_Step 3



CoreLine Panel G5 30x120 OC
Front of pack

CoreLine panel

Product details



Coreline panel G5_ PSD connector
Closed_Step 4



DC plug open with driver and
panel




Coreline panel BN backside
W60L60



Coreline panel G5 Recessed
Ceiling



Coreline panel G5_ PSD connector
Open_Step 2



Coreline panel BN corner W60L60



Coreline panel G5 optical cover




Coreline panel G5 PSD driver
Lumenswitch

CoreLine panel

Product details



DC plug closed with driver and panel




Coreline panel G5 PSD connector open




CoreLine panel All-in backside W60L60



CoreLine panel frame & optical area W62L62



Wieland W5 Dali Connector



Coreline panel G5_ PSD connector Finished_Step 5



UGR19 optical exit window



Coreline panel G5 side angle

CoreLine panel

Product details



Multicolour switch panel, CCT
switch panel



CoreLine panel BN backside
W62L62



CoreLine panel All-in corner
W60L60



Multicolour switch panel, CCT
switch panel

CoreLine panel

General Information

CE mark	Yes
Driver included	Yes
ENEC mark	ENEC mark
Flammability mark	For mounting on normally flammable surfaces
Glow-wire test	Temperature 650 °C, duration 30 s
Light source replaceable	No
Number of gear units	1 unit

Light Technical

Flickering value (PstLM) - Flickering value as per EN 61000-3-3	1
Stroboscopic effect visibility measure (SVM)	0.4

Operating and Electrical

Input Voltage	220-240 V
Line Frequency	50 or 60 Hz

Mechanical and Housing

Housing Color	White
---------------	-------

Approval and Application

Protection class IEC	Safety class II
----------------------	-----------------

Initial Performance (IEC Compliant)

Luminous flux tolerance	+/-10%
-------------------------	--------

Application Conditions

Suitable for random switching	Yes
-------------------------------	-----

General Information

Order Code	Full Product Name	Embedded control	Product family code
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	Interact SNS210 sensor	RC132V
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	-	-
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-	RC132V
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	-	RC132V
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-	RC132V
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	-	RC132V
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	-	RC132V
01383400	RC132V G5 36S/840 PSD W30L120OCEL3W4W2	-	RC132V
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	-	RC132V
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	-	RC132V
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-	-
95007800	RC132V G5 36S/840 PSU W30L120 OC	-	-
95012200	RC132V G5 34S/830 PSD W30L120 OC	-	-
95013900	RC132V G5 36S/840 PSD W30L120 OC	-	-
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	-	-
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	-	-
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	-	-
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	-	-
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-	-
95371000	RC132V G5 36S/840 WIA W30L120 OC	-	-
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	-	-
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	-	-
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	-	-
95016000	RC132V G5 36S/940 PSU W30L120 OC	-	-
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-	-
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	-	-
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-	-
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-	-
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	-	-
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	-	-
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	-	-
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	-	RC132V
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-	RC132V
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCEL3	-	RC132V
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	-	RC132V
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-	RC132V
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	-	RC132V
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	-	RC132V
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	-	RC132V
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	-	RC132V
01385800	RC132V G5 31_36_43S/840PSD6060OCEL3W4W2	-	RC132V
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	-	RC132V
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	-	RC132V
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	-	RC132V
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	-	RC132V
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	-	RC132V
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	-	RC132V
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	-	RC132V
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	-	RC132V
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	-	RC132V
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-	-

Order Code	Full Product Name	Embedded control	Product family code
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-	-
95004700	RC132V G5 34S/830 PSU W60L60 OC	-	-
95005400	RC132V G5 36S/840 PSU W60L60 OC	-	-
95008500	RC132V G5 34S/830 PSD W60L60 OC	-	-
95009200	RC132V G5 36S/840 PSD W60L60 OC	-	-
95010800	RC132V G5 48S/840 PSD W60L60 OC	-	-
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-	-
95015300	RC132V G5 36S/940 PSU W60L60 OC	-	-
95017700	RC132V G5 36S/940 PSD W60L60 OC	-	-
95018400	RC132V G5 43S/940 PSD W60L60 OC	-	-
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	-	-
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	-	-
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	-	-
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	-	-
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	-	-
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	-	-
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-	-
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-	-
95366600	RC132V G5 34S/830 WIA W60L60 OC	-	-
95367300	RC132V G5 36S/840 WIA W60L60 OC	-	-
95368000	RC132V G5 43S/840 WIA W60L60 OC	-	-
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	-	-
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	-	-
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	-	-
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	-	-
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	-	-
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	-	-
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-	-
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-	-
01376600	RC133V G5 36S/840 PSED W62L62 OC	-	RC133V
01377300	RC133V G5 34S/830 PSED W62L62 OC	-	RC133V
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	-	-

Light Technical (1/2)

			Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)				Correlated Color Temperature	Color rendering index	Luminous Efficacy (rated)
Order Code	Full Product Name	All-in Type	(Nom)	(CRI)	(Nom)	Order Code	Full Product Name	All-in Type	(Nom)	(CRI)	(Nom)
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	-	4000 K	≥80	119 lm/W	01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	-	4000 K	≥80	106 lm/W
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	All-in, Multi Lumen	4000 K	≥90	107 lm/W	01383400	RC132V G5 36S/840 PSD W30L120OCELB3W4W2	-	4000 K	≥80	106 lm/W
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-	4000 K	≥80	106 lm/W	01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	-	4000 K	≥80	107 lm/W
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	-	4000 K	≥80	106 lm/W	01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	-	4000 K	≥80	107 lm/W
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-	4000 K	≥80	106 lm/W	95003000	RC132V G5 36S/840 PSU W30L120 NOC	-	4000 K	≥80	125 lm/W
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	-	4000 K	≥80	106 lm/W	95007800	RC132V G5 36S/840 PSU W30L120 OC	-	4000 K	≥80	125 lm/W

CoreLine panel

Order			Correlated	Color	Luminous				Correlated	Color	Luminous
Code	Full Product Name	All-in Type	Color Temperature (Nom)	rendering index (CRI)	Efficacy (rated) (Nom)	Order	Full Product Name	All-in Type	Color Temperature (Nom)	rendering index (CRI)	Efficacy (rated) (Nom)
95012200	RC132V G5 34S/830 PSD W30L120 OC	-	3000 K	≥80	120 lm/W	01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-	4000 K	≥80	106 lm/W
95013900	RC132V G5 36S/840 PSD W30L120 OC	-	4000 K	≥80	125 lm/W	01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	-	3000 K	≥80	100 lm/W
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	-	4000 K	≥80	125 lm/W	01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	-	4000 K	≥80	106 lm/W
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	-	4000 K	≥80	125 lm/W	01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	-	4000 K	≥80	106 lm/W
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	-	3000 K	≥80	120 lm/W	01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	-	4000 K	≥80	106 lm/W
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	-	4000 K	≥80	125 lm/W	01385800	RC132V G5 31_36_43S/840PSD6060OCELB3W4W2	All-in, Multi Lumen	4000 K	≥80	107 lm/W
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-	4000 K	≥80	125 lm/W	01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	-	4000 K	≥80	107 lm/W
95371000	RC132V G5 36S/840 WIA W30L120 OC	-	4000 K	≥80	125 lm/W	01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	-	4000 K	≥80	107 lm/W
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	-	4000 K	≥80	125 lm/W	01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	-	4000 K	≥80	128 lm/W
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	-	4000 K	≥80	126 lm/W	01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	-	4000 K	≥80	107 lm/W
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	All-in, Multi Lumen and Multi Color Temperature	3000 K	≥80	120 lm/W	01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	-	4000 K	≥80	107 lm/W
						01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	-	4000 K	≥80	128 lm/W
95016000	RC132V G5 36S/940 PSU W30L120 OC	-	4000 K	≥90	104 lm/W	01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	-	4000 K	≥80	128 lm/W
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	All-in, Multi Lumen	4000 K	≥80	125 lm/W	01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	-	4000 K	≥80	107 lm/W
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	All-in, Multi Lumen	4000 K	≥80	125 lm/W	01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	-	4000 K	≥80	128 lm/W
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	All-in, Multi Lumen	3000 K	≥80	120 lm/W	94999700	RC132V G5 34S/830 PSU W60L60 NOC	-	3000 K	≥80	120 lm/W
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	All-in, Multi Lumen	4000 K	≥80	125 lm/W	95000900	RC132V G5 36S/840 PSU W60L60 NOC	-	4000 K	≥80	125 lm/W
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	-	4000 K	≥80	126 lm/W	95004700	RC132V G5 34S/830 PSU W60L60 OC	-	3000 K	≥80	120 lm/W
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	-	4000 K	≥80	126 lm/W	95005400	RC132V G5 36S/840 PSU W60L60 OC	-	4000 K	≥80	125 lm/W
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	-	4000 K	≥80	126 lm/W	95008500	RC132V G5 34S/830 PSD W60L60 OC	-	3000 K	≥80	120 lm/W
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	-	4000 K	≥80	106 lm/W	95009200	RC132V G5 36S/840 PSD W60L60 OC	-	4000 K	≥80	125 lm/W
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-	4000 K	≥80	106 lm/W	95010800	RC132V G5 48S/840 PSD W60L60 OC	-	4000 K	≥80	120 lm/W
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	All-in, Multi Lumen	4000 K	≥80	107 lm/W	95014600	RC132V G5 36S/940 PSU W60L60 NOC	-	4000 K	≥90	104 lm/W
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	-	4000 K	≥80	106 lm/W	95015300	RC132V G5 36S/940 PSU W60L60 OC	-	4000 K	≥90	104 lm/W

CoreLine panel

Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)	Order Code	Full Product Name	All-in Type	Correlated Color Temperature (Nom)	Color rendering index (CRI)	Luminous Efficacy (rated) (Nom)
95017700	RC132V G5 36S/940 PSD W60L60 OC	-	4000 K	≥90	104 lm/W	95368000	RC132V G5 43S/840 WIA W60L60 OC	-	4000 K	≥80	125 lm/W
95018400	RC132V G5 43S/940 PSD W60L60 OC	-	4000 K	≥90	107 lm/W	95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	-	3000 K	≥80	120 lm/W
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	-	3000 K	≥80	120 lm/W	95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	-	4000 K	≥80	125 lm/W
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	-	4000 K	≥80	125 lm/W	95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	-	4000 K	≥80	125 lm/W
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	-	3000 K	≥80	120 lm/W	95375800	RC132V G5 34S/830 WIA W60L60 OC W3	-	3000 K	≥80	120 lm/W
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	-	4000 K	≥80	125 lm/W	95376500	RC132V G5 36S/840 WIA W60L60 OC W3	-	4000 K	≥80	125 lm/W
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	-	3000 K	≥80	120 lm/W	95377200	RC132V G5 43S/840 WIA W60L60 OC W3	-	4000 K	≥80	125 lm/W
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	-	4000 K	≥80	125 lm/W	95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-	4000 K	≥80	125 lm/W
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-	3000 K	≥80	120 lm/W	95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-	4000 K	≥80	125 lm/W
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-	4000 K	≥80	125 lm/W	01376600	RC133V G5 36S/840 PSED W62L62 OC	-	4000 K	≥80	120 lm/W
95366600	RC132V G5 34S/830 WIA W60L60 OC	-	3000 K	≥80	120 lm/W	01377300	RC133V G5 34S/830 PSED W62L62 OC	-	3000 K	≥80	113 lm/W
95367300	RC132V G5 36S/840 WIA W60L60 OC	-	4000 K	≥80	125 lm/W	95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	All-in, Multi Lumen	3000 K	≥80	120 lm/W

Light Technical (2/2)

Order Code	Full Product Name	Luminous Flux	Optic type	Order Code	Full Product Name	Luminous Flux	Optic type
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	4,300 lm	Beam angle 90°	95003000	RC132V G5 36S/840 PSU W30L120 NOC	3,600 lm	Beam angle 120°
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	3,100 lm	Beam angle 90°	95007800	RC132V G5 36S/840 PSU W30L120 OC	3,600 lm	Beam angle 90°
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	3,600 lm	Beam angle 90°	95012200	RC132V G5 34S/830 PSD W30L120 OC	3,400 lm	Beam angle 90°
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	3,600 lm	Beam angle 90°	95013900	RC132V G5 36S/840 PSD W30L120 OC	3,600 lm	Beam angle 90°
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	3,600 lm	Beam angle 120°	95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	3,600 lm	Beam angle 120°
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	3,600 lm	Beam angle 120°	95024500	RC132V G5 36S/840 PSU W30L120 OC W3	3,600 lm	Beam angle 90°
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	3,600 lm	Beam angle 90°	95028300	RC132V G5 34S/830 PSD W30L120 OC W5	3,400 lm	Beam angle 90°
01383400	RC132V G5 36S/840 PSD W30L120OCEL3W4W2	3,600 lm	Beam angle 90°	95029000	RC132V G5 36S/840 PSD W30L120 OC W5	3,600 lm	Beam angle 90°
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	3,600 lm	Beam angle 90°	95365900	RC132V G5 36S/840 WIA W30L120 NOC	3,600 lm	Beam angle 120°
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	3,600 lm	Beam angle 90°	95371000	RC132V G5 36S/840 WIA W30L120 OC	3,600 lm	Beam angle 90°

CoreLine panel

Order Code	Full Product Name	Luminous	
		Flux	Optic type
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	3,600 lm	Beam angle 90°
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	3,600 lm	Beam angle 90°
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	2,900 lm	Beam angle 90°
95016000	RC132V G5 36S/940 PSU W30L120 OC	3,600 lm	Beam angle 90°
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	3,100 lm	Beam angle 90°
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	3,100 lm	Beam angle 90°
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	2,900 lm	Beam angle 90°
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	3,100 lm	Beam angle 120°
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	3,600 lm	Beam angle 120°
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	3,600 lm	Beam angle 90°
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	3,600 lm	Beam angle 90°
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	3,600 lm	Beam angle 90°
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	3,600 lm	Beam angle 90°
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	3,100 lm	Beam angle 90°
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	3,600 lm	Beam angle 90°
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	3,600 lm	Beam angle 120°
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	3,400 lm	Beam angle 90°
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	3,600 lm	Beam angle 120°
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	3,600 lm	Beam angle 90°
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	3,600 lm	Beam angle 90°
01385800	RC132V G5 31_36_43S/840PSD6060OCELB3W4W2	3,100 lm	Beam angle 90°
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	3,600 lm	Beam angle 90°
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	3,600 lm	Beam angle 120°
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	4,300 lm	Beam angle 120°
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	3,600 lm	Beam angle 120°

Order Code	Full Product Name	Luminous	
		Flux	Optic type
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	3,600 lm	Beam angle 90°
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	4,300 lm	Beam angle 120°
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	4,300 lm	Beam angle 90°
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	3,600 lm	Beam angle 90°
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	4,300 lm	Beam angle 90°
94999700	RC132V G5 34S/830 PSU W60L60 NOC	3,400 lm	Beam angle 120°
95000900	RC132V G5 36S/840 PSU W60L60 NOC	3,600 lm	Beam angle 120°
95004700	RC132V G5 34S/830 PSU W60L60 OC	3,400 lm	Beam angle 90°
95005400	RC132V G5 36S/840 PSU W60L60 OC	3,600 lm	Beam angle 90°
95008500	RC132V G5 34S/830 PSD W60L60 OC	3,400 lm	Beam angle 90°
95009200	RC132V G5 36S/840 PSD W60L60 OC	3,600 lm	Beam angle 90°
95010800	RC132V G5 48S/840 PSD W60L60 OC	4,800 lm	Beam angle 90°
95014600	RC132V G5 36S/940 PSU W60L60 NOC	3,600 lm	Beam angle 120°
95015300	RC132V G5 36S/940 PSU W60L60 OC	3,600 lm	Beam angle 90°
95017700	RC132V G5 36S/940 PSD W60L60 OC	3,600 lm	Beam angle 90°
95018400	RC132V G5 43S/940 PSD W60L60 OC	4,300 lm	Beam angle 90°
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	3,400 lm	Beam angle 120°
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	3,600 lm	Beam angle 120°
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	3,400 lm	Beam angle 90°
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	3,600 lm	Beam angle 90°
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	3,400 lm	Beam angle 90°
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	3,600 lm	Beam angle 90°
95363500	RC132V G5 34S/830 WIA W60L60 NOC	3,400 lm	Beam angle 120°
95364200	RC132V G5 36S/840 WIA W60L60 NOC	3,600 lm	Beam angle 120°
95366600	RC132V G5 34S/830 WIA W60L60 OC	3,400 lm	Beam angle 90°

CoreLine panel

Order Code	Full Product Name	Luminous	
		Flux	Optic type
95367300	RC132V G5 36S/840 WIA W60L60 OC	3,600 lm	Beam angle 90°
95368000	RC132V G5 43S/840 WIA W60L60 OC	4,300 lm	Beam angle 90°
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	3,400 lm	Beam angle 120°
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	3,600 lm	Beam angle 120°
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	4,300 lm	Beam angle 120°
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	3,400 lm	Beam angle 90°
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	3,600 lm	Beam angle 90°

Order Code	Full Product Name	Luminous	
		Flux	Optic type
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	4,300 lm	Beam angle 90°
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	3,600 lm	Beam angle 90°
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	3,600 lm	Beam angle 90°
01376600	RC133V G5 36S/840 PSED W62L62 OC	3,600 lm	Beam angle 90°
01377300	RC133V G5 34S/830 PSED W62L62 OC	3,400 lm	Beam angle 90°
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	2,900 lm	Beam angle 90°

Operating and Electrical

Order Code	Full Product Name	Power Consumption
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	36 W
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	40 W
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	34 W
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	34 W
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	34 W
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	34 W
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	34 W
01383400	RC132V G5 36S/840 PSD W30L120OCELB3W4W2	34 W
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	34 W
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	34 W
95003000	RC132V G5 36S/840 PSU W30L120 NOC	28.5 W
95007800	RC132V G5 36S/840 PSU W30L120 OC	28.5 W
95012200	RC132V G5 34S/830 PSD W30L120 OC	28.5 W
95013900	RC132V G5 36S/840 PSD W30L120 OC	28.5 W
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	28.5 W
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	28.5 W
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	28.5 W
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	28.5 W
95365900	RC132V G5 36S/840 WIA W30L120 NOC	28.5 W
95371000	RC132V G5 36S/840 WIA W30L120 OC	28.5 W
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	28.5 W
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	28.5 W
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	34.5 W
95016000	RC132V G5 36S/940 PSU W30L120 OC	34.5 W
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	34.5 W
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	34.5 W
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	34.5 W
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	34.5 W
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	28.5 W
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	28.5 W
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	28.5 W
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	34 W
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	34 W

Order Code	Full Product Name	Power Consumption
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	40 W
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	34 W
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	34 W
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	34 W
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	34 W
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	34 W
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	34 W
01385800	RC132V G5 31_36_43S/840PSD6060OCELB3W4W2	40 W
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	34 W
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	34 W
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	34 W
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	34 W
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	34 W
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	34 W
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	34 W
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	34 W
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	34 W
94999700	RC132V G5 34S/830 PSU W60L60 NOC	28.5 W
95000900	RC132V G5 36S/840 PSU W60L60 NOC	28.5 W
95004700	RC132V G5 34S/830 PSU W60L60 OC	28.5 W
95005400	RC132V G5 36S/840 PSU W60L60 OC	28.5 W
95008500	RC132V G5 34S/830 PSD W60L60 OC	28.5 W
95009200	RC132V G5 36S/840 PSD W60L60 OC	28.5 W
95010800	RC132V G5 48S/840 PSD W60L60 OC	40 W
95014600	RC132V G5 36S/940 PSU W60L60 NOC	34.5 W
95015300	RC132V G5 36S/940 PSU W60L60 OC	34.5 W
95017700	RC132V G5 36S/940 PSD W60L60 OC	34.5 W
95018400	RC132V G5 43S/940 PSD W60L60 OC	40 W
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	28.5 W
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	28.5 W
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	28.5 W
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	28.5 W
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	28.5 W

CoreLine panel

Order Code	Full Product Name	Power Consumption
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	28.5 W
95363500	RC132V G5 34S/830 WIA W60L60 NOC	28.5 W
95364200	RC132V G5 36S/840 WIA W60L60 NOC	28.5 W
95366600	RC132V G5 34S/830 WIA W60L60 OC	28.5 W
95367300	RC132V G5 36S/840 WIA W60L60 OC	28.5 W
95368000	RC132V G5 43S/840 WIA W60L60 OC	34.5 W
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	28.5 W
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	28.5 W
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	34.5 W

Order Code	Full Product Name	Power Consumption
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	28.5 W
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	28.5 W
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	34.5 W
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	28.5 W
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	28.5 W
01376600	RC133V G5 36S/840 PSED W62L62 OC	30 W
01377300	RC133V G5 34S/830 PSED W62L62 OC	30 W
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	34.5 W

Temperature

Order Code	Full Product Name	Ambient temperature range
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	0 to +35 °C
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	-10 to +40 °C
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	0 to +35 °C
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	0 to +35 °C
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	0 to +35 °C
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	0 to +35 °C
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	0 to +35 °C
01383400	RC132V G5 36S/840 PSD W30L120OCELB3W4W2	0 to +35 °C
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	0 to +35 °C
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	0 to +35 °C
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-10 to +40 °C
95007800	RC132V G5 36S/840 PSU W30L120 OC	-10 to +40 °C
95012200	RC132V G5 34S/830 PSD W30L120 OC	-10 to +40 °C
95013900	RC132V G5 36S/840 PSD W30L120 OC	-10 to +40 °C
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	-10 to +40 °C
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	-10 to +40 °C
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	-10 to +40 °C
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	-10 to +40 °C
95365900	RC132V G5 36S/840 WIA W30L120 NOC	-10 to +40 °C
95371000	RC132V G5 36S/840 WIA W30L120 OC	-10 to +40 °C
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	-10 to +40 °C
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	-10 to +35 °C
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	-10 to +35 °C
95016000	RC132V G5 36S/940 PSU W30L120 OC	-10 to +40 °C
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-10 to +40 °C
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	-10 to +40 °C
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-10 to +40 °C
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-10 to +40 °C
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	-10 to +35 °C
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	-10 to +35 °C
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	-10 to +35 °C
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	0 to +35 °C
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	0 to +35 °C
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	0 to +35 °C
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	0 to +35 °C
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	0 to +35 °C
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	0 to +35 °C
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	0 to +35 °C

Order Code	Full Product Name	Ambient temperature range
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	0 to +35 °C
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	0 to +35 °C
01385800	RC132V G5 31_36_43S/840PSD6060OCELB3W4W2	0 to +35 °C
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	0 to +35 °C
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	0 to +35 °C
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	0 to +35 °C
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	0 to +35 °C
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	0 to +35 °C
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	0 to +35 °C
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	0 to +35 °C
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	0 to +35 °C
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	0 to +35 °C
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-10 to +40 °C
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-10 to +40 °C
95004700	RC132V G5 34S/830 PSU W60L60 OC	-10 to +40 °C
95005400	RC132V G5 36S/840 PSU W60L60 OC	-10 to +40 °C
95008500	RC132V G5 34S/830 PSD W60L60 OC	-10 to +40 °C
95009200	RC132V G5 36S/840 PSD W60L60 OC	-10 to +40 °C
95010800	RC132V G5 48S/840 PSD W60L60 OC	-10 to +40 °C
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-10 to +40 °C
95015300	RC132V G5 36S/940 PSU W60L60 OC	-10 to +40 °C
95017700	RC132V G5 36S/940 PSD W60L60 OC	-10 to +40 °C
95018400	RC132V G5 43S/940 PSD W60L60 OC	-10 to +40 °C
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	-10 to +40 °C
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	-10 to +40 °C
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	-10 to +40 °C
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	-10 to +40 °C
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	-10 to +40 °C
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	-10 to +40 °C
95363500	RC132V G5 34S/830 WIA W60L60 NOC	-10 to +40 °C
95364200	RC132V G5 36S/840 WIA W60L60 NOC	-10 to +40 °C
95366600	RC132V G5 34S/830 WIA W60L60 OC	-10 to +40 °C
95367300	RC132V G5 36S/840 WIA W60L60 OC	-10 to +40 °C
95368000	RC132V G5 43S/840 WIA W60L60 OC	-10 to +40 °C
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	-10 to +40 °C
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	-10 to +40 °C

CoreLine panel

Order Code	Full Product Name	Ambient temperature range
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	-10 to +40 °C
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	-10 to +40 °C
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	-10 to +40 °C
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	-10 to +40 °C
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	-10 to +40 °C

Order Code	Full Product Name	Ambient temperature range
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	-10 to +40 °C
01376600	RC133V G5 36S/840 PSED W62L62 OC	0 to +35 °C
01377300	RC133V G5 34S/830 PSED W62L62 OC	0 to +35 °C
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	-10 to +40 °C

Controls and Dimming

Order Code	Full Product Name	Dimmable
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	Yes
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	Yes
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	No
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	Yes
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	No
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	No
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	No
01383400	RC132V G5 36S/840 PSD W30L120OCEL3W4W2	Yes
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	Yes
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	Yes
95003000	RC132V G5 36S/840 PSU W30L120 NOC	No
95007800	RC132V G5 36S/840 PSU W30L120 OC	No
95012200	RC132V G5 34S/830 PSD W30L120 OC	Yes
95013900	RC132V G5 36S/840 PSD W30L120 OC	Yes
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	No
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	No
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	Yes
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	Yes
95365900	RC132V G5 36S/840 WIA W30L120 NOC	Yes
95371000	RC132V G5 36S/840 WIA W30L120 OC	Yes
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	Yes
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	No
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	No
95016000	RC132V G5 36S/940 PSU W30L120 OC	No
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	No
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	Yes
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	No
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	No
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	No
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	No
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	Yes
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	Yes
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	No
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCEL3	Yes
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	No
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	No
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	Yes
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	No
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	No
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	Yes
01385800	RC132V G5 31_36_43S/840PSD6060OCEL3W4W2	Yes
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	Yes

Order Code	Full Product Name	Dimmable
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	Yes
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	Yes
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	Yes
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	Yes
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	Yes
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	Yes
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	Yes
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	Yes
94999700	RC132V G5 34S/830 PSU W60L60 NOC	No
95000900	RC132V G5 36S/840 PSU W60L60 NOC	No
95004700	RC132V G5 34S/830 PSU W60L60 OC	No
95005400	RC132V G5 36S/840 PSU W60L60 OC	No
95008500	RC132V G5 34S/830 PSD W60L60 OC	Yes
95009200	RC132V G5 36S/840 PSD W60L60 OC	Yes
95010800	RC132V G5 48S/840 PSD W60L60 OC	Yes
95014600	RC132V G5 36S/940 PSU W60L60 NOC	No
95015300	RC132V G5 36S/940 PSU W60L60 OC	No
95017700	RC132V G5 36S/940 PSD W60L60 OC	Yes
95018400	RC132V G5 43S/940 PSD W60L60 OC	Yes
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	No
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	No
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	No
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	No
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	Yes
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	Yes
95363500	RC132V G5 34S/830 WIA W60L60 NOC	Yes
95364200	RC132V G5 36S/840 WIA W60L60 NOC	Yes
95366600	RC132V G5 34S/830 WIA W60L60 OC	Yes
95367300	RC132V G5 36S/840 WIA W60L60 OC	Yes
95368000	RC132V G5 43S/840 WIA W60L60 OC	Yes
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	Yes
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	Yes
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	Yes
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	Yes
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	Yes
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	Yes
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	Yes
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	Yes
01376600	RC133V G5 36S/840 PSED W62L62 OC	Yes
01377300	RC133V G5 34S/830 PSED W62L62 OC	Yes
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	Yes

Approval and Application

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	IK03	IP20
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	IK03	IP20/44
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	IK03	IP20/44
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	IK03	IP20/44
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	IK03	IP20/44
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	IK03	IP20/44
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	IK03	IP20/44
01383400	RC132V G5 36S/840 PSD W30L120OCELB3W4W2	IK03	IP20/44
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	IK03	IP20/44
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	IK03	IP20/44
95003000	RC132V G5 36S/840 PSU W30L120 NOC	IK03	IP20/44
95007800	RC132V G5 36S/840 PSU W30L120 OC	IK03	IP20/44
95012200	RC132V G5 34S/830 PSD W30L120 OC	IK03	IP20/44
95013900	RC132V G5 36S/840 PSD W30L120 OC	IK03	IP20/44
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	IK03	IP20/44
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	IK03	IP20/44
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	IK03	IP20/44
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	IK03	IP20/44
95365900	RC132V G5 36S/840 WIA W30L120 NOC	IK03	IP20/44
95371000	RC132V G5 36S/840 WIA W30L120 OC	IK03	IP20/44
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	IK03	IP20/44
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	IK02	IP20
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	IK03	IP20
95016000	RC132V G5 36S/940 PSU W30L120 OC	IK03	IP20/44
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	IK03	IP20/44
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	IK03	IP20/44
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	IK03	IP20/44
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	IK03	IP20/44
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	IK02	IP20
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	IK02	IP20
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	IK02	IP20
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	IK03	IP20/44
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	IK03	IP20/44
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCELB3	IK03	IP20/44
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	IK03	IP20/44
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	IK03	IP20/44
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	IK03	IP20/44
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	IK03	IP20/44
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	IK03	IP20/44

Order Code	Full Product Name	Mech. impact protection code	Ingress protection code
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	IK03	IP20/44
01385800	RC132V G5 31_36_43S/ 840PSD6060OCELB3W4W2	IK03	IP20/44
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	IK03	IP20/44
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	IK03	IP20/44
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	IK03	IP20/44
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	IK03	IP20/44
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	IK03	IP20/44
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	IK03	IP20/44
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	IK03	IP20/44
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	IK03	IP20/44
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	IK03	IP20/44
94999700	RC132V G5 34S/830 PSU W60L60 NOC	IK03	IP20/44
95000900	RC132V G5 36S/840 PSU W60L60 NOC	IK03	IP20/44
95004700	RC132V G5 34S/830 PSU W60L60 OC	IK03	IP20/44
95005400	RC132V G5 36S/840 PSU W60L60 OC	IK03	IP20/44
95008500	RC132V G5 34S/830 PSD W60L60 OC	IK03	IP20/44
95009200	RC132V G5 36S/840 PSD W60L60 OC	IK03	IP20/44
95010800	RC132V G5 48S/840 PSD W60L60 OC	IK03	IP20/44
95014600	RC132V G5 36S/940 PSU W60L60 NOC	IK03	IP20/44
95015300	RC132V G5 36S/940 PSU W60L60 OC	IK03	IP20/44
95017700	RC132V G5 36S/940 PSD W60L60 OC	IK03	IP20/44
95018400	RC132V G5 43S/940 PSD W60L60 OC	IK03	IP20/44
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	IK03	IP20/44
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	IK03	IP20/44
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	IK03	IP20/44
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	IK03	IP20/44
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	IK03	IP20/44
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	IK03	IP20/44
95363500	RC132V G5 34S/830 WIA W60L60 NOC	IK03	IP20/44
95364200	RC132V G5 36S/840 WIA W60L60 NOC	IK03	IP20/44
95366600	RC132V G5 34S/830 WIA W60L60 OC	IK03	IP20/44
95367300	RC132V G5 36S/840 WIA W60L60 OC	IK03	IP20/44
95368000	RC132V G5 43S/840 WIA W60L60 OC	IK03	IP20/44
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	IK03	IP20/44
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	IK03	IP20/44
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	IK03	IP20/44
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	IK03	IP20/44
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	IK03	IP20/44
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	IK03	IP20/44
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	IK03	IP20/44
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	IK03	IP20/44

Order Code	Full Product Name	Mech.	Ingress
		impact protection code	protection code
01376600	RC133V G5 36S/840 PSED W62L62 OC	IK03	IP20/44
01377300	RC133V G5 34S/830 PSED W62L62 OC	IK03	IP20/44

Order Code	Full Product Name	Mech.	Ingress
		impact protection code	protection code
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	IK03	IP20/44

Initial Performance (IEC Compliant)

Order Code	Full Product Name	Initial chromaticity
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	(0.38, 0.38) SDCM≤3
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	(0.38, 0.38) SDCM≤3
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	(0.38, 0.38) SDCM≤3
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	(0.38, 0.38) SDCM≤3
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	(0.38, 0.38) SDCM≤3
01383400	RC132V G5 36S/840 PSD W30L120OCEL3W4W2	(0.38, 0.38) SDCM≤3
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	(0.38, 0.38) SDCM≤3
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	(0.38, 0.38) SDCM≤3
95003000	RC132V G5 36S/840 PSU W30L120 NOC	(0.38, 0.38) SDCM≤3
95007800	RC132V G5 36S/840 PSU W30L120 OC	(0.38, 0.38) SDCM≤3
95012200	RC132V G5 34S/830 PSD W30L120 OC	(0.43, 0.40) SDCM≤3
95013900	RC132V G5 36S/840 PSD W30L120 OC	(0.38, 0.38) SDCM≤3
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	(0.38, 0.38) SDCM≤3
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	(0.38, 0.38) SDCM≤3
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	(0.43, 0.40) SDCM≤3
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	(0.38, 0.38) SDCM≤3
95365900	RC132V G5 36S/840 WIA W30L120 NOC	(0.38, 0.38) SDCM≤3
95371000	RC132V G5 36S/840 WIA W30L120 OC	(0.38, 0.38) SDCM≤3
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	(0.38, 0.38) SDCM≤3
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	(0.38, 0.38) SDCM ≤3
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	(0.38, 0.38) SDCM ≤3
95016000	RC132V G5 36S/940 PSU W30L120 OC	(0.38, 0.38) SDCM≤3
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	(0.43, 0.40) SDCM≤3
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	(0.38, 0.38) SDCM ≤3
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	(0.38, 0.38) SDCM ≤3
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	(0.38, 0.38) SDCM ≤3
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCEL3	(0.38, 0.38) SDCM≤3
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	(0.38, 0.38) SDCM≤3
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	(0.43, 0.40) SDCM≤3
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	(0.38, 0.38) SDCM≤3
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	(0.38, 0.38) SDCM≤3
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	(0.38, 0.38) SDCM≤3
01385800	RC132V G5 31_36_43S/840PSD6060OCEL3W4W2	(0.38, 0.38) SDCM≤3
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	(0.38, 0.38) SDCM≤3

Order Code	Full Product Name	Initial chromaticity
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	(0.38, 0.38) SDCM≤3
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	(0.38, 0.38) SDCM≤3
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	(0.38, 0.38) SDCM≤3
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	(0.38, 0.38) SDCM≤3
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	(0.38, 0.38) SDCM≤3
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	(0.38, 0.38) SDCM≤3
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	(0.38, 0.38) SDCM≤3
94999700	RC132V G5 34S/830 PSU W60L60 NOC	(0.43, 0.40) SDCM≤3
95000900	RC132V G5 36S/840 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
95004700	RC132V G5 34S/830 PSU W60L60 OC	(0.43, 0.40) SDCM≤3
95005400	RC132V G5 36S/840 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95008500	RC132V G5 34S/830 PSD W60L60 OC	(0.43, 0.40) SDCM≤3
95009200	RC132V G5 36S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95010800	RC132V G5 48S/840 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95014600	RC132V G5 36S/940 PSU W60L60 NOC	(0.38, 0.38) SDCM≤3
95015300	RC132V G5 36S/940 PSU W60L60 OC	(0.38, 0.38) SDCM≤3
95017700	RC132V G5 36S/940 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95018400	RC132V G5 43S/940 PSD W60L60 OC	(0.38, 0.38) SDCM≤3
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	(0.43, 0.40) SDCM≤3
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	(0.38, 0.38) SDCM≤3
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	(0.43, 0.40) SDCM≤3
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	(0.38, 0.38) SDCM≤3
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	(0.43, 0.40) SDCM≤3
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	(0.38, 0.38) SDCM≤3
95363500	RC132V G5 34S/830 WIA W60L60 NOC	(0.43, 0.40) SDCM≤3
95364200	RC132V G5 36S/840 WIA W60L60 NOC	(0.38, 0.38) SDCM≤3
95366600	RC132V G5 34S/830 WIA W60L60 OC	(0.43, 0.40) SDCM≤3
95367300	RC132V G5 36S/840 WIA W60L60 OC	(0.38, 0.38) SDCM≤3
95368000	RC132V G5 43S/840 WIA W60L60 OC	(0.38, 0.38) SDCM≤3
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	(0.43, 0.40) SDCM≤3
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	(0.38, 0.38) SDCM≤3
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	(0.38, 0.38) SDCM≤3
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	(0.43, 0.40) SDCM≤3
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	(0.38, 0.38) SDCM≤3
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	(0.38, 0.38) SDCM≤3
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	(0.38, 0.38) SDCM≤3
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	(0.38, 0.38) SDCM≤3
01376600	RC133V G5 36S/840 PSED W62L62 OC	(0.38, 0.38) SDCM≤3
01377300	RC133V G5 34S/830 PSED W62L62 OC	(0.43, 0.40) SDCM≤3
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	(0.43, 0.40) SDCM≤3

Application Conditions

Order Code	Full Product Name	Maximum dim level
01397100	RC132V G5 43S/840 SIA W60L60 OC IA4	-
95040500	RC132V G5 31_36_43S/940 PSD W30L120 OC	3%
01369800	RC132V G5 36S/840 PSU W30L120 OC ELB3	-
01370400	RC132V G5 36S/840 PSD W30L120 OC ELB3	3%
01375900	RC132V G5 36S/840 PSU W30L120 NOC ELB3	-
01381000	RC132V G5 36S/840 PSU W30L120 NOC ELB3W4	-
01382700	RC132V G5 36S/840 PSU W30L120 OC ELB3 W4	-
01383400	RC132V G5 36S/840 PSD W30L120OCEL3W4W2	3%
01388900	RC132V G5 36S/840 WIA W30L120 OC ELB3	1%
01392600	RC132V G5 36S/840 WIA W30L120 OC ELB3 W4	1%
95003000	RC132V G5 36S/840 PSU W30L120 NOC	-
95007800	RC132V G5 36S/840 PSU W30L120 OC	-
95012200	RC132V G5 34S/830 PSD W30L120 OC	3%
95013900	RC132V G5 36S/840 PSD W30L120 OC	3%
95021400	RC132V G5 36S/840 PSU W30L120 NOC W3	-
95024500	RC132V G5 36S/840 PSU W30L120 OC W3	-
95028300	RC132V G5 34S/830 PSD W30L120 OC W5	3%
95029000	RC132V G5 36S/840 PSD W30L120 OC W5	3%
95365900	RC132V G5 36S/840 WIA W30L120 NOC	1%
95371000	RC132V G5 36S/840 WIA W30L120 OC	1%
95378900	RC132V G5 36S/840 WIA W30L120 OC W3	1%
50189800	RC133V G5 36S/840 PSU W62L62 OC BN	-
50176800	RC132V G5 29_36_43S/830_40 PSU W60L60 OC	-
95016000	RC132V G5 36S/940 PSU W30L120 OC	-
95031300	RC132V G5 31_36_43S/840 PSU W60L60 OC	-
95037500	RC132V G5 31_36_43S/840 PSD W60L60 OC	3%
95030600	RC132V G5 29_34_40S/830 PSU W60L60 OC	-
95035100	RC132V G5 31_36_43S/840 PSU W60L60 NOC	-
51064799	RC132V G5 36S/840 PSU W60L60 NOC BN6	-
51065499	RC132V G5 36S/840 PSU W60L60 OC BN6	-
50195900	RC132V G5 36S/840 PSD W60L60 OC BN	3%
01367400	RC132V G5 36S/840 PSD W60L60 OC ELB3	3%
01368100	RC132V G5 36S/840 PSU W60L60 OC ELB3	-
01371100	RC132V G5 31_36_43S/840 PSD W60L60OCEL3	3%
01372800	RC132V G5 36S/840 PSD W60L60 OCTP(a)ELB3	-
01373500	RC132V G5 36S/840 PSU W60L60 NOC ELB3	-
01374200	RC132V G5 34S/830 PSD W60L60 OC ELB3	3%
01378000	RC132V G5 36S/840 PSU W60L60 NOC ELB3W4	-
01379700	RC132V G5 36S/840 PSU W60L60 OC ELB3W4	-
01380300	RC132V G5 36S/840 PSD W60L60 OC ELB3W4W2	3%
01385800	RC132V G5 31_36_43S/840PSD6060OCEL3W4W2	3%
01386500	RC132V G5 36S/840 WIA W60L60 OC ELB3	1%

Order Code	Full Product Name	Maximum dim level
01387200	RC132V G5 36S/840 WIA W60L60 NOC ELB3	1%
01389600	RC132V G5 43S/840 WIA W60L60 NOC ELB3	1%
01390200	RC132V G5 36S/840 WIA W60L60 NOC ELB3 W4	1%
01391900	RC132V G5 36S/840 WIA W60L60 OC ELB3 W4	1%
01393300	RC132V G5 43S/840 WIA W60L60 NOC ELB3 W4	1%
01394000	RC132V G5 43S/840 WIA W60L60 OC ELB3	1%
01395700	RC132V G5 36/840 WIA W60L60 OC ELB3TP(a)	1%
01396400	RC132V G5 43S/840 WIA W60L60 OC ELB3 W4	1%
94999700	RC132V G5 34S/830 PSU W60L60 NOC	-
95000900	RC132V G5 36S/840 PSU W60L60 NOC	-
95004700	RC132V G5 34S/830 PSU W60L60 OC	-
95005400	RC132V G5 36S/840 PSU W60L60 OC	-
95008500	RC132V G5 34S/830 PSD W60L60 OC	3%
95009200	RC132V G5 36S/840 PSD W60L60 OC	3%
95010800	RC132V G5 48S/840 PSD W60L60 OC	3%
95014600	RC132V G5 36S/940 PSU W60L60 NOC	-
95015300	RC132V G5 36S/940 PSU W60L60 OC	-
95017700	RC132V G5 36S/940 PSD W60L60 OC	3%
95018400	RC132V G5 43S/940 PSD W60L60 OC	3%
95019100	RC132V G5 34S/830 PSU W60L60 NOC W3	-
95020700	RC132V G5 36S/840 PSU W60L60 NOC W3	-
95022100	RC132V G5 34S/830 PSU W60L60 OC W3	-
95023800	RC132V G5 36S/840 PSU W60L60 OC W3	-
95026900	RC132V G5 34S/830 PSD W60L60 OC W5	3%
95027600	RC132V G5 36S/840 PSD W60L60 OC W5	3%
95363500	RC132V G5 34S/830 WIA W60L60 NOC	1%
95364200	RC132V G5 36S/840 WIA W60L60 NOC	1%
95366600	RC132V G5 34S/830 WIA W60L60 OC	1%
95367300	RC132V G5 36S/840 WIA W60L60 OC	1%
95368000	RC132V G5 43S/840 WIA W60L60 OC	1%
95372700	RC132V G5 34S/830 WIA W60L60 NOC W3	1%
95373400	RC132V G5 36S/840 WIA W60L60 NOC W3	1%
95374100	RC132V G5 43S/840 WIA W60L60 NOC W3	1%
95375800	RC132V G5 34S/830 WIA W60L60 OC W3	1%
95376500	RC132V G5 36S/840 WIA W60L60 OC W3	1%
95377200	RC132V G5 43S/840 WIA W60L60 OC W3	1%
95379600	RC132V G5 36S/840 WIA W60L60 OC TP(a)	1%
95380200	RC132V G5 36S/840 PSD W60L60 OC TP(a)	3%
01376600	RC133V G5 36S/840 PSED W62L62 OC	3%
01377300	RC133V G5 34S/830 PSED W62L62 OC	3%
95036800	RC132V G5 29_34_40S/830 PSD W60L60 OC	3%

CoreLine panel

