



High-tech accent lighting

GreenAccent

The new GreenAccent LED accent luminaire has a refined finish, and the 4 different mounting options make it possible to address an environment's accent lighting needs while retaining the same visual concept. With optimized service life in the segment and high energy efficiency, it allows the replacement of traditional metal vapor lamp systems with high quality lighting and faithful color rendering.

Benefits

- Text only available for Brazilian version

Features

- Recessed, Semi-recessed, Surface-mounted and Rail Versions
- Color Temperature Warm White 3000K (IRC 80) – Neutral White 4000K Version available on request
- White Body in Injected Aluminum – Black Finish available on request
- Beam Angle 16° (NB), 24° (MB) and 32° (WB)
- Power 15W (LED10) and 30W (LED20) – Luminous Efficacy 65 lm/w
- Service life of 30,000 hours
- Electronic driver 220-240 V and 50/60 Hz

Application

- Ideal for accent lighting in areas such as:
- Shopping areas
- Stores
- Museums
- Supermarkets

Specifications

Type	LED Floodlight
Light source	LED10/LED20 Module

Mains Voltage	Electronic Fixed 220 V - 60/50 Hz: (PSU)
Materials and finishing	Body in Injected Aluminum

Installation	Recessed/Rail	Approbation Signs	N/A
--------------	---------------	-------------------	-----

Versions



GreenAccent Semi-Embutir

GreenAccent Trilho

General Information

Light source color	830 warm white
Duplication code	A
Number of light sources	1 pc

General Information

Order Code	Full Product Name	Lamp family code
919406000591	RS181B A LED10/830 PSU-E MB 24G WH	LED10
919406000601	RS181B A LED10/830 PSU-E NB 16G WH	LED10
919406000611	RS181B A LED10/830 PSU-E WB 32G WH	LED10
919406000621	RS181B A LED20/830 PSU-E MB 24G WH	LED20
919406000631	RS181B A LED20/830 PSU-E NB 16G WH	LED20
919406000641	RS181B A LED20/830 PSU-E WB 32G WH	LED20
919406000651	ST181C A LED10/830 PSU-E MB 24G WH	LED10
919406000661	ST181C A LED10/830 PSU-E NB 16G WH	LED10
919406000671	ST181C A LED10/830 PSU-E WB 32G WH	LED10

Order Code	Full Product Name	Lamp family code
919406000681	ST181C A LED20/830 PSU-E MB 24G WH	LED20
919406000691	ST181C A LED20/830 PSU-E NB 16G WH	LED20
919406000701	ST181C A LED20/830 PSU-E WB 32G WH	LED20
919406000771	ST181T A LED10/830 PSU-E MB 24G 1C WH	LED10
919406000781	ST181T A LED10/830 PSU-E NB 16G 1C WH	LED10
919406000791	ST181T A LED10/830 PSU-E WB 32G 1C WH	LED10
919406000801	ST181T A LED20/830 PSU-E MB 24G 1C WH	LED20
919406000811	ST181T A LED20/830 PSU-E NB 16G 1C WH	LED20

