



ConTempo RVP150/250/350

ConTempo

The ConTempo floodlight has a registered design that blends well with contemporary outdoor environments. It has a rugged pressure die-casted aluminum housing with corrosion resistant powder coating. ConTempo also features an integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor. The unit has passed rigorous tests for dust and water ingress protection.

Benefits

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminium housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodised reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Features

- Blends well with contemporary outdoor environments
- Rugged pressure die-casted aluminum housing with corrosion resistant powder coating
- Integrated energy saving copper ballast, electronic semi-parallel ignitor and capacitor
- Custom-designed peened anodized reflector for efficient symmetric and asymmetric optics
- Hinged toughened glass cover for easy operation
- Rigorously tested for dust and water ingress protection
- Ergonomic installation and maintenance mechanisms

Application

- Functional: bays, outdoor storage areas, surveillance, parking areas, construction sites
- Recreational/sports: training fields, game courts, swimming pools
- Decorative: facades, edifices, billboards, gardens, patios, fountains, bridges, landscapes

Versions



RVP350/RVP250

General Information	
Country version	NO
Gear	CONV
Number of light sources	1
Mechanical and Housing	
Colour	-

General Information

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
911401056380	RVP250 MHN-TD70W K IC 240V-50Hz S SP	R7S	MHN-TD	70 W	Symmetrical
911401056480	RVP350 SON-T400W K IC 240V-50Hz S SP	E40	SON-T	400 W	Symmetrical
911401056580	RVP350 HPI-T250W K IC 240V-50Hz S SP	E40	HPI-TP	250 W	Symmetrical
911401056680	RVP350 HPI-T400W K IC 240V-50Hz S SP	E40	HPI-TP	400 W	Symmetrical
911401056780	RVP350 SON-T250W K IC 240V-50Hz A SP	E40	SON-T	250 W	Asymmetrical
911401056880	RVP350 SON-T400W K IC 240V-50Hz A SP	E40	SON-T	400 W	Asymmetrical
911401056980	RVP350 HPI-T250W K IC 240V-50Hz A SP	E40	HPI-TP	250 W	Asymmetrical

Order Code	Full Product Name	Cap-Base	Lamp family code	Lamp power	Optic type
911401057080	RVP350 HPI-T400W K IC 240V-50Hz A SP	E40	HPI-TP	400 W	Asymmetrical
911401057180	RVP250 MHN-TD150W K IC 240V-50Hz S SP	R7S	MHN-TD	150 W	Symmetrical
911401057280	RVP250 SON-T70W K IC 240V-50Hz S SP	E27	SON-T	70 W	Symmetrical
911401057380	RVP250 SON-T150W K IC 240V-50Hz S SP	E40	SON-T	150 W	Symmetrical
911401057580	RVP250 MHN-TD150W K IC 240V-50Hz A SP	R7S	MHN-TD	150 W	Asymmetrical
911401057780	RVP250 SON-T150W K IC 240V-50Hz A SP	E40	SON-T	150 W	Asymmetrical
911401057880	RVP350 SON-T250W K IC 240V-50Hz S SP	E40	SON-T	250 W	Symmetrical

