

Tempo – compact and consistent

Tempo 3 RVP351

Tempo is a complete floodlighting range offering a wide choice of lamp types and symmetrical and asymmetrical reflectors. It is designed for general-purpose floodlighting, and is particularly suited to small- to medium-scale area or surface lighting. The Tempo series' compact housing guarantees optimum visual integration. Anodized-aluminum reflectors ensure a highly efficient beam distribution, while the nylon bolt caps feature a goniometric aiming device for easy adjustment and alignment. A universal mounting bracket allows ceiling, wall or surface mounting with a wide range of adjustment for both down- and uplighting. Tempo's all-weather construction is designed to make cleaning and servicing easy and fast. Access to the lamp and gear is simple, via the hinged front glass with its quick-release stainless-steel clips. All Tempo luminaires are RoHS-compliant.

Benefits

- Complete floodlighting range with a wide choice of lamp types and symmetrical or asymmetrical reflectors for highly efficient beam distribution
- Ideal for a variety of outdoor applications from architectural, facade and billboard lighting to area and (leisure) sports lighting
- Optimal visual integration with compact housing and metallic grey finish

Features

- Wide choice of lamp types
- Symmetrical and asymmetrical reflectors
- Compact housing with metallic grey finish
- Aiming device
- Hinged front glass with quick-release clips

Tempo 3 RVP351

Application

- Facades
- Area lighting
- Architectural lighting
- Billboards

Specifications

Type	RVP351
Light source	HID: <ul style="list-style-type: none">- 1 x MASTER HPI-T Plus / E40 / 250, 400 W- 1 x SON-TPP / E40 / 250, 400 W
Lamp included	Yes (K)
Gear and compensation (integrated)	Electromagnetic (low loss), 230 or 240 V / 50 Hz: <ul style="list-style-type: none">- Parallel compensated (IC)
Optic	Asymmetrical (A) Symmetrical (S)
Materials and finishing	Housing: die-cast aluminum, corrosion-resistant powder coating Glass: thermally hardened, 4 mm thick Gasket: premium bonded silicone Mounting bracket: steel Aiming device cap: nylon Fixation clips: stainless steel Reflector: anodized, high-purity aluminum

Color	Grey, RAL 9007, powder-coated Color-matched bracket, grommet and hinges
Installation	Ceiling, wall or floor mounting Cable entry via M20 cable gland Ambient temperature outdoor: 35°C Drag factor (SCx): 0.203 m Max. adjustment from the horizontal: 175°
Maintenance	Hinged front glass with quick-release clips for in-position lamp replacement No internal cleaning required

Versions



Tempo 3 RVP351 area flood-lighting luminaire

Product details




Rear view



Protractor scale having degree intervals for easy adjustment and alignment

Tempo 3 RVP351

Product details



Integrated gear unit

Approval and Application

Mech. impact protection code IK07

Controls and Dimming

Dimmable No

General Information

CE mark CE mark
Light source colour 645 neutral white
Optical cover/lens type FG
ENEC mark -
Gear CONV
Glow-wire test 850/5
Lamp family code HPI-TP
Lamp power 250 W
Number of light sources 1

Initial Performance (IEC Compliant)

Init. Corr. Colour Temperature 4500 K
Init. Colour Rendering Index 65

Light Technical

Upward light output ratio 0

Mechanical and Housing

Colour Gray

General Information

Order Code	Full Product Name	Optic type
14970700	RVP351 HPI-TP250W K IC A	Asymmetrical
14971400	RVP351 HPI-TP250W K IC S	Symmetrical

