



Compact and robust

Tempo 4 RVP451

The Contempo projector has a highly innovative design. It is made of cast aluminum with a powder coating to ensure greater protection when used outdoors. It has a dedicated housing for auxiliary equipment (ballast, igniter, and capacitor), which is mounted on an aluminum chassis and ensures excellent heat dissipation.

Benefits

- Lightweight, compact
- Philips solution: lamp, ballast, and luminaire
- IP65: provides increased security for the installation and protects equipment within the luminaire
- Anodized aluminum reflector ensures excellent light distribution
- Tempered glass front
- Stainless-steel fixing clips
- Two beam options: greater flexibility for the designer

Features

- Seamless integration with the architecture of the site
- Extremely robust and resistant for outdoor use
- Equipped with lamp
- Available in symmetrical and asymmetrical versions
- Easy maintenance and access to parts

Application

- Functional: ports, storage areas, parking areas, construction sites
- Recreation / sports: training grounds, sports courts, swimming pools
- Decorative: facades, buildings, billboards, gardens, courtyards, fountains, bridges, landscapes

Specifications

Tempo 4 RVP451

Type	RVP451
Power supply	220 V
Frequency	60 Hz
Number of lamps	1 or 2

Power and lamp models	1 x SON-T / E40 /400, 600 W
	2 x SON-T / E40 /400, 600 W
	1 x SON-T / E40 /1000 W
	1 x HPI-T / E40 /1000 W

Versions



Tempo 4 RVP451 sports and area floodlighting luminaire

Product details



Opening suspended front cover provides access to lamp



Mains cable entrance and cable gland for HPI-T / SON-T lamp versions

Light Technical	
Upward light output ratio	0

General Information

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources	Optic type
919306015161	RVP451 HPI-TP1000W K A-NB	HPI-T	1000 W	-	Asymmetrical narrow beam
919306015171	RVP451 HPI-TP1000W K A-WB	HPI-T	1000 W	-	Asymmetrical wide beam
919306015181	RVP451 HPI-TP1000W K S-NB	HPI-T	1000 W	-	Symmetrical narrow beam
919306015191	RVP451 HPI-TP1000W K S-WB	HPI-T	1000 W	-	Symmetrical wide beam
919306015201	RVP451 SON-T1000W K A-NB	SON-T	1000 W	-	Asymmetrical narrow beam
919306015211	RVP451 SON-T1000W K A-WB	SON-T	1000 W	-	Asymmetrical wide beam

Order Code	Full Product Name	Lamp family code	Lamp power	Number of light sources	Optic type
919306015221	RVP451 SON-T1000W K S-NB	SON-T	1000 W	-	Symmetrical narrow beam
919306015231	RVP451 SON-T1000W K S-WB	SON-T	1000 W	-	Symmetrical wide beam
919306015241	RVP451 2xHPI-T400W K S-WB	HPI-T	400 W	2 pcs	Symmetrical wide beam
919306015251	RVP451 2xSON-T400W K S-WB	SON-T	400 W	2 pcs	Symmetrical wide beam
919306015261	RVP451 2xSON-T600W K S-WB	SON-T	600 W	2 pcs	Symmetrical wide beam

Tempo 4 RVP451

