



# Koffer<sup>2</sup> – economical system

## Koffer<sup>2</sup> SGP070

Koffer<sup>2</sup> is an archetypal modern road lighting luminaire which meets the needs of today's road users and operators. Total cost over lifetime was a key consideration in the development of Koffer<sup>2</sup>. The future-proof luminaire delivers outstanding optical performance, enabling optimum spacing and energy efficiency, and is easy to install and maintain. With its rectangular shape, Koffer<sup>2</sup> offers an alternative to rounded luminaires. It is available in three sizes – for mounting heights from 3.5 to 12 meters – and with dedicated masts and brackets, making it equally suitable for integration into modern urban environments or more traditional lighting designs. The Koffer<sup>2</sup> family accommodates CosmoPolis white-light technology and LED-enabled versions. Each Koffer<sup>2</sup> luminaire is fully recyclable; only the light source and driver have to be recycled separately.

### Benefits

- Meets the needs of today's road users and operators, with an archetypal modern road lighting luminaire
- Highly versatile design with rectangular luminaire in two sizes for integration into futuristic concepts or more traditional lighting designs
- Focus on optimum total cost over lifetime - sound construction and low maintenance costs plus high optical performance and energy-efficiency

### Features

- Warm-white Luxeon Rebel LEDs
- LifeLED<SUP>TM</SUP> module – re-LEDing upgrade possible
- Simplified components platform

### Application

- Residential areas
- Pavements and (cycle) paths

### Specifications

## Koffer<sup>2</sup> SGP070

<b>Type</b>	SGP070
<b>Light source</b>	HID: - 1 x MASTER CosmoWhite CPO-TW / PGZ12 / 45, 60, 90, 140 W - 1 x MASTER CityWhite CDO-TT / E27 / 70 W - 1 x CDO-ET / E27 / 70 W - 1 x MASTER SON-T PIA Plus / E27 / 50, 70 W - 1 x MASTER SON-T PIA Plus / E40 / 100 W - 1 x SON / E27 / 50, 70 W - 1 x SON / E40 / 100 W Compact fluorescent: - 2 x MASTER PL-L 4 Pin / 2G11 / 11 W - 1 x or 2 x MASTER PL-L 4 PIN / 2G11 / 18 W Induction lamp system: - 1 x MASTER QL system / 55 W
<b>Lamp included</b>	Yes (K or light color 827, 830 or 840) No
<b>Mains supply</b>	230 or 240 V
<b>Gear and compensation</b>	Electro magnetic (low loss), 230 or 240 V / 50 Hz: - Inductive (IN) Electronic, 220 - 240 V / 50 - 60 Hz: - Electronic (EB)


## Specifications

<b>Options</b>	Lighting controls: Chronosense (CH) Light regulation: - Dimming switch (SW) - Dimming switch with reverse function (SWR) - Dimming via SDU01S (D4) - Dimming via SDU11S (D5) - Dimming via external communication 1-10Vdc (D7) Photocell: NEMA socket (P1), Minicell (P3) Filter coil (F) included Fuse (FU) included Knife-connector (KC) included Pre-equipped cables without plug connector: - cable lengths of: 6 m (C6K), 10 m (C12K)
<b>Materials and finishing</b>	Housing: aluminum Optical covers: acrylic or polycarbonate bowls, UV-stabilized or hardened glass, min IK08

<b>Optic</b>	Open CT-POT (OR) "Opti-O" easy lamp access for CosmoPolis, CDO and SON lamps Cycle path optic (CYC). Only for GB and PC. At low mounting heights in narrow paths optimize for CosmoPolis low S-classes Reflector for railways (RW), for narrow platforms with maximum glare control
<b>Optical cover</b>	Glass bowl (GB) better spacing and better night preservation solution Glass bowl with DynaClean coating (GBD) on addition to GB the self-cleaning technology improve the maintenance factor Glass flat (FG), reduce glare and improve night nuisance Glass flat with DynaClean coating (FGD) Acrylic bowl, frosted (ACF) no yellowing Polycarbonate bowl, frosted (PCF) vandal-resistant
<b>Ignitor</b>	Semi-parallel, digital (SND) Series digital ignitor (SUD)

<b>Color</b>	Grey (RAL 7035) or white (RAL 9006) Other RAL colors available on request (e.g. 7024)
<b>Installation</b>	Side-entry mounting: lateral entry Ø 42 / 48 mm Post-top mounting: axial entry Ø 60 / 76 mm Spigot is integrated, continuously variable Recommended mounting height: 3.5 - 7 m Standard tilt angle post top: 10° Adjustable tilt angle: n/a Adjustable light distribution: 5 positions Max windage area: 0.08 m Max SCx values by side: 0.035 m
<b>Maintenance</b>	Toolless from below. Opening by one main clip
<b>Accessories</b>	Front and back louvers, ZGP070 L-FRONT resp L-BACK Dedicated mast and pole brackets available for different mounting possibilities
<b>Main applications</b>	Pedestrian and parking areas, bicycle paths

Dimensional drawing




Product	A
SGP070 CPO-TW60W K EB II GB	163 mm
SGP070 CPO-TW140W K EB II FG	133 mm
SGP070 CPO-TW140W K EB II GB	163 mm
SGP070 SON-T50/70W II RW FG	133 mm
SGP070 CPO-TW60W K EB II FG	133 mm


Product details




IP66 protection keeps luminaire clean on the inside and therefore minimizes maintenance



For post-top installations, 76 mm: The opening is fully open and the round, moon-shaped baffles are pivoted inside the luminaire.



Post-top installation, 60mm: The round baffle is pivoted inside the luminaire. The moon-shaped baffle closes the rest of the opening and the surface of the luminaire is totally flush.



Side-entry installation: Both baffles close the opening and the surface is totally flush.



Toolless opening of the luminaire



Quickly replace glass bowls

## Koffer<sup>2</sup> SGP070

### Product details



Quickly replace the gear tray



Replace lamps without tools



Koffer<sup>2</sup> SGP070, small version



Koffer<sup>2</sup> SGP100, large version

