



SGP268 Broadway

Broadway SGP268

A road lighting luminaire which embodies functionality and aesthetics, reflecting the aspirations of today modern cities. A step dimming option is available for SON-T 400W and SON 250W lamp versions.

Benefits

- High IP

Features


- Dedicated faceted optics to optimize beam control and maximise light output
- Adjustable optics
- Choice of different bowls: curved or flat glass
- High IP: lamp compartment IP66, dust-tight and jet-water proof
- Dimming option available for SON-T 250/400W lamp versions
- Maintenance from above in an ergonomic position

Application

- Major urban roads
- Expressways
- Motorways

Broadway SGP268

Versions



SGP268 SON

General Information

Optical cover/lens type	GB
Lamp family code	SON-T

General Information

Order Code	Full Product Name	Cap base	Country version	Gear	Lamp power	Number of light sources	Optic type
01962780	SGP268 SON-T150W 220V-50Hz GB SI	E40	NO	SGR	150 W	1	Open T-POT
01962880	SGP268 SON-T250W 220V-50Hz GB SI	E40	NO	SGR	250 W	1	Open T-POT
03364180	SGP268 SON-T400W 220V GB SI SD	E40	CN	SGR	400 W	1	Open T-POT
03364280	SGP268 SON-T250W 220V GB SI SD	E40	CN	SGR	250 W	1	Open T-POT
00329480	SGP268 SON-T250W 230V-50Hz GB SI	E40	NO	SGR	250 W	1	Open T-POT
00988780	SGP268 SON-T250W 220V-50Hz GB ALU	E40	NO	SGR	250 W	1	Open T-POT
00999080	SGP268 SON-T150W 240V-50Hz GB RAL7040	-	NO	CONV	150 W	1	-
00999180	SGP268 SON-T250W 240V-50Hz GB RAL7040	-	NO	CONV	250 W	1	-
00999280	SGP268 SON-T400W 240V-50Hz GB RAL7040	-	NO	CONV	400 W	1	-
00999380	SGP268 SON-T250W 220V-50Hz GB SD RAL7040	-	NO	-	250 W	-	-
00999480	SGP268 SON-T400W 220V-50Hz GB SD RAL7040	-	NO	-	400 W	-	-

Light Technical

Order Code	Full Product Name	Light output ratio	Order Code	Full Product Name	Light output ratio
01962780	SGP268 SON-T150W 220V-50Hz GB SI	0.93	00999080	SGP268 SON-T150W 240V-50Hz GB RAL7040	-
01962880	SGP268 SON-T250W 220V-50Hz GB SI	0.84	00999180	SGP268 SON-T250W 240V-50Hz GB RAL7040	-
03364180	SGP268 SON-T400W 220V GB SI SD	-	00999280	SGP268 SON-T400W 240V-50Hz GB RAL7040	-
03364280	SGP268 SON-T250W 220V GB SI SD	-	00999380	SGP268 SON-T250W 220V-50Hz GB SD RAL7040	-
00329480	SGP268 SON-T250W 230V-50Hz GB SI	0.93	00999480	SGP268 SON-T400W 220V-50Hz GB SD RAL7040	-
00988780	SGP268 SON-T250W 220V-50Hz GB ALU	-			

Mechanical and Housing

Order Code	Full Product Name	Colour	Order Code	Full Product Name	Colour
01962780	SGP268 SON-T150W 220V-50Hz GB SI	Silver	00988780	SGP268 SON-T250W 220V-50Hz GB ALU	Aluminum
01962880	SGP268 SON-T250W 220V-50Hz GB SI	Silver	00999080	SGP268 SON-T150W 240V-50Hz GB RAL7040	-
03364180	SGP268 SON-T400W 220V GB SI SD	Silver	00999180	SGP268 SON-T250W 240V-50Hz GB RAL7040	-
03364280	SGP268 SON-T250W 220V GB SI SD	Silver	00999280	SGP268 SON-T400W 240V-50Hz GB RAL7040	-
00329480	SGP268 SON-T250W 230V-50Hz GB SI	Silver	00999380	SGP268 SON-T250W 220V-50Hz GB SD RAL7040	-

Broadway SGP268

Order Code	Full Product Name	Colour
00999480	SGP268 SON-T400W 220V-50Hz GB SD RAL7040	-

