



SGP338 Velocity

Velocity

Road lighting luminaire for tubular high-pressure sodium lamps up to 400W. Step dimming option available up to SON-T 250W lamp version.

Benefits

- Step dimming option available up to SON-T 250W lamp version

Features

- High quality optical system for clear tubular lamps
- Adjustable lamp position to obtain several light distributions
- Dustproof and jetproof (IP66) lamp compartment: no internal cleaning required
- Easy access and maintenance of gear and lamp

Application

- Motorways
- Major roads
- Expressways

Versions

