



A touch of elegance for cities

GullWing

Designed to offer better energy efficiency, the GullWing outdoor luminaire incorporates electronic ballasts and medium-power lamps (210 and 315 W) from the Color Master family. Its design allows seamless integration with the city, contributing to the beautification of urban spaces.

Benefits

- Lightweight, compact
- Philips solution: lamp, electronic ballast, and luminaire
- Several beam apertures for different needs
- High-gloss anodized aluminum reflector ensures excellent light distribution
- Tempered glass front
- Available in different colors (brass, white, black, aluminum, etc.)
- Several mounting options

Features

- The product is designed to have as little impact as possible on the existing architecture
- Very robust luminaire with IP66 for both the optics compartment and the ballast housing
- Easy maintenance - no tools required for interior access
- Reflector designed with the latest technology to make maximum use of light
- System with excellent CRI (Color Rendering Index) and long life expectancy

Application

- Residential streets
- Avenues
- Roads
- Industrial yards
- Parking lots
- Traffic circles

Specifications

Type	SRS618	Frequency	60 Hz
Power supply	220 V	Power and lamp models	1 x CDM Elite / PGZ19 / 315 W

Versions



Product details

