



SRX509

SRX509

Underpass luminaire suitable for use with SON-T 150W, 250W, 400W high pressure sodium vapour lamps..

Benefits

- Removable gear tray for easy repair and maintenance

Features

- Reflector is made of high purity anodised aluminium to give a wide beam and maximum optical efficiency
- Removable gear tray for easy repair and maintenance
- Socket plug terminal for easy and fast lamp connection
- Gear unit uses Philips standard basic ballast
- Ambient temperature of max 45°C

Application

- Toll gate station.
- Underpass.
- Basement parking areas.

SRX509

Versions



SRX509 SON 220V

General Information	
Cap-Base	E40
Gear	SON gear
Lamp family code	SON-T
Number of light sources	1
Optic type	Symmetrical

General Information

Order Code	Full Product Name	Lamp power	Order Code	Full Product Name	Lamp power
910401602280	SRX509 SON-T150W 220V-50Hz S	150 W	910401602380	SRX509 SON-T250W 220V-50Hz S	250 W

