



Product Description

Ecoclick Starters

Range of premium-quality glow switch starters for igniting fluorescent lamps with electromagnetic ballast.

Benefits

- The only starter that offers fast, easy installation with no need to use any extra tools
- No irritation – even firmly stuck starters can be removed easily
- Eco-friendly, recyclable concept (free of lead and radioactivity)
- More than 25% longer lamp life; lower maintenance costs compared with lower-quality, non-IEC-compliant starters
- Optimal connectivity through brass components and oxidation-resistant brass pins
- Flame-retardant components and UV-resistant canister for additional safety and secure ignition (validated by Underwriters Laboratories UL)

Features


- Redesigned canister top with 2 installation notches into which the pins of another starter fit perfectly (patented innovation)
- Radioactive-free (patented) and lead-free (RoHS-compliant)
- Premium reliability with 10,000 safe switches
- 2-pin igniter in plastic (flame-retardant polycarbonate) canister with high-quality radio-interference suppression capacitor
- Well-defined preheat and peak voltage ensure proper ignition

Ecoclick Starters

Application

- Ignite fluorescent lamps of all brands with conventional electromagnetic ballast using TL-D (T8), TL (T12), TL mini and PL-L lamps
- S2 Ecoclick starters are suitable for:
 - 110/130V, 4-22W single applications
 - 220/240V, 4-6-8-15-18-22W single applications
 - 220/240V, 4-22W series applications
- S10 Ecoclick starters are suitable for 220/240V, 4-65W single applications
- S10 Ecoclick starter is required for 220/240V, 13W single application
- S2 Ecoclick starter is recommended for 220/240V, 18W single application for optimum performance

Dimensional drawing



| Product | C (max) | E (max) |
|----------------------------------------|---------|---------|
| S10 4-65W SIN 220-240V WH EUR/1000 | 40.3 mm | 21.5 mm |
| S10 4-65W SIN 220-240V WH EUR/20X10CT | 40.3 mm | 21.5 mm |
| S16 70-125W 240V UNP/20X10CT | 40.3 mm | 21.5 mm |
| S2 4-22W SER 220-240V WH EUR BOX/20X10 | 40.3 mm | 21.5 mm |
| S2 4-22W SER 220-240V WH EUR/1000 | 40.3 mm | 21.5 mm |

Product details



S16 70-125 W, WH

Mechanical and Housing

| | |
|----------------|-------|
| Housing Colour | White |
|----------------|-------|

Operating and Electrical

| Order Code | Full Product Name | Voltage (nom.) | Power Consumption |
|------------|---------------------------------------|----------------|-------------------|
| 69769128 | S10 4-65W SIN 220-240V WH EUR/1000 | 220-240 V | 4 W |
| 69769131 | S10 4-65W SIN 220-240V WH EUR/20X10CT | 220-240 V | 4 W |
| 69750928 | S2 4-22W SER 220-240V WH EUR/1000 | 220-240 V | 22 W |

| Order Code | Full Product Name | Voltage (nom.) | Power Consumption |
|------------|----------------------------------------|----------------|-------------------|
| 69750931 | S2 4-22W SER 220-240V WH EUR BOX/20X10 | 220-240 V | 22 W |
| 90356331 | S16 70-125W 240V UNP/20X10CT | 240 V | 125 W |

