



SlimLine – Extensive functionality

SlimLine TBS020

SlimLine luminaires are compact and versatile for better distribution of light in the environment. Their slim design offers lots of advantages to designers and installers, with better adaptation to ceilings. Available in recessed (TBS020) and surface-mounted (TCS020) models with a choice of four optical systems. Ideal for 16 and 32 W TL-D tubular fluorescent lamps.

Benefits

- Extensive functionality in recessed and surface-mounted luminaires
- The best choice for high-performance luminaires with four optic options
- Slim design that integrates with the architecture
- Easy installation and maintenance

Features

- Perfect light distribution that enhances your project
- Slim design

Application

- Offices
- Shops
- Banks
- Schools
- Hotels

Specifications

Type	TBS020
Light source	2 x 16 W / 2 x 32 W / 2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W TL-D / TL5

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
	Electronic Touch&Dim DALI (HFD)
Optical cover	Textured transparent acrylic diffuser - diffuse light (AC)

SlimLine TBS020

Materials and finishing	Phosphated steel-plate body of 0.5 mm thickness in white color	High-purity aluminum optics. Parabolic wings in high-gloss aluminum (C5) or flat aluminum wings in white color (C1)
Installation	For plaster modules: 615 x 165 mm or 1230 x 165 mm	

Versions



General Information	
Gear	EB
Number of light sources	2 pcs

General Information

Order Code	Full Product Name	Optical cover/lens type	Lamp family code	Lamp power	Optic type
820619256139	TBS020 A 2XTLD16W/840 EB C5	-	TL-D	16 W	High-gloss optic double parabolic
919106026501	TBS020 2xTL- D32W/840 EB C1	-	TL-D	32 W	High-gloss mirror flat lamellae louver
919106026521	TBS020 2xTL-D32/840 EB C5	-	TL-D	32 W	High-gloss optic double parabolic
919106031321	TBS020 2XTL5-28W/840 EB C5	-	TL5	28 W	High-gloss optic double parabolic
919106026481	TBS020 2XTL- D32W/840 EB R-H	-	TL-D	32 W	Reflector high reflectance
919106027709	TBS020 2xTL5-28W/840 EB R- H	-	TL5	28 W	Reflector high reflectance

Order Code	Full Product Name	Optical cover/lens type	Lamp family code	Lamp power	Optic type
919106031711	TBS020 2XTL5-50W/840 EB R- H	-	TL5	50 W	Reflector high reflectance
919106026581	TBS020 2xTL- D32W/840 EB AC	Acrylic bowl/cover	TL-D	32 W	-
919106030431	TBS020 2XTL5-28W/840 EB AC	Acrylic bowl/cover	TL5	28 W	-
919106032781	TBS020 2XTL5-25W/840 EB AC	Acrylic bowl/cover	TL5	25 W	-

