



SmartForm – the new standard for office lighting with slender recessed luminaires

SmartForm TBS415

Reflecting Philips' drive for simplicity and sustainability, SmartForm recessed is a complete family of highly versatile modular and semi-modular luminaires. These luminaires are available with a choice of LED or MASTER TL5 light sources in very small, slender versions. Designed to fit in a wide range of ceiling types, this complete family can fulfill the majority of project requirements in most applications. Energy efficiency As well as incorporating energy-efficient light sources and electronic ballasts, the SmartForm recessed family can be equipped with lighting controls. These include solutions for presence detection and daylight regulation (ActiLume) or daylight regulation only (Luxsense), thereby further reducing energy consumption (W/m^2 is very low). In this way, this Green Flagship range lowers overall cost of ownership as well as CO₂ levels, making SmartForm an environmentally friendly choice. SmartForm recessed TBS415 – 'light beam' semi-modular – 600 mm module SmartForm recessed luminaires are designed for integration in linear ceiling systems with a width of 148 mm (half module 300 mm) for exposed and concealed T-bar and the extended versions for bandrastrer ceilings. 'Light surface' TBS415 1-lamp MLO and asymmetrical optic in 1/2 modular concept, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 1-lamp: micro-optics in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm. 'Light beam' TBS415 2-lamps Mini-optics, 2-lamps in 1/2 modular concept with AIR function, width 148 mm. Modular length 600, 900, 1200 and 1500 mm. To extend till 2400 mm.

Οφέλη

- Slender, recessed 'light surface' luminaires with MLO Micro Lens Optics or 'light beam' luminaires with micro- or mini-optics for unobtrusive ceiling integration
- Complete family of linear luminaires designed to fit a wide range of ceiling types
- Available with either 1 or 2 TL5 lamps for excellent, energy-efficient office lighting solutions


Χαρακτηριστικά

- Δυνατότητα επιλογής πηγών φωτός LED ή MASTER TL5
- Οπτικά συστήματα MLO
- Ηλεκτρονικό μπάλαστ
- Μπορεί να εξοπλιστεί με συστήματα ελέγχου φωτισμού για ανίχνευση παρουσίας και ρύθμιση φωτός σύμφωνα με το φυσικό φως της ημέρας (ActiLume) ή μόνο ρύθμιση φωτός σύμφωνα με το φυσικό φως της ημέρας (Luxsense)


Εφαρμογή

- Γραφεία
- Κλάδος εκπαίδευσης
- Κλάδος υγείας
- Ψυχαγωγία
- Καταστήματα
- Βιομηχανία

Versions



Λεπτομέρειες για το προϊόν



IPDP_TBS415i_0039-Detail photo



