

# Pentura Mini – ultra-slim decorative batten

## Pentura Mini

Pentura Mini TCH128 is an ultra-slim decorative batten for domestic applications. A cost-effective, ready-to-install mini fluorescent solution. Pentura Mini TCH128 offers the energy-saving benefits of miniature fluorescent lamp technology coupled with lightweight electronics and a patented internal reflector for improved lighting performance. The batten is easy to install e.g. over worktops and workstations in the home, home office and recreational environments, etc. it provides bright light where needed even where installation space is limited. Pentura Mini TCH128 battens are fitted with lamp, tough polycarbonate diffuser and all fixing accessories, reducing installation time to a minimum. The battens are through-wired with removeable end-caps at both ends covering the push-button connection blocks for simple connection and through-wiring.

### Benefits

- Ultra-slim decorative batten providing a cost-effective, ready-to-install mini fluorescent solution for domestic use
- The energy-saving benefits of miniature fluorescent lamp technology with lightweight electronics and a patented internal reflector for improved lighting performance
- Easy to install to provide bright light where needed, even if installation space is limited

### Features

- Miniature fluorescent lamp technology
- Patented internal reflector
- Polycarbonate diffuser
- Push-button connection blocks

### Application

- Home lighting
- Undershelf lighting
- Task lighting

### Specifications

Pentura Mini


Type	TCH128
Light source	Fluorescent: - 1 x TL5-Essential / G5 /8, 14, 21, 28 W - 1 x MASTER TL5 / G5 / 35 W
Lamp included	Yes (lamp color 830 or 840, 8 W version is 827) No (35 W version only)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency (HF)

Material	Housing and end caps: polycarbonate, white Cover: polycarbonate, transparent
Installation	Individual or in-line; screw mounting
Remarks	All installation accessories included; ready to install
Main applications	Home, undershelf, task lighting

Versions



Dimensional drawing



Product	A
TCH128 1xTL5-35W HF	1523 mm
TCH128 1xTL5-28W/830 HF	1223 mm
TCH128 1xTL5-28W/840 HF	1223 mm
TCH128 1xTL5-14W/840 HF	623 mm
TCH128 1xTL5-21W/840 HF	923 mm
TCH128 1xTL5-14W/830 HF	623 mm
TCH128 1xTL5-21W/830 HF	923 mm

Product details



All installation accessories are included

Individual battens can be connected to form lines of light



# Pentura Mini

## Product details

Ultra-slim batten



### Approval and Application

Ingress protection code IP20

### Operating and Electrical

Input Voltage 220 to 240 V

### General Information

CE mark CE mark

Protection class IEC Safety class II

Flammability mark For mounting on normally flammable surfaces

Gear HF

Glow-wire test Temperature 850 °C, duration 5 s

Lamp family code TL5

Number of light sources 1 pc

### General Information

Order Code	Full Product Name	Kombipack	Lamp power
910502537318	TCH128 1xTL5-14W/840 HF	Lamp(s) included	14 W
910502537418	TCH128 1xTL5-14W/830 HF	Lamp(s) included	14 W
910502537518	TCH128 1xTL5-21W/840 HF	Lamp(s) included	21 W
910502537618	TCH128 1xTL5-21W/830 HF	Lamp(s) included	21 W
910502537718	TCH128 1xTL5-28W/840 HF	Lamp(s) included	28 W
910502537818	TCH128 1xTL5-28W/830 HF	Lamp(s) included	28 W
910503609918	TCH128 1xTL5-35W HF	-	35 W

