



# TCS027 – Functional and convenient

## TCS027

The TCS027 luminaires have a compact design for use in areas that require diffuse light in large quantities. The surface-mounted models are designed for use with 32 W TL-D tubular fluorescent lamps and are easy to install and maintain. Also available for recessed mounting (TBS027).

### Benefits

- Functional and convenient for easy application and quality of light
- Easy installation and maintenance

### Features

- High-gloss aluminum reflectors
- Perfect light distribution that enhances your project
- Ideal luminaire for projects that require high-level lighting

### Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

### Specifications

Type	TCS027
Light source	2 x 32 W TL-D
Mains voltage	Electronic 220 V / 60-50 Hz: (EB)

Materials and finishing	Phosphated steel body in white color
	High-purity aluminum optics
Installation	Surface-mounted TCS027

## TCS027

### Versions



#### General Information

Lamp family code	TL-D
Lamp power	32 W
Number of light sources	2 pcs
Optic type	Reflector high reflectance

### Operating and Electrical

Order Code	Full Product Name	Input Voltage
919106050121	TCS027 2XTL-D32W/840 EI 110/220V R-H	110 to 220 V

Order Code	Full Product Name	Input Voltage
919106050131	TCS027 2XTL-D32W/840 EB R-H	-

### General Information

Order Code	Full Product Name	Gear
919106050121	TCS027 2XTL-D32W/840 EI 110/220V R-H	EI

Order Code	Full Product Name	Gear
919106050131	TCS027 2XTL-D32W/840 EB R-H	EB

