



TCS065 – Extensive functionality

TCS065

The TCS065 luminaires have been specially developed for indoor commercial lighting. They are available in recessed (TBS06) and surface-mounted (TCS065) models. This is an economical range for use with tubular fluorescent lamps of 16, 20, 32 or 40 W. The TCS has a C4 optical system that guarantees high-quality projects, energy savings, excellent lighting efficiency, and easy installation.

Benefits

- Functional and convenient for easy application and quality of light
- C4 optic that provides good-quality lighting
- Easy installation and maintenance

Features

- High-gloss aluminum reflectors
- Perfect light distribution that enhances your project

Application

- Offices
- Buildings
- Schools
- Universities
- Libraries
- Shops
- Hospitals

Specifications

Type	TCS065
Light source	4 x 16 W / 2 x3 2 W TL-D

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
---------------	-----------------------------------

TCS065

Materials and finishing	Phosphated steel body of 0.5 mm thickness in white color
	High-purity aluminum optics

Installation	Parabolic wings in high-gloss aluminum (C4)
	Surface-mounted TCS065 on slabs
	For plaster modules

Versions



General Information	
Gear	EB
Lamp family code	TL-D
Optic type	High-gloss optic with V-shaped cross-lamellae

General Information

Order Code	Full Product Name	Lamp power	Number of light sources
919106032331	TCS065 2XTL-D32W/840 EB C4	32 W	2 pcs

Order Code	Full Product Name	Lamp power	Number of light sources
919106032351	TCS065 4XTL-D16W/840 EB C4	16 W	4 pcs

