



EFix – for a greener office

EFix TCS260

The EFix TL5 luminaire range is a dedicated, affordable choice of innovative lighting that enables massive energy savings to be made when old electromagnetic installations are replaced by the latest Philips technology. The range's optical performance complies with the latest EN-12464 norms, ensuring improved lighting quality in every application. Used in combination with high-frequency gear, Philips MASTER TL5 lamps enable substantial energy savings to be made. These savings can be further increased by using a Luxsense daylight controller integrated into the luminaire. The practical design of EFix combines both surface-mounted (TCS260) and suspended (TPS262) luminaires in one design. Thanks to the luminaire's easily removable top cover, the beam can be adjusted to provide direct or direct/indirect lighting. EFix is supplied with lamps and is ready to install, minimizing installation time. EFix recessed TBS260 completes Philips' range of luminaires for general lighting applications in offices and shops.

Benefits

- In its segment the easiest product to install
- Dedicated TL5 luminaire design, which is appealing because of its simplicity
- Office compliant luminaire using the mini optics

Features

- Simple design
- MASTER TL5 lamps; suitable for use with high-frequency gear
- Mini optics; performance compliant with EN-12464 norms
- Integrated Luxsense daylight controller available
- Easily removable top cover: allows beam adjustment to provide direct or direct/indirect lighting

EFix TCS260

Application

- Offices
- Shops


Specifications

Type	TCS260	Connection	Push-in connector, from outside
Light source	Fluorescent: - 1 x or 2 x MASTER TL5 / G5 / 28, 35, 49, 54, 80 W	Color	White, RAL 9016 (WH) Silver, RAL 9006 (SI)
Lamp included	Yes (lamp color 830 or 840)	Option	Lighting controls: - Luxsense daylight controller (LX) - Actilume multi controller (ACL)
Gear	Electronic, 220 - 240 V / 50 - 60 Hz: - High Frequency Performer Intelligent (HFPI) - High Frequency Performer (HFP) - High Frequency Regulator (HFR)	Material	Housing: pre-lacquered steel Optic: pre-lacquered steel or aluminum End cap: polycarbonate
Optic	High-gloss optic, double parabolic, closed (C6) Semi-high-gloss optic, double parabolic (D6) Matt optic, double parabolic louvers, closed (M6) Matt mirror, ribbed cross louvers (M2) Asymmetrical mirror (A) Prismatic/opal curved polycarbonate cover in matt high-quality aluminum optic (OD)	Installation	Individual or in line; clicking the luminaire into pre-screwed ceiling brackets
		Accessory	Suspension set delivered with electrical cable, ZCS260 SME WH or SI
		Remarks	Delivered with lamps, push-in connector and ceiling brackets

Versions



EFix TCS260 surface-mounted luminaire with OLC semi-high-gloss aluminum optic with 3D lamellae (D6)



EFix TCS260 surface-mounted luminaire with OLC semi-high-gloss aluminum optic with 3D lamellae (D6)



EFix TCS260 surface-mounted luminaire with matt aluminum optic with profiled lamellae (M2)



EFix TCS260 surface-mounted luminaire with matt aluminum optic with profiled lamellae (M2)

Versions



EFix TCS260 surface-mounted luminaire with OLC semi-high-gloss aluminum optic with 3D lamellae (D6)



EFix TCS260 surface-mounted luminaire with OLC high-gloss aluminum optic with 3D lamellae (C6)




EFix TCS260 surface-mounted luminaire with OLC matt aluminum optic with 3D lamellae (M6)



EFix TCS260 surface-mounted luminaire with OLC high-gloss aluminum optic with 3D lamellae (C6)



EFix TCS260 surface-mounted luminaire with OLC matt aluminum optic with 3D lamellae (M6)



EFix TCS260 surface-mounted luminaire with matt aluminum optic with profiled lamellae (M2)



EFix TCS260 surface-mounted luminaire with OLC high-gloss aluminum optic with 3D lamellae (C6)




EFix TCS260 surface-mounted luminaire with OLC high-gloss aluminum optic with 3D lamellae (C6)


Versions



EFix TCS260 surface-mounted luminaire with OLC semi-high-gloss aluminum optic with 3D lamellae (D6)



EFix TCS260 surface-mounted luminaire with matt aluminum optic with profiled lamellae (M2)




EFix TCS260 surface-mounted luminaire with OLC matt aluminum optic with 3D lamellae (M6)



EFix TCS260 surface-mounted luminaire with OLC matt aluminum optic with 3D lamellae (M6)

Dimensional drawing



Product	A	B	C
TCS260 1x28W/830 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/830 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/830 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x35W/830 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS D6 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFD-T D6 ACL PVCFR WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFD-T D6 ACL PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFD-T D6 ACL SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFD D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFR M2 LX WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFD-T D6 ACL PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFD D6 PVCFR WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFD D6 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFD D6 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFS M2 PVCFR WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFS M2 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS M2 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFS D6 PVCFR WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFS D6 PVCFR WH	1300 mm	650 mm	1541 mm
TCS260 1x28/54W HFPI M2 SI			
TCS260 1x35-80W HFPI C6 SI			
TCS260 1x35-80W HFPI D6 SI			
TCS260 1x35-80W HFPI M2 SI			
TCS260 2x28/54W HFPI C6 SI			
TCS260 2x28/54W HFPI D6 SI			
TCS260 2x28/54W HFPI M2 SI			
TCS260 2x35-80W HFPI C6 SI			
TCS260 2x35-80W HFPI D6 SI			
TCS260 2x35-80W HFPI M2 SI			
TCS260 2x35W/830 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFD-T D6 ACL SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFD-T D6 ACL WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFD D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/830 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFD D6 WH	1300 mm	650 mm	1541 mm

Dimensional drawing

Product	A	B	C
TCS260 2x49W/840 HFD D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFD D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFD D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x28W/830 HFD-T D6 ACL WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/830 HFD D6 WH	1000 mm	500 mm	1241 mm
TCS260 1x49W/830 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 1x54W/830 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 1x54W/830 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 1x54W/830 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x80W/830 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 1x80W/830 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFS M6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/830 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/830 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/830 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x54W/830 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/830 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/830 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/830 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x28W/830 HFS M2 SI	1000 mm	500 mm	1241 mm
TCS260 1x35W/830 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 1x54W/830 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x80W/830 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x80W/830 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFS M2 SI	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/830 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/830 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 2x54W/830 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 2x54W/830 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 2x54W/830 HFS M6 SI	1000 mm	500 mm	1241 mm
TCS260 1x28W/840 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/840 HFS D6 WH	1000 mm	500 mm	1241 mm

EFix TCS260

Product	A	B	C
TCS260 1x28W/840 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x35W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 1x54W/840 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 1x54W/840 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 1x54W/840 HFS M6 WH	1000 mm	500 mm	1241 mm
TCS260 1x54W/840 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x80W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/840 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS M6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS M6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x54W/840 HFS C6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS M6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS M2 WH	1000 mm	500 mm	1241 mm
TCS260 1x28W/840 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 1x28W/840 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x28W/840 HFS M6 SI	1000 mm	500 mm	1241 mm
TCS260 1x35W/840 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x35W/840 HFS M6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFS M6 SI	1300 mm	650 mm	1541 mm
TCS260 1x54W/840 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 1x54W/840 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x54W/840 HFS M6 SI	1000 mm	500 mm	1241 mm
TCS260 1x80W/840 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 1x80W/840 HFS M6 SI	1300 mm	650 mm	1541 mm
TCS260 2x28W/840 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS M6 SI	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFS M2 SI	1000 mm	500 mm	1241 mm
TCS260 2x35W/840 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS M6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS C6 SI	1300 mm	650 mm	1541 mm

EFix TCS260

Product	A	B	C
TCS260 2x49W/840 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS M6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 2x54W/840 HFS C6 SI	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS D6 SI	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS M6 SI	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFS M2 SI	1000 mm	500 mm	1241 mm
TCS260 2x80W/840 HFS C6 WH	1300 mm	650 mm	1541 mm
TCS260 2x80W/840 HFS D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x80W/840 HFS M2 WH	1300 mm	650 mm	1541 mm
TCS260 2x80W/840 HFS C6 SI	1300 mm	650 mm	1541 mm
TCS260 2x80W/840 HFS D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x80W/840 HFS M2 SI	1300 mm	650 mm	1541 mm
TCS260 1x54W/840 HFR C6 WH	1000 mm	500 mm	1241 mm
TCS260 2x49W/840 HFR C6 WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFR D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFR D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x28W/830 HFR D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x49W/830 HFR D6 SI	1300 mm	650 mm	1541 mm
TCS260 1x28W/840 HFR D6 WH	1000 mm	500 mm	1241 mm
TCS260 1x49W/840 HFR D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x54W/840 HFR D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFR D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/840 HFR D6 WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFR D6 WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/840 HFR D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFR D6 SI	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFR C6 LX WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFR C6 LX WH	1300 mm	650 mm	1541 mm
TCS260 1x28W/830 HFR D6 LX WH	1000 mm	500 mm	1241 mm
TCS260 1x35W/830 HFR D6 LX WH	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFR D6 LX WH	1300 mm	650 mm	1541 mm
TCS260 1x35W/830 HFR D6 LX SI	1300 mm	650 mm	1541 mm
TCS260 1x49W/830 HFR D6 LX SI	1300 mm	650 mm	1541 mm
TCS260 1x28W/840 HFR D6 LX WH	1000 mm	500 mm	1241 mm
TCS260 1x49W/840 HFR D6 LX WH	1300 mm	650 mm	1541 mm
TCS260 1x54W/840 HFR D6 LX WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/840 HFR D6 LX WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/840 HFR D6 LX WH	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFR D6 LX WH	1300 mm	650 mm	1541 mm
TCS260 2x35W/840 HFR D6 LX SI	1300 mm	650 mm	1541 mm
TCS260 2x49W/840 HFR D6 LX SI	1300 mm	650 mm	1541 mm
TCS260 1x28W/830 HFR M2 WH	1000 mm	500 mm	1241 mm
TCS260 2x28W/830 HFR M2 WH	1000 mm	500 mm	1241 mm
TCS260 2x35W/830 HFR M6 WH	1300 mm	650 mm	1541 mm
TCS260 2x28W/830 HFR M6 LX WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFR D6 WH	1000 mm	500 mm	1241 mm
TCS260 2x54W/840 HFR D6 SI	1000 mm	500 mm	1241 mm
TCS260 1x28/54W HFPI C6 WH			
TCS260 1x28/54W HFPI D6 WH			
TCS260 1x28/54W HFPI M2 WH			
TCS260 1x35-80W HFPI C6 WH			

EFix TCS260

Product	A	B	C
TCS260 1x35-80W HFPI D6 WH			
TCS260 1x35-80W HFPI M2 WH			
TCS260 2x28/54W HFPI C6 WH			
TCS260 2x28/54W HFPI D6 WH			
TCS260 2x28/54W HFPI M2 WH			
TCS260 2x35-80W HFPI C6 WH			
TCS260 2x35-80W HFPI D6 WH			
TCS260 2x35-80W HFPI M2 WH			
TCS260 1x28/54W HFPI C6 SI			
TCS260 1x28/54W HFPI D6 SI			

Product details



IPDP_TCS260i_0005-Detail
photo



IPDP_TCS260i_0009-Detail
photo



EFix TCS260

Product details




IPDP_TCS260i_0017-Detail photo



IPDP_TCS260i_0023-Detail photo

IPDP_TCS260i_0025-Detail photo



IPDP_TCS260i_0029-Detail photo



Product details



Accessories




Suspension set with electrical cable, 3 or 5 pole

Ordercode 910925225011, 910925225411



Suspension set with electrical cable, 3 or 5 pole

Ordercode 910925225111, 910925225511



Suspension set twin, 1500 mm

Ordercode 910925225211



Suspension set twin, 1500 mm

Ordercode 910925229811

Application conditions	
Suitable for random switching	Not applicable
Approval and application	
Ingress protection code	IP20
Operating and electrical	
Input Voltage	220 to 240 V
General information	
CE mark	CE mark
Protection class IEC	Safety class I
Optical cover/lens type	-
Emergency lighting	-
Flammability mark	For mounting on normally flammable surfaces
Lamp family code	TL5
Product Family Code	TCS260

General information (1/2)

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Embedded control
910402287012	TCS260 1x35W/840 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	35 W	ActiLume
910402287212	TCS260 1x35W/830 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	35 W	ActiLume
910402287412	TCS260 1x49W/840 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	49 W	ActiLume
910402287612	TCS260 1x49W/830 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	49 W	ActiLume
910402287812	TCS260 1x35W/840 HFD D6 WH	HFD	Lamp(s) included	35 W	-
910402288012	TCS260 1x35W/830 HFD D6 WH	HFD	Lamp(s) included	35 W	-
910402288212	TCS260 1x49W/840 HFD D6 WH	HFD	Lamp(s) included	49 W	-
910402288412	TCS260 1x49W/830 HFD D6 WH	HFD	Lamp(s) included	49 W	-
910402374112	TCS260 1x28W/830 HFS D6 WH	HFS	Lamp(s) included	28 W	-
910402374612	TCS260 1x35W/830 HFS D6 WH	HFS	Lamp(s) included	35 W	-
910402375112	TCS260 1x49W/830 HFS D6 WH	HFS	Lamp(s) included	49 W	-
910402375612	TCS260 1x54W/830 HFS D6 WH	HFS	Lamp(s) included	54 W	-
910402382312	TCS260 1x28W/840 HFS D6 WH	HFS	Lamp(s) included	28 W	-
910402382812	TCS260 1x35W/840 HFS D6 WH	HFS	Lamp(s) included	35 W	-
910402383312	TCS260 1x49W/840 HFS D6 WH	HFS	Lamp(s) included	49 W	-
910402383812	TCS260 1x54W/840 HFS D6 WH	HFS	Lamp(s) included	54 W	-
910402393612	TCS260 1x35W/830 HFR D6 WH	HFR	Lamp(s) included	35 W	-
910402393712	TCS260 1x49W/830 HFR D6 WH	HFR	Lamp(s) included	49 W	-
910402394912	TCS260 1x28W/840 HFR D6 WH	HFR	Lamp(s) included	28 W	-
910402395112	TCS260 1x49W/840 HFR D6 WH	HFR	Lamp(s) included	49 W	-
910402395212	TCS260 1x54W/840 HFR D6 WH	HFR	Lamp(s) included	54 W	-
910402399112	TCS260 1x28W/830 HFR D6 LX WH	HFR	Lamp(s) included	28 W	Luxsense
910402399212	TCS260 1x35W/830 HFR D6 LX WH	HFR	Lamp(s) included	35 W	Luxsense
910402399312	TCS260 1x49W/830 HFR D6 LX WH	HFR	Lamp(s) included	49 W	Luxsense
910402447512	TCS260 1x28W/840 HFR D6 LX WH	HFR	Lamp(s) included	28 W	Luxsense
910402447812	TCS260 1x49W/840 HFR D6 LX WH	HFR	Lamp(s) included	49 W	Luxsense
910402447912	TCS260 1x54W/840 HFR D6 LX WH	HFR	Lamp(s) included	54 W	Luxsense
910402461112	TCS260 1x28/54W HFPI D6 WH	HFPI	-	28, 54 W	-
910402461412	TCS260 1x35-80W HFPI D6 WH	HFPI	-	35, 49, 80 W	-
910925516612	TCS260 1x28W/830 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	28 W	ActiLume
910925516712	TCS260 1x28W/830 HFD D6 WH	HFD	Lamp(s) included	28 W	-
910402287512	TCS260 1x49W/840 HFD-T D6 ACL SI	HFD-T	Lamp(s) included	49 W	ActiLume
910402288312	TCS260 1x49W/840 HFD D6 SI	HFD	Lamp(s) included	49 W	-
910402378212	TCS260 1x28W/830 HFS D6 SI	HFS	Lamp(s) included	28 W	-
910402378712	TCS260 1x35W/830 HFS D6 SI	HFS	Lamp(s) included	35 W	-
910402379212	TCS260 1x49W/830 HFS D6 SI	HFS	Lamp(s) included	49 W	-
910402379712	TCS260 1x54W/830 HFS D6 SI	HFS	Lamp(s) included	54 W	-
910402380212	TCS260 1x80W/830 HFS D6 SI	HFS	Lamp(s) included	80 W	-
910402386412	TCS260 1x28W/840 HFS D6 SI	HFS	Lamp(s) included	28 W	-
910402386912	TCS260 1x35W/840 HFS D6 SI	HFS	Lamp(s) included	35 W	-
910402387412	TCS260 1x49W/840 HFS D6 SI	HFS	Lamp(s) included	49 W	-
910402387912	TCS260 1x54W/840 HFS D6 SI	HFS	Lamp(s) included	54 W	-
910402394212	TCS260 1x28W/830 HFR D6 SI	HFR	Lamp(s) included	28 W	-
910402394412	TCS260 1x49W/830 HFR D6 SI	HFR	Lamp(s) included	49 W	-

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Embedded control
910402395812	TCS260 1x49W/840 HFR D6 SI	HFR	Lamp(s) included	49 W	-
910402399912	TCS260 1x35W/830 HFR D6 LX SI	HFR	Lamp(s) included	35 W	Luxsense
910402446912	TCS260 1x49W/830 HFR D6 LX SI	HFR	Lamp(s) included	49 W	Luxsense
910402462312	TCS260 1x28/54W HFPI D6 SI	HFPI	-	28, 54 W	-
910402462612	TCS260 1x35-80W HFPI D6 SI	HFPI	-	35, 49, 80 W	-
910402288812	TCS260 1x49W/830 HFR M2 LX WH	HFR	Lamp(s) included	49 W	Luxsense
910402374312	TCS260 1x28W/830 HFS M2 WH	HFS	Lamp(s) included	28 W	-
910402374812	TCS260 1x35W/830 HFS M2 WH	HFS	Lamp(s) included	35 W	-
910402375312	TCS260 1x49W/830 HFS M2 WH	HFS	Lamp(s) included	49 W	-
910402375812	TCS260 1x54W/830 HFS M2 WH	HFS	Lamp(s) included	54 W	-
910402376312	TCS260 1x80W/830 HFS M2 WH	HFS	Lamp(s) included	80 W	-
910402382512	TCS260 1x28W/840 HFS M2 WH	HFS	Lamp(s) included	28 W	-
910402383012	TCS260 1x35W/840 HFS M2 WH	HFS	Lamp(s) included	35 W	-
910402383512	TCS260 1x49W/840 HFS M2 WH	HFS	Lamp(s) included	49 W	-
910402384012	TCS260 1x54W/840 HFS M2 WH	HFS	Lamp(s) included	54 W	-
910402454012	TCS260 1x28W/830 HFR M2 WH	HFR	Lamp(s) included	28 W	-
910402461212	TCS260 1x28/54W HFPI M2 WH	HFPI	-	28, 54 W	-
910402461512	TCS260 1x35-80W HFPI M2 WH	HFPI	-	35, 49, 80 W	-
910402298312	TCS260 2x28W/830 HFS M2 PVCFR WH	HFS	Lamp(s) included	28 W	-
910402298412	TCS260 2x35W/830 HFS M2 PVCFR WH	HFS	Lamp(s) included	35 W	-
910402298512	TCS260 2x49W/830 HFS M2 PVCFR WH	HFS	Lamp(s) included	49 W	-
910402376812	TCS260 2x28W/830 HFS M2 WH	HFS	Lamp(s) included	28 W	-
910402377212	TCS260 2x35W/830 HFS M2 WH	HFS	Lamp(s) included	35 W	-
910402377612	TCS260 2x49W/830 HFS M2 WH	HFS	Lamp(s) included	49 W	-
910402378012	TCS260 2x54W/830 HFS M2 WH	HFS	Lamp(s) included	54 W	-
910402385012	TCS260 2x28W/840 HFS M2 WH	HFS	Lamp(s) included	28 W	-
910402385412	TCS260 2x35W/840 HFS M2 WH	HFS	Lamp(s) included	35 W	-
910402385812	TCS260 2x49W/840 HFS M2 WH	HFS	Lamp(s) included	49 W	-
910402386212	TCS260 2x54W/840 HFS M2 WH	HFS	Lamp(s) included	54 W	-
910402390612	TCS260 2x80W/840 HFS M2 WH	HFS	Lamp(s) included	80 W	-
910402454512	TCS260 2x28W/830 HFR M2 WH	HFR	Lamp(s) included	28 W	-
910402461812	TCS260 2x28/54W HFPI M2 WH	HFPI	-	28, 54 W	-
910402462112	TCS260 2x35-80W HFPI M2 WH	HFPI	-	35, 49, 80 W	-
910402298612	TCS260 2x28W/830 HFS D6 PVCFR WH	HFS	Lamp(s) included	28 W	-
910402298712	TCS260 2x35W/830 HFS D6 PVCFR WH	HFS	Lamp(s) included	35 W	-
910402298812	TCS260 2x49W/830 HFS D6 PVCFR WH	HFS	Lamp(s) included	49 W	-
910402298912	TCS260 2x28W/830 HFD-T D6 ACL PVCFR WH	HFD-T	Lamp(s) included	28 W	ActiLume
910402299012	TCS260 2x35W/830 HFD-T D6 ACL PVCFR WH	HFD-T	Lamp(s) included	35 W	ActiLume
910402299112	TCS260 2x49W/830 HFD-T D6 ACL PVCFR WH	HFD-T	Lamp(s) included	49 W	ActiLume
910402299212	TCS260 2x28W/830 HFD D6 PVCFR WH	HFD	Lamp(s) included	28 W	-

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Embedded control
910402299312	TCS260 2x35W/830 HFD D6 PVCFR WH	HFD	Lamp(s) included	35 W	-
910402299412	TCS260 2x49W/830 HFD D6 PVCFR WH	HFD	Lamp(s) included	49 W	-
910402376612	TCS260 2x28W/830 HFS D6 WH	HFS	Lamp(s) included	28 W	-
910402377012	TCS260 2x35W/830 HFS D6 WH	HFS	Lamp(s) included	35 W	-
910402377412	TCS260 2x49W/830 HFS D6 WH	HFS	Lamp(s) included	49 W	-
910402377812	TCS260 2x54W/830 HFS D6 WH	HFS	Lamp(s) included	54 W	-
910402384812	TCS260 2x28W/840 HFS D6 WH	HFS	Lamp(s) included	28 W	-
910402385212	TCS260 2x35W/840 HFS D6 WH	HFS	Lamp(s) included	35 W	-
910402385612	TCS260 2x49W/840 HFS D6 WH	HFS	Lamp(s) included	49 W	-
910402386012	TCS260 2x54W/840 HFS D6 WH	HFS	Lamp(s) included	54 W	-
910402390512	TCS260 2x80W/840 HFS D6 WH	HFS	Lamp(s) included	80 W	-
910402395312	TCS260 2x28W/840 HFR D6 WH	HFR	Lamp(s) included	28 W	-
910402395412	TCS260 2x35W/840 HFR D6 WH	HFR	Lamp(s) included	35 W	-
910402395512	TCS260 2x49W/840 HFR D6 WH	HFR	Lamp(s) included	49 W	-
910402453012	TCS260 2x28W/840 HFR D6 LX WH	HFR	Lamp(s) included	28 W	Luxsense
910402453112	TCS260 2x35W/840 HFR D6 LX WH	HFR	Lamp(s) included	35 W	Luxsense
910402453212	TCS260 2x49W/840 HFR D6 LX WH	HFR	Lamp(s) included	49 W	Luxsense
910402459712	TCS260 2x54W/840 HFR D6 WH	HFR	Lamp(s) included	54 W	-
910402461712	TCS260 2x28/54W HFPI D6 WH	HFPI	-	28, 54 W	-
910402462012	TCS260 2x35-80W HFPI D6 WH	HFPI	-	35, 49, 80 W	-
910925500412	TCS260 2x35W/830 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	35 W	ActiLume
910925500612	TCS260 2x49W/840 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	49 W	ActiLume
910925500812	TCS260 2x49W/830 HFD-T D6 ACL WH	HFD-T	Lamp(s) included	49 W	ActiLume
910925501012	TCS260 2x35W/840 HFD D6 WH	HFD	Lamp(s) included	35 W	-
910925501212	TCS260 2x35W/830 HFD D6 WH	HFD	Lamp(s) included	35 W	-
910925501412	TCS260 2x49W/840 HFD D6 WH	HFD	Lamp(s) included	49 W	-
910925501612	TCS260 2x49W/830 HFD D6 WH	HFD	Lamp(s) included	49 W	-
910402374012	TCS260 1x28W/830 HFS C6 WH	HFS	Lamp(s) included	28 W	-
910402374512	TCS260 1x35W/830 HFS C6 WH	HFS	Lamp(s) included	35 W	-
910402375012	TCS260 1x49W/830 HFS C6 WH	HFS	Lamp(s) included	49 W	-
910402375512	TCS260 1x54W/830 HFS C6 WH	HFS	Lamp(s) included	54 W	-
910402382212	TCS260 1x28W/840 HFS C6 WH	HFS	Lamp(s) included	28 W	-
910402382712	TCS260 1x35W/840 HFS C6 WH	HFS	Lamp(s) included	35 W	-
910402383212	TCS260 1x49W/840 HFS C6 WH	HFS	Lamp(s) included	49 W	-
910402383712	TCS260 1x54W/840 HFS C6 WH	HFS	Lamp(s) included	54 W	-
910402384212	TCS260 1x80W/840 HFS C6 WH	HFS	Lamp(s) included	80 W	-
910402392412	TCS260 1x54W/840 HFR C6 WH	HFR	Lamp(s) included	54 W	-
910402461012	TCS260 1x28/54W HFPI C6 WH	HFPI	-	28, 54 W	-
910402461312	TCS260 1x35-80W HFPI C6 WH	HFPI	-	35, 49, 80 W	-
910402374712	TCS260 1x35W/830 HFS M6 WH	HFS	Lamp(s) included	35 W	-
910402376212	TCS260 1x80W/830 HFS M6 WH	HFS	Lamp(s) included	80 W	-
910402383412	TCS260 1x49W/840 HFS M6 WH	HFS	Lamp(s) included	49 W	-
910402383912	TCS260 1x54W/840 HFS M6 WH	HFS	Lamp(s) included	54 W	-
910402376512	TCS260 2x28W/830 HFS C6 WH	HFS	Lamp(s) included	28 W	-
910402376912	TCS260 2x35W/830 HFS C6 WH	HFS	Lamp(s) included	35 W	-
910402377312	TCS260 2x49W/830 HFS C6 WH	HFS	Lamp(s) included	49 W	-

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Embedded control
910402377712	TCS260 2x54W/830 HFS C6 WH	HFS	Lamp(s) included	54 W	-
910402384712	TCS260 2x28W/840 HFS C6 WH	HFS	Lamp(s) included	28 W	-
910402385112	TCS260 2x35W/840 HFS C6 WH	HFS	Lamp(s) included	35 W	-
910402385512	TCS260 2x49W/840 HFS C6 WH	HFS	Lamp(s) included	49 W	-
910402385912	TCS260 2x54W/840 HFS C6 WH	HFS	Lamp(s) included	54 W	-
910402390412	TCS260 2x80W/840 HFS C6 WH	HFS	Lamp(s) included	80 W	-
910402392712	TCS260 2x49W/840 HFR C6 WH	HFR	Lamp(s) included	49 W	-
910402398212	TCS260 2x35W/840 HFR C6 LX WH	HFR	Lamp(s) included	35 W	Luxsense
910402398312	TCS260 2x49W/840 HFR C6 LX WH	HFR	Lamp(s) included	49 W	Luxsense
910402461612	TCS260 2x28/54W HFPI C6 WH	HFPI	-	28, 54 W	-
910402461912	TCS260 2x35-80W HFPI C6 WH	HFPI	-	35, 49, 80 W	-
910402376712	TCS260 2x28W/830 HFS M6 WH	HFS	Lamp(s) included	28 W	-
910402377112	TCS260 2x35W/830 HFS M6 WH	HFS	Lamp(s) included	35 W	-
910402377512	TCS260 2x49W/830 HFS M6 WH	HFS	Lamp(s) included	49 W	-
910402384912	TCS260 2x28W/840 HFS M6 WH	HFS	Lamp(s) included	28 W	-
910402385312	TCS260 2x35W/840 HFS M6 WH	HFS	Lamp(s) included	35 W	-
910402385712	TCS260 2x49W/840 HFS M6 WH	HFS	Lamp(s) included	49 W	-
910402386112	TCS260 2x54W/840 HFS M6 WH	HFS	Lamp(s) included	54 W	-
910402457912	TCS260 2x35W/830 HFR M6 WH	HFR	Lamp(s) included	35 W	-
910402458412	TCS260 2x28W/830 HFR M6 LX WH	HFR	Lamp(s) included	28 W	Luxsense
910402378412	TCS260 1x28W/830 HFS M2 SI	HFS	Lamp(s) included	28 W	-
910402378912	TCS260 1x35W/830 HFS M2 SI	HFS	Lamp(s) included	35 W	-
910402379412	TCS260 1x49W/830 HFS M2 SI	HFS	Lamp(s) included	49 W	-
910402380412	TCS260 1x80W/830 HFS M2 SI	HFS	Lamp(s) included	80 W	-
910402462412	TCS260 1x28/54W HFPI M2 SI	HFPI	-	28, 54 W	-
910402462712	TCS260 1x35-80W HFPI M2 SI	HFPI	-	35, 49, 80 W	-
910402379112	TCS260 1x49W/830 HFS C6 SI	HFS	Lamp(s) included	49 W	-
910402386312	TCS260 1x28W/840 HFS C6 SI	HFS	Lamp(s) included	28 W	-
910402386812	TCS260 1x35W/840 HFS C6 SI	HFS	Lamp(s) included	35 W	-
910402387312	TCS260 1x49W/840 HFS C6 SI	HFS	Lamp(s) included	49 W	-
910402387812	TCS260 1x54W/840 HFS C6 SI	HFS	Lamp(s) included	54 W	-
910402388312	TCS260 1x80W/840 HFS C6 SI	HFS	Lamp(s) included	80 W	-
910402462212	TCS260 1x28/54W HFPI C6 SI	HFPI	-	28, 54 W	-
910402462512	TCS260 1x35-80W HFPI C6 SI	HFPI	-	35, 49, 80 W	-
910402380612	TCS260 2x28W/830 HFS C6 SI	HFS	Lamp(s) included	28 W	-
910402381012	TCS260 2x35W/830 HFS C6 SI	HFS	Lamp(s) included	35 W	-
910402381412	TCS260 2x49W/830 HFS C6 SI	HFS	Lamp(s) included	49 W	-
910402381812	TCS260 2x54W/830 HFS C6 SI	HFS	Lamp(s) included	54 W	-
910402388812	TCS260 2x28W/840 HFS C6 SI	HFS	Lamp(s) included	28 W	-
910402389212	TCS260 2x35W/840 HFS C6 SI	HFS	Lamp(s) included	35 W	-
910402389612	TCS260 2x49W/840 HFS C6 SI	HFS	Lamp(s) included	49 W	-
91040239001	TCS260 2x54W/840 HFS C6 SI	HFS	Lamp(s) included	54 W	-
2					
910402390712	TCS260 2x80W/840 HFS C6 SI	HFS	Lamp(s) included	80 W	-
910402462812	TCS260 2x28/54W HFPI C6 SI	HFPI	-	28, 54 W	-
910402463112	TCS260 2x35-80W HFPI C6 SI	HFPI	-	35, 49, 80 W	-
910402380712	TCS260 2x28W/830 HFS D6 SI	HFS	Lamp(s) included	28 W	-
910402381112	TCS260 2x35W/830 HFS D6 SI	HFS	Lamp(s) included	35 W	-
910402381512	TCS260 2x49W/830 HFS D6 SI	HFS	Lamp(s) included	49 W	-
910402381912	TCS260 2x54W/830 HFS D6 SI	HFS	Lamp(s) included	54 W	-
910402388912	TCS260 2x28W/840 HFS D6 SI	HFS	Lamp(s) included	28 W	-

Order Code	Full Product Name	Gear	Kombipack	Lamp power	Embedded control
910402389312	TCS260 2x35W/840 HFS D6 SI	HFS	Lamp(s) included	35 W	-
910402389712	TCS260 2x49W/840 HFS D6 SI	HFS	Lamp(s) included	49 W	-
910402390112	TCS260 2x54W/840 HFS D6 SI	HFS	Lamp(s) included	54 W	-
910402390812	TCS260 2x80W/840 HFS D6 SI	HFS	Lamp(s) included	80 W	-
910402396212	TCS260 2x49W/840 HFR D6 SI	HFR	Lamp(s) included	49 W	-
910402453812	TCS260 2x35W/840 HFR D6 LX SI	HFR	Lamp(s) included	35 W	Luxsense
910402453912	TCS260 2x49W/840 HFR D6 LX SI	HFR	Lamp(s) included	49 W	Luxsense
910402459912	TCS260 2x54W/840 HFR D6 SI	HFR	Lamp(s) included	54 W	-
910402462912	TCS260 2x28/54W HFPI D6 SI	HFPI	-	28, 54 W	-
910402463212	TCS260 2x35-80W HFPI D6 SI	HFPI	-	35, 49, 80 W	-
910925500712	TCS260 2x49W/840 HFD-T D6 ACL SI	HFD-T	Lamp(s) included	49 W	ActiLume
910925501112	TCS260 2x35W/840 HFD D6 SI	HFD	Lamp(s) included	35 W	-
910925501512	TCS260 2x49W/840 HFD D6 SI	HFD	Lamp(s) included	49 W	-
910925501712	TCS260 2x49W/830 HFD D6 SI	HFD	Lamp(s) included	49 W	-
910402380912	TCS260 2x28W/830 HFS M2 SI	HFS	Lamp(s) included	28 W	-
910402381712	TCS260 2x49W/830 HFS M2 SI	HFS	Lamp(s) included	49 W	-
910402389112	TCS260 2x28W/840 HFS M2 SI	HFS	Lamp(s) included	28 W	-
910402389512	TCS260 2x35W/840 HFS M2 SI	HFS	Lamp(s) included	35 W	-
910402389912	TCS260 2x49W/840 HFS M2 SI	HFS	Lamp(s) included	49 W	-
910402390312	TCS260 2x54W/840 HFS M2 SI	HFS	Lamp(s) included	54 W	-
91040239091	TCS260 2x80W/840 HFS M2 SI	HFS	Lamp(s) included	80 W	-
910402463012	TCS260 2x28/54W HFPI M2 SI	HFPI	-	28, 54 W	-
910402463312	TCS260 2x35-80W HFPI M2 SI	HFPI	-	35, 49, 80 W	-
910402382012	TCS260 2x54W/830 HFS M6 SI	HFS	Lamp(s) included	54 W	-
910402389012	TCS260 2x28W/840 HFS M6 SI	HFS	Lamp(s) included	28 W	-
910402389412	TCS260 2x35W/840 HFS M6 SI	HFS	Lamp(s) included	35 W	-
910402389812	TCS260 2x49W/840 HFS M6 SI	HFS	Lamp(s) included	49 W	-
910402390212	TCS260 2x54W/840 HFS M6 SI	HFS	Lamp(s) included	54 W	-
910402386512	TCS260 1x28W/840 HFS M6 SI	HFS	Lamp(s) included	28 W	-
910402387012	TCS260 1x35W/840 HFS M6 SI	HFS	Lamp(s) included	35 W	-
910402387512	TCS260 1x49W/840 HFS M6 SI	HFS	Lamp(s) included	49 W	-
910402388012	TCS260 1x54W/840 HFS M6 SI	HFS	Lamp(s) included	54 W	-
910402388512	TCS260 1x80W/840 HFS M6 SI	HFS	Lamp(s) included	80 W	-

General information (2/2)

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402287012	TCS260 1x35W/840 HFD-T D6 ACL WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402287212	TCS260 1x35W/830 HFD-T D6 ACL WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402287412	TCS260 1x49W/840 HFD-T D6 ACL WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402287612	TCS260 1x49W/830 HFD-T D6 ACL WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402287812	TCS260 1x35W/840 HFD D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402288012	TCS260 1x35W/830 HFD D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard

EFix TCS260

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402288212	TCS260 1x49W/840 HFD D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402288412	TCS260 1x49W/830 HFD D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402374112	TCS260 1x28W/830 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402374612	TCS260 1x35W/830 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402375112	TCS260 1x49W/830 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402375612	TCS260 1x54W/830 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402382312	TCS260 1x28W/840 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402382812	TCS260 1x35W/840 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402383312	TCS260 1x49W/840 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402383812	TCS260 1x54W/840 HFS D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402393612	TCS260 1x35W/830 HFR D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402393712	TCS260 1x49W/830 HFR D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402394912	TCS260 1x28W/840 HFR D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402395112	TCS260 1x49W/840 HFR D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402395212	TCS260 1x54W/840 HFR D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402399112	TCS260 1x28W/830 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402399212	TCS260 1x35W/830 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402399312	TCS260 1x49W/830 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402447512	TCS260 1x28W/840 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402447812	TCS260 1x49W/840 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402447912	TCS260 1x54W/840 HFR D6 LX WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402461112	TCS260 1x28/54W HFPI D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402461412	TCS260 1x35-80W HFPI D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910925516612	TCS260 1x28W/830 HFD-T D6 ACL WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910925516712	TCS260 1x28W/830 HFD D6 WH	1 pc	Semi-high-gloss optic double parabolic	Standard
910402287512	TCS260 1x49W/840 HFD-T D6 ACL SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402288312	TCS260 1x49W/840 HFD D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402378212	TCS260 1x28W/830 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402378712	TCS260 1x35W/830 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402379212	TCS260 1x49W/830 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402379712	TCS260 1x54W/830 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402380212	TCS260 1x80W/830 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard

EFix TCS260

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402386412	TCS260 1x28W/840 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402386912	TCS260 1x35W/840 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402387412	TCS260 1x49W/840 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402387912	TCS260 1x54W/840 HFS D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402394212	TCS260 1x28W/830 HFR D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402394412	TCS260 1x49W/830 HFR D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402395812	TCS260 1x49W/840 HFR D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402399912	TCS260 1x35W/830 HFR D6 LX SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402446912	TCS260 1x49W/830 HFR D6 LX SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402462312	TCS260 1x28/54W HFPI D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402462612	TCS260 1x35-80W HFPI D6 SI	1 pc	Semi-high-gloss optic double parabolic	Standard
910402288812	TCS260 1x49W/830 HFR M2 LX WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402374312	TCS260 1x28W/830 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402374812	TCS260 1x35W/830 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402375312	TCS260 1x49W/830 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402375812	TCS260 1x54W/830 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402376312	TCS260 1x80W/830 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402382512	TCS260 1x28W/840 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402383012	TCS260 1x35W/840 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402383512	TCS260 1x49W/840 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402384012	TCS260 1x54W/840 HFS M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402454012	TCS260 1x28W/830 HFR M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402461212	TCS260 1x28/54W HFPI M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402461512	TCS260 1x35-80W HFPI M2 WH	1 pc	Matt mirror ribbed lamellae louver	Standard
910402298312	TCS260 2x28W/830 HFS M2 PVCFR WH	2 pcs	Matt mirror ribbed lamellae louver	PVC free
910402298412	TCS260 2x35W/830 HFS M2 PVCFR WH	2 pcs	Matt mirror ribbed lamellae louver	PVC free
910402298512	TCS260 2x49W/830 HFS M2 PVCFR WH	2 pcs	Matt mirror ribbed lamellae louver	PVC free
910402376812	TCS260 2x28W/830 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402377212	TCS260 2x35W/830 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402377612	TCS260 2x49W/830 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402378012	TCS260 2x54W/830 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402385012	TCS260 2x28W/840 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402385412	TCS260 2x35W/840 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402385812	TCS260 2x49W/840 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402386212	TCS260 2x54W/840 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402390612	TCS260 2x80W/840 HFS M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402454512	TCS260 2x28W/830 HFR M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402461812	TCS260 2x28/54W HFPI M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402462112	TCS260 2x35-80W HFPI M2 WH	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402298612	TCS260 2x28W/830 HFS D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402298712	TCS260 2x35W/830 HFS D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402298812	TCS260 2x49W/830 HFS D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402298912	TCS260 2x28W/830 HFD-T D6 ACL PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402299012	TCS260 2x35W/830 HFD-T D6 ACL PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402299112	TCS260 2x49W/830 HFD-T D6 ACL PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402299212	TCS260 2x28W/830 HFD D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402299312	TCS260 2x35W/830 HFD D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402299412	TCS260 2x49W/830 HFD D6 PVCFR WH	2 pcs	Semi-high-gloss optic double parabolic	PVC free
910402376612	TCS260 2x28W/830 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402377012	TCS260 2x35W/830 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402377412	TCS260 2x49W/830 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402377812	TCS260 2x54W/830 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402384812	TCS260 2x28W/840 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402385212	TCS260 2x35W/840 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402385612	TCS260 2x49W/840 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402386012	TCS260 2x54W/840 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402390512	TCS260 2x80W/840 HFS D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402395312	TCS260 2x28W/840 HFR D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402395412	TCS260 2x35W/840 HFR D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402395512	TCS260 2x49W/840 HFR D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402453012	TCS260 2x28W/840 HFR D6 LX WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402453112	TCS260 2x35W/840 HFR D6 LX WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402453212	TCS260 2x49W/840 HFR D6 LX WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402459712	TCS260 2x54W/840 HFR D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402461712	TCS260 2x28/54W HFPI D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402462012	TCS260 2x35-80W HFPI D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925500412	TCS260 2x35W/830 HFD-T D6 ACL WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925500612	TCS260 2x49W/840 HFD-T D6 ACL WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925500812	TCS260 2x49W/830 HFD-T D6 ACL WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501012	TCS260 2x35W/840 HFD D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501212	TCS260 2x35W/830 HFD D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501412	TCS260 2x49W/840 HFD D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501612	TCS260 2x49W/830 HFD D6 WH	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402374012	TCS260 1x28W/830 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard

EFix TCS260

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402374512	TCS260 1x35W/830 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402375012	TCS260 1x49W/830 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402375512	TCS260 1x54W/830 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402382212	TCS260 1x28W/840 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402382712	TCS260 1x35W/840 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402383212	TCS260 1x49W/840 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402383712	TCS260 1x54W/840 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402384212	TCS260 1x80W/840 HFS C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402392412	TCS260 1x54W/840 HFR C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402461012	TCS260 1x28/54W HFPI C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402461312	TCS260 1x35-80W HFPI C6 WH	1 pc	High-gloss optic double parabolic closed	Standard
910402374712	TCS260 1x35W/830 HFS M6 WH	1 pc	Matt optic double parabolic louver closed	Standard
910402376212	TCS260 1x80W/830 HFS M6 WH	1 pc	Matt optic double parabolic louver closed	Standard
910402383412	TCS260 1x49W/840 HFS M6 WH	1 pc	Matt optic double parabolic louver closed	Standard
910402383912	TCS260 1x54W/840 HFS M6 WH	1 pc	Matt optic double parabolic louver closed	Standard
910402376512	TCS260 2x28W/830 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402376912	TCS260 2x35W/830 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402377312	TCS260 2x49W/830 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402377712	TCS260 2x54W/830 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402384712	TCS260 2x28W/840 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402385112	TCS260 2x35W/840 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402385512	TCS260 2x49W/840 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402385912	TCS260 2x54W/840 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402390412	TCS260 2x80W/840 HFS C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402392712	TCS260 2x49W/840 HFR C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402398212	TCS260 2x35W/840 HFR C6 LX WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402398312	TCS260 2x49W/840 HFR C6 LX WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402461612	TCS260 2x28/54W HFPI C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402461912	TCS260 2x35-80W HFPI C6 WH	2 pcs	High-gloss optic double parabolic closed	Standard
910402376712	TCS260 2x28W/830 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402377112	TCS260 2x35W/830 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402377512	TCS260 2x49W/830 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard

EFix TCS260

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402384912	TCS260 2x28W/840 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402385312	TCS260 2x35W/840 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402385712	TCS260 2x49W/840 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402386112	TCS260 2x54W/840 HFS M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402457912	TCS260 2x35W/830 HFR M6 WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402458412	TCS260 2x28W/830 HFR M6 LX WH	2 pcs	Matt optic double parabolic louver closed	Standard
910402378412	TCS260 1x28W/830 HFS M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402378912	TCS260 1x35W/830 HFS M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402379412	TCS260 1x49W/830 HFS M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402380412	TCS260 1x80W/830 HFS M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402462412	TCS260 1x28/54W HFPI M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402462712	TCS260 1x35-80W HFPI M2 SI	1 pc	Matt mirror ribbed lamellae louver	Standard
910402379112	TCS260 1x49W/830 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402386312	TCS260 1x28W/840 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402386812	TCS260 1x35W/840 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402387312	TCS260 1x49W/840 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402387812	TCS260 1x54W/840 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402388312	TCS260 1x80W/840 HFS C6 SI	1 pc	High-gloss optic double parabolic closed	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402462212	TCS260 1x28/54W HFPI C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402462512	TCS260 1x35-80W HFPI C6 SI	1 pc	High-gloss optic double parabolic closed	Standard
910402380612	TCS260 2x28W/830 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402381012	TCS260 2x35W/830 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402381412	TCS260 2x49W/830 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402381812	TCS260 2x54W/830 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402388812	TCS260 2x28W/840 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402389212	TCS260 2x35W/840 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402389612	TCS260 2x49W/840 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402390012	TCS260 2x54W/840 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402390712	TCS260 2x80W/840 HFS C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402462812	TCS260 2x28/54W HFPI C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402463112	TCS260 2x35-80W HFPI C6 SI	2 pcs	High-gloss optic double parabolic closed	Standard
910402380712	TCS260 2x28W/830 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402381112	TCS260 2x35W/830 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402381512	TCS260 2x49W/830 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard

EFix TCS260

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402381912	TCS260 2x54W/830 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402388912	TCS260 2x28W/840 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402389312	TCS260 2x35W/840 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402389712	TCS260 2x49W/840 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402390112	TCS260 2x54W/840 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402390812	TCS260 2x80W/840 HFS D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402396212	TCS260 2x49W/840 HFR D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402453812	TCS260 2x35W/840 HFR D6 LX SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402453912	TCS260 2x49W/840 HFR D6 LX SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402459912	TCS260 2x54W/840 HFR D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402462912	TCS260 2x28/54W HFPI D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910402463212	TCS260 2x35-80W HFPI D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925500712	TCS260 2x49W/840 HFD-T D6 ACL SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501112	TCS260 2x35W/840 HFD D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501512	TCS260 2x49W/840 HFD D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard
910925501712	TCS260 2x49W/830 HFD D6 SI	2 pcs	Semi-high-gloss optic double parabolic	Standard

Order Code	Full Product Name	Number of light sources	Optic type	Internal wiring
910402380912	TCS260 2x28W/830 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402381712	TCS260 2x49W/830 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402389112	TCS260 2x28W/840 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402389512	TCS260 2x35W/840 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402389912	TCS260 2x49W/840 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402390312	TCS260 2x54W/840 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402390912	TCS260 2x80W/840 HFS M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402463012	TCS260 2x28/54W HFPI M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402463312	TCS260 2x35-80W HFPI M2 SI	2 pcs	Matt mirror ribbed lamellae louver	Standard
910402382012	TCS260 2x54W/830 HFS M6 SI	2 pcs	Matt optic double parabolic louver closed	Standard
910402389012	TCS260 2x28W/840 HFS M6 SI	2 pcs	Matt optic double parabolic louver closed	Standard
910402389412	TCS260 2x35W/840 HFS M6 SI	2 pcs	Matt optic double parabolic louver closed	Standard
910402389812	TCS260 2x49W/840 HFS M6 SI	2 pcs	Matt optic double parabolic louver closed	Standard
910402390212	TCS260 2x54W/840 HFS M6 SI	2 pcs	Matt optic double parabolic louver closed	Standard
910402386512	TCS260 1x28W/840 HFS M6 SI	1 pc	Matt optic double parabolic louver closed	Standard
910402387012	TCS260 1x35W/840 HFS M6 SI	1 pc	Matt optic double parabolic louver closed	Standard
910402387512	TCS260 1x49W/840 HFS M6 SI	1 pc	Matt optic double parabolic louver closed	Standard
910402388012	TCS260 1x54W/840 HFS M6 SI	1 pc	Matt optic double parabolic louver closed	Standard
910402388512	TCS260 1x80W/840 HFS M6 SI	1 pc	Matt optic double parabolic louver closed	Standard

Mechanical and housing

EFix TCS260

Order Code	Full Product Name	Color
910402287012	TCS260 1x35W/840 HFD-T D6 ACL WH	White
910402287212	TCS260 1x35W/830 HFD-T D6 ACL WH	White
910402287412	TCS260 1x49W/840 HFD-T D6 ACL WH	White
910402287612	TCS260 1x49W/830 HFD-T D6 ACL WH	White
910402287812	TCS260 1x35W/840 HFD D6 WH	White
910402288012	TCS260 1x35W/830 HFD D6 WH	White
910402288212	TCS260 1x49W/840 HFD D6 WH	White
910402288412	TCS260 1x49W/830 HFD D6 WH	White
910402374112	TCS260 1x28W/830 HFS D6 WH	White
910402374612	TCS260 1x35W/830 HFS D6 WH	White
910402375112	TCS260 1x49W/830 HFS D6 WH	White
910402375612	TCS260 1x54W/830 HFS D6 WH	White
910402382312	TCS260 1x28W/840 HFS D6 WH	White
910402382812	TCS260 1x35W/840 HFS D6 WH	White
910402383312	TCS260 1x49W/840 HFS D6 WH	White
910402383812	TCS260 1x54W/840 HFS D6 WH	White
910402393612	TCS260 1x35W/830 HFR D6 WH	White
910402393712	TCS260 1x49W/830 HFR D6 WH	White
910402394912	TCS260 1x28W/840 HFR D6 WH	White
910402395112	TCS260 1x49W/840 HFR D6 WH	White
910402395212	TCS260 1x54W/840 HFR D6 WH	White
910402399112	TCS260 1x28W/830 HFR D6 LX WH	White
910402399212	TCS260 1x35W/830 HFR D6 LX WH	White
910402399312	TCS260 1x49W/830 HFR D6 LX WH	White
910402447512	TCS260 1x28W/840 HFR D6 LX WH	White
910402447812	TCS260 1x49W/840 HFR D6 LX WH	White
910402447912	TCS260 1x54W/840 HFR D6 LX WH	White
910402461112	TCS260 1x28/54W HFPI D6 WH	White
910402461412	TCS260 1x35-80W HFPI D6 WH	White
910925516612	TCS260 1x28W/830 HFD-T D6 ACL WH	White
910925516712	TCS260 1x28W/830 HFD D6 WH	White
910402287512	TCS260 1x49W/840 HFD-T D6 ACL SI	Silver
910402288312	TCS260 1x49W/840 HFD D6 SI	Silver
910402378212	TCS260 1x28W/830 HFS D6 SI	Silver
910402378712	TCS260 1x35W/830 HFS D6 SI	Silver
910402379212	TCS260 1x49W/830 HFS D6 SI	Silver
910402379712	TCS260 1x54W/830 HFS D6 SI	Silver
910402380212	TCS260 1x80W/830 HFS D6 SI	Silver
910402386412	TCS260 1x28W/840 HFS D6 SI	Silver
910402386912	TCS260 1x35W/840 HFS D6 SI	Silver
910402387412	TCS260 1x49W/840 HFS D6 SI	Silver
910402387912	TCS260 1x54W/840 HFS D6 SI	Silver
910402394212	TCS260 1x28W/830 HFR D6 SI	Silver
910402394412	TCS260 1x49W/830 HFR D6 SI	Silver
910402395812	TCS260 1x49W/840 HFR D6 SI	Silver
910402399912	TCS260 1x35W/830 HFR D6 LX SI	Silver
910402446912	TCS260 1x49W/830 HFR D6 LX SI	Silver
910402462312	TCS260 1x28/54W HFPI D6 SI	Silver
910402462612	TCS260 1x35-80W HFPI D6 SI	Silver
910402288812	TCS260 1x49W/830 HFR M2 LX WH	White
910402374312	TCS260 1x28W/830 HFS M2 WH	White
910402374812	TCS260 1x35W/830 HFS M2 WH	White

Order Code	Full Product Name	Color
910402375312	TCS260 1x49W/830 HFS M2 WH	White
910402375812	TCS260 1x54W/830 HFS M2 WH	White
910402376312	TCS260 1x80W/830 HFS M2 WH	White
910402382512	TCS260 1x28W/840 HFS M2 WH	White
910402383012	TCS260 1x35W/840 HFS M2 WH	White
910402383512	TCS260 1x49W/840 HFS M2 WH	White
910402384012	TCS260 1x54W/840 HFS M2 WH	White
910402454012	TCS260 1x28W/830 HFR M2 WH	White
910402461212	TCS260 1x28/54W HFPI M2 WH	White
910402461512	TCS260 1x35-80W HFPI M2 WH	White
910402298312	TCS260 2x28W/830 HFS M2 PVCFR WH	White
910402298412	TCS260 2x35W/830 HFS M2 PVCFR WH	White
910402298512	TCS260 2x49W/830 HFS M2 PVCFR WH	White
910402376812	TCS260 2x28W/830 HFS M2 WH	White
910402377212	TCS260 2x35W/830 HFS M2 WH	White
910402377612	TCS260 2x49W/830 HFS M2 WH	White
910402378012	TCS260 2x54W/830 HFS M2 WH	White
910402385012	TCS260 2x28W/840 HFS M2 WH	White
910402385412	TCS260 2x35W/840 HFS M2 WH	White
910402385812	TCS260 2x49W/840 HFS M2 WH	White
910402386212	TCS260 2x54W/840 HFS M2 WH	White
910402390612	TCS260 2x80W/840 HFS M2 WH	White
910402454512	TCS260 2x28W/830 HFR M2 WH	White
910402461812	TCS260 2x28/54W HFPI M2 WH	White
910402462112	TCS260 2x35-80W HFPI M2 WH	White
910402298612	TCS260 2x28W/830 HFS D6 PVCFR WH	White
910402298712	TCS260 2x35W/830 HFS D6 PVCFR WH	White
910402298812	TCS260 2x49W/830 HFS D6 PVCFR WH	White
910402298912	TCS260 2x28W/830 HFD-T D6 ACL PVCFR WH	White
910402299012	TCS260 2x35W/830 HFD-T D6 ACL PVCFR WH	White
910402299112	TCS260 2x49W/830 HFD-T D6 ACL PVCFR WH	White
910402299212	TCS260 2x28W/830 HFD D6 PVCFR WH	White
910402299312	TCS260 2x35W/830 HFD D6 PVCFR WH	White
910402299412	TCS260 2x49W/830 HFD D6 PVCFR WH	White
910402376612	TCS260 2x28W/830 HFS D6 WH	White
910402377012	TCS260 2x35W/830 HFS D6 WH	White
910402377412	TCS260 2x49W/830 HFS D6 WH	White
910402377812	TCS260 2x54W/830 HFS D6 WH	White
910402384812	TCS260 2x28W/840 HFS D6 WH	White
910402385212	TCS260 2x35W/840 HFS D6 WH	White
910402385612	TCS260 2x49W/840 HFS D6 WH	White
910402386012	TCS260 2x54W/840 HFS D6 WH	White
910402390512	TCS260 2x80W/840 HFS D6 WH	White
910402395312	TCS260 2x28W/840 HFR D6 WH	White
910402395412	TCS260 2x35W/840 HFR D6 WH	White
910402395512	TCS260 2x49W/840 HFR D6 WH	White
910402453012	TCS260 2x28W/840 HFR D6 LX WH	White
910402453112	TCS260 2x35W/840 HFR D6 LX WH	White
910402453212	TCS260 2x49W/840 HFR D6 LX WH	White
910402459712	TCS260 2x54W/840 HFR D6 WH	White
910402461712	TCS260 2x28/54W HFPI D6 WH	White
910402462012	TCS260 2x35-80W HFPI D6 WH	White

EFix TCS260

Order Code	Full Product Name	Color
910925500412	TCS260 2x35W/830 HFD-T D6 ACL WH	White
910925500612	TCS260 2x49W/840 HFD-T D6 ACL WH	White
910925500812	TCS260 2x49W/830 HFD-T D6 ACL WH	White
910925501012	TCS260 2x35W/840 HFD D6 WH	White
910925501212	TCS260 2x35W/830 HFD D6 WH	White
910925501412	TCS260 2x49W/840 HFD D6 WH	White
910925501612	TCS260 2x49W/830 HFD D6 WH	White
910402374012	TCS260 1x28W/830 HFS C6 WH	White
910402374512	TCS260 1x35W/830 HFS C6 WH	White
910402375012	TCS260 1x49W/830 HFS C6 WH	White
910402375512	TCS260 1x54W/830 HFS C6 WH	White
910402382212	TCS260 1x28W/840 HFS C6 WH	White
910402382712	TCS260 1x35W/840 HFS C6 WH	White
910402383212	TCS260 1x49W/840 HFS C6 WH	White
910402383712	TCS260 1x54W/840 HFS C6 WH	White
910402384212	TCS260 1x80W/840 HFS C6 WH	White
910402392412	TCS260 1x54W/840 HFR C6 WH	White
910402461012	TCS260 1x28/54W HFPI C6 WH	White
910402461312	TCS260 1x35-80W HFPI C6 WH	White
910402374712	TCS260 1x35W/830 HFS M6 WH	White
910402376212	TCS260 1x80W/830 HFS M6 WH	White
910402383412	TCS260 1x49W/840 HFS M6 WH	White
910402383912	TCS260 1x54W/840 HFS M6 WH	White
910402376512	TCS260 2x28W/830 HFS C6 WH	White
910402376912	TCS260 2x35W/830 HFS C6 WH	White
910402377312	TCS260 2x49W/830 HFS C6 WH	White
910402377712	TCS260 2x54W/830 HFS C6 WH	White
910402384712	TCS260 2x28W/840 HFS C6 WH	White
910402385112	TCS260 2x35W/840 HFS C6 WH	White
910402385512	TCS260 2x49W/840 HFS C6 WH	White
910402385912	TCS260 2x54W/840 HFS C6 WH	White
910402390412	TCS260 2x80W/840 HFS C6 WH	White
910402392712	TCS260 2x49W/840 HFR C6 WH	White
910402398212	TCS260 2x35W/840 HFR C6 LX WH	White
910402398312	TCS260 2x49W/840 HFR C6 LX WH	White
910402461612	TCS260 2x28/54W HFPI C6 WH	White
910402461912	TCS260 2x35-80W HFPI C6 WH	White
910402376712	TCS260 2x28W/830 HFS M6 WH	White
910402377112	TCS260 2x35W/830 HFS M6 WH	White
910402377512	TCS260 2x49W/830 HFS M6 WH	White
910402384912	TCS260 2x28W/840 HFS M6 WH	White
910402385312	TCS260 2x35W/840 HFS M6 WH	White
910402385712	TCS260 2x49W/840 HFS M6 WH	White
910402386112	TCS260 2x54W/840 HFS M6 WH	White
910402457912	TCS260 2x35W/830 HFR M6 WH	White
910402458412	TCS260 2x28W/830 HFR M6 LX WH	White
910402378412	TCS260 1x28W/830 HFS M2 SI	Silver
910402378912	TCS260 1x35W/830 HFS M2 SI	Silver
910402379412	TCS260 1x49W/830 HFS M2 SI	Silver
910402380412	TCS260 1x80W/830 HFS M2 SI	Silver
910402462412	TCS260 1x28/54W HFPI M2 SI	Silver
910402462712	TCS260 1x35-80W HFPI M2 SI	Silver

Order Code	Full Product Name	Color
910402379112	TCS260 1x49W/830 HFS C6 SI	Silver
910402386312	TCS260 1x28W/840 HFS C6 SI	Silver
910402386812	TCS260 1x35W/840 HFS C6 SI	Silver
910402387312	TCS260 1x49W/840 HFS C6 SI	Silver
910402387812	TCS260 1x54W/840 HFS C6 SI	Silver
910402388312	TCS260 1x80W/840 HFS C6 SI	Silver
910402462212	TCS260 1x28/54W HFPI C6 SI	Silver
910402462512	TCS260 1x35-80W HFPI C6 SI	Silver
910402380612	TCS260 2x28W/830 HFS C6 SI	Silver
910402381012	TCS260 2x35W/830 HFS C6 SI	Silver
910402381412	TCS260 2x49W/830 HFS C6 SI	Silver
910402381812	TCS260 2x54W/830 HFS C6 SI	Silver
910402388812	TCS260 2x28W/840 HFS C6 SI	Silver
910402389212	TCS260 2x35W/840 HFS C6 SI	Silver
910402389612	TCS260 2x49W/840 HFS C6 SI	Silver
910402390012	TCS260 2x54W/840 HFS C6 SI	Silver
910402390712	TCS260 2x80W/840 HFS C6 SI	Silver
910402462812	TCS260 2x28/54W HFPI C6 SI	Silver
910402463112	TCS260 2x35-80W HFPI C6 SI	Silver
910402380712	TCS260 2x28W/830 HFS D6 SI	Silver
910402381112	TCS260 2x35W/830 HFS D6 SI	Silver
910402381512	TCS260 2x49W/830 HFS D6 SI	Silver
910402381912	TCS260 2x54W/830 HFS D6 SI	Silver
910402388912	TCS260 2x28W/840 HFS D6 SI	Silver
910402389312	TCS260 2x35W/840 HFS D6 SI	Silver
910402389712	TCS260 2x49W/840 HFS D6 SI	Silver
910402390112	TCS260 2x54W/840 HFS D6 SI	Silver
910402390812	TCS260 2x80W/840 HFS D6 SI	Silver
910402396212	TCS260 2x49W/840 HFR D6 SI	Silver
910402453812	TCS260 2x35W/840 HFR D6 LX SI	Silver
910402453912	TCS260 2x49W/840 HFR D6 LX SI	Silver
910402459912	TCS260 2x54W/840 HFR D6 SI	Silver
910402462912	TCS260 2x28/54W HFPI D6 SI	Silver
910402463212	TCS260 2x35-80W HFPI D6 SI	Silver
910925500712	TCS260 2x49W/840 HFD-T D6 ACL SI	Silver
910925501112	TCS260 2x35W/840 HFD D6 SI	Silver
910925501512	TCS260 2x49W/840 HFD D6 SI	Silver
910925501712	TCS260 2x49W/830 HFD D6 SI	Silver
910402380912	TCS260 2x28W/830 HFS M2 SI	Silver
910402381712	TCS260 2x49W/830 HFS M2 SI	Silver
910402389112	TCS260 2x28W/840 HFS M2 SI	Silver
910402389512	TCS260 2x35W/840 HFS M2 SI	Silver
910402389912	TCS260 2x49W/840 HFS M2 SI	Silver
910402390312	TCS260 2x54W/840 HFS M2 SI	Silver
910402390912	TCS260 2x80W/840 HFS M2 SI	Silver
910402463012	TCS260 2x28/54W HFPI M2 SI	Silver
910402463312	TCS260 2x35-80W HFPI M2 SI	Silver
910402382012	TCS260 2x54W/830 HFS M6 SI	Silver
910402389012	TCS260 2x28W/840 HFS M6 SI	Silver
910402389412	TCS260 2x35W/840 HFS M6 SI	Silver
910402389812	TCS260 2x49W/840 HFS M6 SI	Silver
910402390212	TCS260 2x54W/840 HFS M6 SI	Silver

EFix TCS260

Order Code	Full Product Name	Color
910402386512	TCS260 1x28W/840 HFS M6 SI	Silver
910402387012	TCS260 1x35W/840 HFS M6 SI	Silver
910402387512	TCS260 1x49W/840 HFS M6 SI	Silver

Order Code	Full Product Name	Color
910402388012	TCS260 1x54W/840 HFS M6 SI	Silver
910402388512	TCS260 1x80W/840 HFS M6 SI	Silver

