



# TCS398

## TCS398 C

TCS398 is also suitable for TL5 or TLD fluorescent lamps, with a wide range of high-performance optics. The luminaire is a direct version and can be surface-mounted or suspended. Two types of suspension systems are available: wire and tube suspension. The luminaire can be mounted individually and in configurations.

### Features


- Wide selection of best-in-class optics, customized to meet your specific needs
- Choice of fluorescent lamps TL5 or TLD: increased efficiency, luminaire is optimized with TL5 version
- Compact dimensions, clean lines and subtly-round edges: offer stylish design & a high quality appearance
- Semi-matt housing (RAL9010), suitable for modern interiors
- Philips V-clips to ease installation and maintenance
- Choice of suspended or surface mounting offers flexibility in application
- Top mirror on request: offers higher luminaire performance
- In-line mounting on request for a smooth visual appearance

### Application

- Club offices
- Cell offices
- Hive offices
- Meet office spaces
- Lobby office spaces
- Recreational areas
- Public buildings, schools, and hospitals
- General industries

TCS398 C

Dimensional drawing



Product	A	B	C
TCS398 C 1xTL5-35W K HFP M6 FTB	1488 mm	1558 mm	195 mm

