



Waterproof lighting solution

TCW060

Designed for use in demanding environments, TCW060 is an economical, compact waterproof luminaire. Dedicated versions are available for TL-D and TL5 lamps. Ingress-protected to a level of IP65 and operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces – at the same cost as an electromagnetic solution. A flexible ceiling clip facilitates easy installation and maintenance.

Benefits

- Economical, compact waterproof luminaire designed for use in demanding environments
- Operating solely on electronic gear, this is a competitive energy-saving solution for wet spaces at the same cost as a standard electromagnetic solution
- Dedicated versions available for TL5 and TL-D lamps

Features

- Dedicated versions for TL-D and TL5 lamps
- IP65
- Electronic gear
- Flexible ceiling clip

Application

- Wet environments
- Light industry
- Parking garages

Specifications

Type	TCW059
	TCW060

Light source	Fluorescent:
	- 1 or 2 x MASTER TL5 / G5 / 14, 28, 35, 49 W

TCW060

	- 1 or 2 x MASTER TL-D / G13 / 18, 36, 58 W
Lamp included	No
Ballast	Electronic, High Frequency 220 - 240 V / 50 - 60 Hz
Optical cover	Polycarbonate, prismatic (PCP)
Option	Only for TCW60 version: - Emergency lighting (integrated): 1 hour (EL1), 3 hours (EL3)
Connection	Screw connector
Material	Housing: - TCW060: polycarbonate, grey - TCW059: ABS, grey Cover: polycarbonate, UV-resistant Ceiling clips: stainless steel Cover clips: polycarbonate, grey or stainless steel

Installation	Surface mounted Operating temperature: -15°C < T
Maintenance	Hingeable cover for easy lamp replacement
Main applications	Wet environments, light industries, parkings

Accessories



Stainless-steel clips for the
TCW060/059 TL-D versions.

Ordercode 910930025518,
910930025618, 910930029318,
910930029618

