



# TCW060 – Just LIGHT

## TCW060 A

The new TCW060 hermetic luminaire is ideal for use in harsh environments where protection against vapor, water, and dust is required. It has been specially designed and developed for use with TL-D / TL5 tubular fluorescent lamps and electronic ballasts. Its compact and economical design provides perfect integration with the environment. The IP65 protection means the TCW060 is waterproof, enabling it to be used in damp places such as in industry, warehouses, garages, etc. It is easy to install and maintain because it has adjustable ceiling clips to make installation even more flexible and practical.

### Benefits

- Economical, compact luminaire designed for use in hermetic environments where robustness and performance are key
- Operates exclusively with an electronic ballast, making it the best option for damp areas; energy saving
- Versions available with TL5 and TL-D lamps
- Easy installation and maintenance

### Features

- Complies in full with the standards for IP65 protection - provides protection against moderate impact, dust, and moisture
- Electronic ballast saves energy and produces less noise and flicker

### Application

- Industries
- Garages
- External and coastal areas (salt water)

### Specifications

Type	TCW060
Light source	2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W TL5

Mains voltage	Electronic 220 V / 60-50 Hz: (EB)
---------------	-----------------------------------

TCW060 A

Materials and finishing	Body: Basic reinforced fiber-glass version (ABS)
	Professional polycarbonate version (PC)
	UV-resistant polycarbonate diffuser (PC)
	Steel chassis in white color (RAL9003)

Installation	Fastening clips included in the polycarbonate luminaire (PC)
	Stainless-steel suspension system
	Suspended or surface-mounted on the ceiling


Versions



Accessories



Ordercode 919506130061



Ordercode 919506238551



Ordercode 919506238561

General Information	
Gear	EB
Number of light sources	2 pcs

General Information

## TCW060 A

Order Code	Full Product Name	Optical cover/lens type	Lamp family code	Lamp power
919106031571	TCW060 2XTL-D32W/840 EB ABS-PC-L	Polycarbonate bowl/cover	TL-D	32 W
919106031621	TCW060 2xTL-D32W/840 EB PC-L	Polycarbonate large	TL-D	32 W
919106032201	TCW060 2XTL-D32W/840 EB110/220V ABS-PC	Polycarbonate bowl/cover	TL-D	32 W
919106032421	TCW060 2XTL-D32W-CO-25 EB110/220V ABS-PC	Polycarbonate bowl/cover	TL-D	32 W
919106031581	TCW060 2xTL5-28W/840 EB ABS-PC-L	Polycarbonate large	TL5	28 W
919106031591	TCW060 2xTL5-54W/840 EB ABS-PC-L	Polycarbonate large	TL5	54 W
919106031601	TCW060 2xTL5-28W/840 EB ABS-PC-S	Polycarbonate small	TL5	28 W
919106031611	TCW060 2xTL5-54W/840 EB ABS-PC-S	Polycarbonate small	TL5	54 W

Order Code	Full Product Name	Optical cover/lens type	Lamp family code	Lamp power
919106031631	TCW060 2xTL5-25W/840 EB PC-L	Polycarbonate large	TL5	25 W
919106031641	TCW060 2xTL5-28W/840 EB PC-L	Polycarbonate large	TL5	28 W
919106031651	TCW060 2xTL5-50W/840 EB PC-L	Polycarbonate large	TL5	50 W
919106031661	TCW060 2xTL5-54W/840 EB PC-L	Polycarbonate large	TL5	54 W
919106031671	TCW060 2xTL5-25W/840 EB PC-S	Polycarbonate small	TL5	25 W
919106031681	TCW060 2xTL5-28W/840 EB PC-S	Polycarbonate small	TL5	28 W
919106031691	TCW060 2xTL5-50W/840 EB PC-S	Polycarbonate small	TL5	50 W
919106031701	TCW060 2xTL5-54W/840 EB PC-S	Polycarbonate small	TL5	54 W

### Operating and Electrical

Order Code	Full Product Name	Input Voltage
919106031571	TCW060 2XTL-D32W/840 EB ABS-PC-L	-
919106031621	TCW060 2xTL-D32W/840 EB PC-L	-
919106032201	TCW060 2XTL-D32W/840 EB110/220V ABS-PC	110 to 220 V
919106032421	TCW060 2XTL-D32W-CO-25 EB110/220V ABS-PC	110 to 220 V
919106031581	TCW060 2xTL5-28W/840 EB ABS-PC-L	-
919106031591	TCW060 2xTL5-54W/840 EB ABS-PC-L	-
919106031601	TCW060 2xTL5-28W/840 EB ABS-PC-S	-
919106031611	TCW060 2xTL5-54W/840 EB ABS-PC-S	-

Order Code	Full Product Name	Input Voltage
919106031631	TCW060 2xTL5-25W/840 EB PC-L	-
919106031641	TCW060 2xTL5-28W/840 EB PC-L	-
919106031651	TCW060 2xTL5-50W/840 EB PC-L	-
919106031661	TCW060 2xTL5-54W/840 EB PC-L	-
919106031671	TCW060 2xTL5-25W/840 EB PC-S	-
919106031681	TCW060 2xTL5-28W/840 EB PC-S	-
919106031691	TCW060 2xTL5-50W/840 EB PC-S	-
919106031701	TCW060 2xTL5-54W/840 EB PC-S	-

