



Fit-for-use TL5 lamp

TL5 EssentialView Super 80

Philips TL5 EssentialView is a compact, highly efficient fluorescent lamp that provides functional light at an affordable price.

Benefits

- Same lifetime as Standard TL-D and most cost-efficient TL5 lamps
- Slim tube allows more compact and flexible luminaire design
- Maximum lumen output at suitable ambient temperature

Features

- Small diameter of only 16 mm
- To be used with electronic ballast for TL5 only
- Operating temperature from 5 to 50 °C

Application

- Offices, shops, supermarkets, schools, hospitals and industrial facilities


Versions



G5, T5

TL5 EssentialView Super 80

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL5 EssentialView 14W/865	17.0 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
1SL/40					

