



# The world's most efficient fluorescent lighting

# **MASTER TL5 High Efficiency Eco**

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HE Eco lamp offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

#### **Benefits**

- Up to 10 % energy saving with simply changing the lamp
- The same quality of light as compared with MASTER TL5 HE lamps
- · All benefits of regular TL5 lamps

### **Features**

- $\cdot$  High lamp efficacies up to 114 lm/W
- $\cdot$  Up to 10% power reduction in comparison with standard MASTER TL5 HE lamps
- · Fluorescent Super 80 light quality

#### **Application**


• Ideally suited for recessed, surface-mounted and suspended luminaires e.g. in offices, shops, schools, public buildings and industry (low ceiling), wherever high-quality, energy-efficient lighting is required

#### **Warnings and Safety**

- $\cdot$  A reduction in energy consumption is only achieved with current-controlled gear.
- $\cdot$  The lamps operate perfectly with power-controlled gear, but in that case the light output can be up to 10% higher.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

# **MASTER TL5 High Efficiency Eco**

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Eco	17 mm	549.0 mm	556.1 mm	553.7 mm	563.2 mm
13=14W/840 UNP/40					
MASTER TL5 HE Eco	17 mm	1,149.0 mm	1,156.1 mm	1,153.7 mm	1,163.2 mm
25=28W/840 UNP/40					

General Information	
Cap base	G5
Light Technical	
Chromaticity Coordinate X (Nom)	0.38
Chromaticity Coordinate Y (Nom)	0.38
Colour designation	Cool White (CW)
Correlated Colour Temperature	4000 K
Colour rendering index (CRI)	80
Operating and Electrical	
Lamp current (nom.)	0.170 A
Controls and Dimming	
Dimmable	Yes
Mechanical and Housing	
Bulb shape	T5
Approval and Application	
Mercury (Hg) content (nom.)	1.2 mg

## **Light Technical**

Order Code	Full Product Name	Luminous efficacy (rated) (nom.)	Luminous Flux
88083000	MASTER TL5 HE Eco 13=14W/840 UNP/40	92 lm/W	1,150 lm
82589300	MASTER TL5 HE Eco 25=28W/840 UNP/40	103 lm/W	2,520 lm

## Operating and Electrical

Order Code	Full Product Name	Power Consumption
88083000	MASTER TL5 HE Eco 13=14W/840 UNP/40	12.5 W



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.

# **MASTER TL5 High Efficiency Eco**

Order Code	Full Product Name	Power Consumption
82589300	MASTER TL5 HE Eco 25=28W/840 UNP/40	25.4 W

## **Approval and Application**

		Energy consumption kWh/	
Order Code	Full Product Name	1,000 hours	
88083000	MASTER TL5 HE Eco 13=14W/840 UNP/40	13 kWh	

		Energy consumption kWh/	
Order Code	Full Product Name	1,000 hours	
82589300	MASTER TL5 HE Eco 25=28W/840 UNP/40	26 kWh	



© 2023 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.