

# The ideal combination of extra-long life and highest efficiency

## MASTER TL5 High Efficiency Xtra Eco

TL5 High Efficiency Xtra Eco lamp (tube diameter 16 mm) provides the ideal combination of extra-long life and extra energy savings via simple lamp-for-lamp replacement of TL5 HE lamps, without any compromise on the high lighting quality.

### Benefits

- The longer product lifetime lowers maintenance costs and facilitates the change from spot to group replacement, while at the same time reducing waste and disposal cost.
- Up to 10% energy saving
- The same quality of light as from MASTER TL5 HE lamps

### Features


- High lamp efficacies up to 114 lm/W
- Up to 10% power reduction and double the lamp life compared to standard MASTER TL5 HE

### Application

- All current TL5 HE applications, e.g. offices, schools, supermarkets, industry


# MASTER TL5 High Efficiency Xtra Eco

## Versions



G5, T5

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL5 HE Xtra	17 mm	1149.0 mm	1156.1 mm	1153.7 mm	1163.2 mm
Eco 25=28W/840 1SL					

