



# The world's most efficient and brightest fluorescent lighting

## MASTER TL5 High Output Eco

This extremely efficient TL5 lamp (tube diameter 16 mm) saves considerable energy by simple lamp-for-lamp replacement. The TL5 HO Eco lamp is optimized for installations requiring high light output and offers excellent lumen maintenance and colour rendering. Application areas vary from offices and industry to schools and retail environments.

### Benefits

- Up to 10 % energy saving with simply changing the lamp
- The same quality of light as compared with MASTER TL5 HO lamps
- All benefits of regular TL5 lamps

### Features

- High lamp efficacies up to 109 lm/W
- Up to 10% power reduction in comparison with standard MASTER TL5 HO lamps

### Application


- Offers very economic solutions for high-ceiling lighting in shops, industry and department stores
- The high luminous flux gives optimal results in aesthetic pendants and furniture-mounted luminaires in offices, workshops, restaurants and reception areas

# MASTER TL5 High Output Eco

## Versions



## Dimensional drawing



| Product                                | D (max) | A (max)   | B (max)   | B (min)   | C (max)   |
|--|---------|-----------|-----------|-----------|-----------|
| MASTER TL5 HO Eco<br>50=54W/840 1SL/40 | 17 mm   | 1149.0 mm | 1156.1 mm | 1153.7 mm | 1163.2 mm |

