



Product Description

MASTER TL-D 90 Graphica

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Excellent colour rendering. Making representation of colours extremely realistic
- Lamp developed to answer the needs of the demanding graphical industry (consistent with the strict standards for the graphical industry defined in EN-12464)
- Very accurate colour point
- Attractive packaging configuration
- Direct retrofit for all Standard and Super 80 TL-D lamps operating on conventional or electronic gear
- Choice of daylight and cool daylight colours

Features

- High-quality fluorescent coating
- Available in two colour designations

Application


- Used in applications where excellent colour rendering is crucial, such as the graphical industry, printing industry, photo shops, hospitals, etc.

MASTER TL-D 90 Graphica

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
Graphica 36W/965					
SLV/10					

