



Product Description

MASTER TL-D 90 De Luxe

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Very good color rendering, making products appear more attractive and colors appear rich, deep and enhanced as they do in daylight
- Very good colour rendering. Making colours appear rich, deep and enhanced as they do in daylight, making products appear more attractive
- Enabling customer to switch to improved color rendering properties with (almost) no decrease of light level
- 25% More light than competition
- Enabling customers (in certain segments) to respect the new European standard for lighting of indoor workplaces (CEN 12464-1), without investing in new luminaires
- Enabling customer to switch to 900-colours with (almost) no decrease of light level
- Enabling customers (in certain segments) to respect the new European standard for lighting of indoor workplaces (CEN 12464-1), without investing in new luminaires
- Attractive packaging configuration
- Direct retrofit for all Standard and Super 80 TL-D lamps operating on conventional or HF gear
- Possible to create atmospheres from warm white to cool daylight

Features

- High-quality fluorescent coating for improved color rendering
- High-quality fluorescent coating
- Use of three-band phosphors for high efficacy
- Available in various colour designations
- Retrofit in current luminaires for standard TL-D lamps
- Available in various color designations

MASTER TL-D 90 De Luxe

Application

- Used in applications where good color rendering is crucial, such as shops (flower, fashion, department, etc.), hairdresser, museums, hospitals, etc.
- Used in applications where good colour rendering is crucial, such as shops (flower, fashion, department, etc.), hairdresser, museums, hospitals, etc

Warnings and Safety


- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

Versions



LPPR TL-D9HLM G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D 90 De Luxe 18W/965 SLV/10	28 mm	589.8 mm	596.9 mm	594.5 mm	604 mm

MASTER TL-D 90 De Luxe

