



# For reliable unveiling of secrets

## TL-D Blacklight Blue

TL-D/08 Blacklight Blue lamps are low-pressure mercury-vapor fluorescent lamps. They have an inner envelope coated with a fluorescent powder that emits long-wave UV radiation to excite luminescence.

### 优点

- Quick detection of UV-reflecting materials
- Creates special lighting atmospheres and effects

### 特点

- Straight outer envelope

### 应用

- Detection and analysis in the textile and chemical industries
- Banking and forensic science
- Special effects in night clubs, discos and theatres, and sign lighting

### 安全提示

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.

## TL-D Blacklight Blue

### Versions

