



Red, Green and Blue fluorescent lighting

TL-D Colored

This TL-D lamp (tube diameter 26 mm) helps to create special effects and atmospheres or attract attention by using red, green, blue and yellow light. Apart from using the specific colors, it is also possible to mix the colors to create white light. This lamp offers a high light output, thanks to the use of basic powders. Application areas include shops and showrooms, bars and restaurants, demonstration areas, sign lighting and entertainment stores.

优点

- Choice of attractive colors

特点

- The fluorescent powders of Red and Yellow lamps are mixed with a pigment to filter out unwanted wavelengths
- Can be used with conventional or electronic gear
- Depending on the control gear, dimming is possible

应用


- For color effects in stage lighting, shop-window lighting, festive lighting, bars, dance halls etc.

TL-D Colored

Versions



二维绘图



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-D Colored 58W Yellow 1SL/25	28.0 mm	1500.0 mm	1507.1 mm	1504.7 mm	1514.2 mm
TL-D Colored 36W Yellow 1SL/25	28.0 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm
TL-D Colored 18W Yellow 1SL/25	28.0 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

应用	
能效标签 (EEL)	B
汞 (Hg) 含量 (标称)	13.0 mg
控制调光	
可调光	Yes
基本信息	
底盖	G13
10% 故障条件下的使用寿命 (标称)	12000 h
50% 故障条件下的使用寿命 (标称)	15000 h
照明科技	
颜色代码	160
颜色名称	黄色
机械和壳体	
灯泡外形	T8
温度	
设计温度 (标称)	25 °C

应用		
Order Code	Full Product Name	能耗 kWh/1000 h
928048001605	TL-D Colored 18W Yellow 1SL/25	23 kWh
928048501605	TL-D Colored 36W Yellow 1SL/25	44 kWh
928049001605	TL-D Colored 58W Yellow 1SL/25	70 kWh

运营和电气

TL-D Colored

Order Code	Full Product Name	功率(额定) (标称)		
		灯具电流(标称)	电压(标称)	称)
928048001605	TL-D Colored 18W Yellow 1SL/25	0.360 A	59 V	18.0 W
928048501605	TL-D Colored 36W Yellow 1SL/25	0.440 A	103 V	36.0 W

Order Code	Full Product Name	功率(额定) (标称)		
		灯具电流(标称)	电压(标称)	称)
928049001605	TL-D Colored 58W Yellow 1SL/25	0.670 A	111 V	58.5 W

照明科技

Order Code	Full Product Name	LLMF 2000	光通量 (额定)	
		小时额定	光通量(标称)	(标称)
928048001605	TL-D Colored 18W Yellow 1SL/25	85 %	700 lm	700 lm
928048501605	TL-D Colored 36W Yellow 1SL/25	85 %	1580 lm	1580 lm

Order Code	Full Product Name	LLMF 2000	光通量 (额定)	
		小时额定	光通量(标称)	(标称)
928049001605	TL-D Colored 58W Yellow 1SL/25	80 %	2250 lm	2250 lm

