



Product Description

MASTER TL-D Secura

Low-pressure mercury discharge lamps with a tubular 26 mm envelope

Benefits

- Special protective coating in the lamp-, prevents products from contamination in case of accidental lamp breakage
- Easy identification in audit situations by blue ring at one end
- Special fluorescent coating gives good colour rendering
- Relatively high efficacy, both initially and during lamp lifetime, with high lumen maintenance
- Protects products from discolouring and loss of taste by 90% lower UV emission
- Compliant with HACCP regulations and supports HACCP certification

Features

- Protective coating around the entire lamp
- Blue ring around one end
- Direct retrofit for all Standard and Super /80 TL-D lamps operating on conventional or HF gear
- Highly efficient 3-band fluorescent coating in combination with New Generation pre-coating technology
- Available in various colour designations
- Low mercury dose
- Recyclable at end-of-life, including the protective lamp coating
- End-cap has green bottom plate to identify lamp as recyclable

Application

- For use where contamination resulting from lamp breakage must be prevented, e.g. in food preparation, health care, pharmaceuticals, cleanrooms etc.
- Suitable for use in environments with increased risk of breakage, e.g. sports halls
- Suitable for use in environments where UV emission should be reduced (museums, libraries, archives, food industry, fashion shops, etc.)

MASTER TL-D Secura

Warnings and Safety


- Not suitable for closed luminaires (as indicated by two blue rings)
- Recommended use in combination with self-stopping lamp control system
- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.
- It's strongly recommended to replace Secura lamps before or at the moment the specified lamp life (50% failures @ 3 hrs switching cycle) is reached.

Versions



TL-D8SE G13 RT

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Secura 58W/840 SLV/25	28 mm	1,500.0 mm	1,507.1 mm	1,504.7 mm	1,514.2 mm

