



Φωτισμός φθορισμού για ψυχρά περιβάλλοντα

MASTER TL-D Xtreme Polar

Ο λαμπτήρας MASTER TL-D Xtreme Polar προσφέρει τη μέγιστη φωτεινή ροή σε συνθήκες χαμηλής θερμοκρασίας λόγω της μόνωσης που δημιουργείται τοποθετώντας ένα λαμπτήρα TL-D (T8) εντός ενός σωλήνα T10 ή T12. Μπορεί να χρησιμοποιείται σε υφιστάμενα φωτιστικά για λαμπτήρες T8 και είναι κατάλληλος για όλες τις εφαρμογές με κύκλους λειτουργίας μεγάλης διάρκειας σε ψυχρά περιβάλλοντα.

Οφέλη

- High lighting level in low-ambient-temperature applications compared with other fluorescent tubes
- Sharp reduction in maintenance costs due to high reliability and long lifetime
- Supports end-user sustainability programs (low mercury level and low waste due to long lifetime)

Χαρακτηριστικά

- Improved light output in low ambient temperatures
- Peak luminous flux for 58 W is reached at an ambient temperature of -5 °C around the lamp
- The same reliable, long-lifetime performance as regular MASTER TL-D Xtreme

Εφαρμογή


- Indoor: cold stores and other refrigerated areas
- Outdoor: petrol stations, car parks, shipping docks, petrochemical plants, sign lighting, tunnels

MASTER TL-D Xtreme Polar

Versions



Σχεδιάγραμμα διαστάσεων



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtreme Polar 18W/840 SLV/10	40.5 mm	589.8 mm	596.9 mm	594.5 mm	604.0 mm

