



Long life fluorescent lighting

MASTER TL-D Xtra

This TL-D Xtra lamp offers a longer lifetime and guarantees fewer early failures. This results in low maintenance costs and saves on expensive spot replacement. It is therefore suitable for places where lamp replacement is expensive due to high ceilings or disturbance of operations. This lamp can be operated on existing gear or dedicated HF Xtreme gear.

Benefits

- Longer lifetime results in lower maintenance costs, less waste and disposal costs at end-of-life
- Less hassle due to fewer early failures
- Facilitating the change from spot to group replacement

Features

- Extra long lifetime; longest lifetime is achieved with specially designed Philips HF Xtreme gear
- End-cap has an x-shaped green bottom plate to distinguish the lamp from other fluorescent lamps
- Low mercury dose (3mg)

Application


- Suitable for use in applications where maintenance costs are high (high ceilings, difficult to reach): department stores, supermarkets, warehouses, production halls and public areas like car parks and railway stations

MASTER TL-D Xtra

Versions



Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MASTER TL-D Xtra 36W/830 SLV/25	28 mm	1199.4 mm	1206.5 mm	1204.1 mm	1213.6 mm

