



Product Description

TL Mini Standard Colours

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

Benefits

- Creates atmospheres from warm white to cool daylight

Features

- 16 mm diameter tubes with moderate colour rendering

Application


- Ideal for applications where space is limited and colour rendering is not important
- Orientation lighting
- Emergency lighting

Versions



TL Mini Standard Colours

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL Mini 8W/33-640 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

