



# Product Description

## MASTER TL Mini Super 80

Low-pressure mercury discharge lamps with a tubular 16 mm envelope

### Benefits

- Good colour rendering
- High efficacy, both initially and during lamp lifetime, with high lumen maintenance compared with standard lamps
- Small lamp dimensions enables system miniaturisation

### Features

- 16 mm diameter tubes with highly efficient 3-band fluorescent coating

### Application

- Ideal for applications where space is limited but requiring better colour rendering and efficacy than standard colours:
- hall and staircase lighting in apartment buildings
- built into furniture, mirror and cupboard lighting
- emergency lighting

### Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


# MASTER TL Mini Super 80

## Versions



LPPR TL8MINI

## Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
MST TL Mini 8W/840 FAM/10X25BOX	16 mm	288.3 mm	295.4 mm	293.0 mm	302.5 mm

