



Product Description

TL-M Rapid Start Standard Colours

Low-pressure mercury discharge lamps with a tubular 38 mm envelope

Benefits

- Well defined ignition for fast, easy ignition at low temperatures

Features

- RS (Rapid Start) lamps with an external silicon coating
- External ignition strip connected via a high-ohmic resistor to one of the electrodes
- Available in standard colours and varying colour designations

Application

- Standard colours are mostly used in applications where colour rendering is not an important factor

Warnings and Safety

- A lamp breaking is extremely unlikely to have any impact on your health. If a lamp breaks, ventilate the room for 30 minutes and remove the parts, preferably with gloves. Put them in a sealed plastic bag and take it to your local waste facilities for recycling. Do not use a vacuum cleaner.


TL-M Rapid Start Standard Colours

Versions



LPPR TL-M-RS G13

Dimensional drawing



Product	D (max)	A (max)	B (max)	B (min)	C (max)
TL-M RS 40W/33-640 SLV/25	40.5 mm	1,199.4 mm	1,206.5 mm	1,204.1 mm	1,213.6 mm

