



TMS011

TMS011

An indoor luminaire in single and twin fluorescent lamp versions for general lighting. The range is available with TLD 18W, 36W or 58W lamps for surface-mounted applications. The luminaires can be suspended or direct ceiling mounted. A range of attractive attachments is also available.

Features

- A high quality luminaire with enhanced safety
- Easy installation and maintenance
- Philips ballast is pre-wired inside the luminaire
- The starter is also provided

Application

- Discount stores
- Hyper- and supermarkets
- DIY stores
- Convenient stores
- Coves
- Home lighting
- General industries

TMS011

Versions



General information

Protection class IEC	Safety class I
Lamp family code	TL-D

Approval and application

Order Code	Full Product Name	Ingress protection code
911400856480	TMS011 1xTL-D36W HF 220V/50Hz	IP20
911400856580	TMS011 1xTL-D18W HF 220V/50Hz	IP20
911400856680	TMS011 2xTL-D18W HF 220V/50Hz	IP20
911400857180	TMS011 1xTL-D36W	IP20
911400857280	TMS011 2xTL-D36W I	IP20
911400857480	TMS011 1xTL-D36W IC	-
911400857580	TMS011 2xTL-D36W IC	-
911400857680	TMS011 1xTL-D18W	IP20
911400857780	TMS011 2xTL-D18W I	IP20
911400857880	TMS011 1xTL-D18W IC	-
911400857980	TMS011 2xTL-D18W IC	-
911400858080	TMS011 1xTL-D36W I R	IP20
911400858180	TMS011 1xTL-D36W IC R	-
911400858280	TMS011 2xTL-D36W I R	IP20
911400858380	TMS011 2xTL-D36W IC R	-
911400858580	TMS011 1xTL-D18W IC R	-
911400858780	TMS011 2xTL-D18W IC R	-
911400859180	TMS011 1xTL-D58W I	IP20
911400859280	TMS011 1xTL-D58W IC	-
911400859380	TMS011 2xTL-D58W I	IP20
911400859480	TMS011 2xTL-D58W IC	-

Order Code	Full Product Name	Ingress protection code
911400859580	TMS011 1xTL-D58W IC R	-
911400859680	TMS011 2xTL-D58W I R	IP20
911400859780	TMS011 1xTL-D58W I R	IP20
911400859880	TMS011 2xTL-D58W IC R	-
911400860180	TMS011 1xTL-D18W I P	IP20
911400860380	TMS011 1xTL-D18W IC P	-
911400860480	TMS011 1xTL-D36W I P	IP20
911400860580	TMS011 1xTL-D36W IC P	-
911400860780	TMS011 1xTL-D58W I 220V-50Hz P	IP20
911400860880	TMS011 1xTL-D58W IC P	-
911400861280	TMS011 2xTL-D36W HF 220V/50Hz	IP20
911400864780	TMS011 1xTL-D36W HFS GKH 220V 50Hz	IP20
911400864880	TMS011 1xTL-D36W HFS GMP 220V 50Hz	IP20
911400864980	TMS011 1xTL-D18W HFS GMP 220V 50Hz	IP20
911400865080	TMS011 1xTL-D18W HFS GKH 220V 50Hz	IP20
911400865180	TMS011 1xTL-D36W HFS 220V 50Hz	IP20
911400865680	TMS011 2xTL-D18W HFS 220V 50Hz	IP20
911400865780	TMS011 2xTL-D36W HFS 220V 50Hz	IP20
911400865880	TMS011 1xTL-D18W HFS 220V 50Hz	IP20
911400865980	TMS011 2xTL-D36W HFS GKH 220V 50Hz	IP20

Operating and electrical

Order Code	Full Product Name	Input Voltage
911400856480	TMS011 1xTL-D36W HF 220V/50Hz	220 V
911400856580	TMS011 1xTL-D18W HF 220V/50Hz	220 V
911400856680	TMS011 2xTL-D18W HF 220V/50Hz	220 V
911400857180	TMS011 1xTL-D36W	220 V
911400857280	TMS011 2xTL-D36W I	-
911400857480	TMS011 1xTL-D36W IC	-

Order Code	Full Product Name	Input Voltage
911400857580	TMS011 2xTL-D36W IC	-
911400857680	TMS011 1xTL-D18W	220 V
911400857780	TMS011 2xTL-D18W I	-
911400857880	TMS011 1xTL-D18W IC	-
911400857980	TMS011 2xTL-D18W IC	-
911400858080	TMS011 1xTL-D36W I R	-

TMS011


Order Code	Full Product Name	Input Voltage	Order Code	Full Product Name	Input Voltage
911400858180	TMS011 1xTL-D36W IC R	-	911400860480	TMS011 1xTL-D36W I P	-
911400858280	TMS011 2xTL-D36W I R	-	911400860580	TMS011 1xTL-D36W IC P	-
911400858380	TMS011 2xTL-D36W IC R	-	911400860780	TMS011 1xTL-D58W I 220V-50Hz P	220 V
911400858580	TMS011 1xTL-D18W IC R	-	911400860880	TMS011 1xTL-D58W IC P	-
911400858780	TMS011 2xTL-D18W IC R	-	911400861280	TMS011 2xTL-D36W HF 220V/50Hz	220 V
911400859180	TMS011 1xTL-D58W I	-	911400864780	TMS011 1xTL-D36W HFS GKH 220V 50Hz	-
911400859280	TMS011 1xTL-D58W IC	-	911400864880	TMS011 1xTL-D36W HFS GMP 220V 50Hz	-
911400859380	TMS011 2xTL-D58W I	-	911400864980	TMS011 1xTL-D18W HFS GMP 220V 50Hz	-
911400859480	TMS011 2xTL-D58W IC	-	911400865080	TMS011 1xTL-D18W HFS GKH 220V 50Hz	-
911400859580	TMS011 1xTL-D58W IC R	-	911400865180	TMS011 1xTL-D36W HFS 220V 50Hz	-
911400859680	TMS011 2xTL-D58W I R	-	911400865680	TMS011 2xTL-D18W HFS 220V 50Hz	-
911400859780	TMS011 1xTL-D58W I R	-	911400865780	TMS011 2xTL-D36W HFS 220V 50Hz	-
911400859880	TMS011 2xTL-D58W IC R	-	911400865880	TMS011 1xTL-D18W HFS 220V 50Hz	-
911400860180	TMS011 1xTL-D18W I P	-	911400865980	TMS011 2xTL-D36W HFS GKH 220V 50Hz	-
911400860380	TMS011 1xTL-D18W IC P	-			

General information

Order Code	Full Product Name	Compensation circuit	Optical cover/lens				
			type	Gear	Lamp power	Number of light sources	Optic type
911400856480	TMS011 1xTL-D36W HF 220V/50Hz	-	-	EBE	36 W	1 pc	-
911400856580	TMS011 1xTL-D18W HF 220V/50Hz	-	-	EBE	18 W	1 pc	-
911400856680	TMS011 2xTL-D18W HF 220V/50Hz	-	-	EBE	18 W	2 pcs	-
911400857180	TMS011 1xTL-D36W	-	-	-	36 W	1 pc	-
911400857280	TMS011 2xTL-D36W I	Inductive	-	CONV	36 W	2 pcs	-
911400857480	TMS011 1xTL-D36W IC	Inductive parallel compensated	-	CONV	36 W	1 pc	-
911400857580	TMS011 2xTL-D36W IC	Inductive parallel compensated	-	CONV	36 W	2 pcs	-
911400857680	TMS011 1xTL-D18W	-	-	-	18 W	1 pc	-
911400857780	TMS011 2xTL-D18W I	Inductive	-	CONV	18 W	2 pcs	-
911400857880	TMS011 1xTL-D18W IC	Inductive parallel compensated	-	CONV	18 W	1 pc	-
911400857980	TMS011 2xTL-D18W IC	Inductive parallel compensated	-	CONV	18 W	2 pcs	-
911400858080	TMS011 1xTL-D36W I R	Inductive	-	CONV	36 W	1 pc	Reflector
911400858180	TMS011 1xTL-D36W IC R	Inductive parallel compensated	-	CONV	36 W	1 pc	Reflector
911400858280	TMS011 2xTL-D36W I R	Inductive	-	CONV	36 W	2 pcs	Reflector
911400858380	TMS011 2xTL-D36W IC R	Inductive parallel compensated	-	CONV	36 W	2 pcs	Reflector
911400858580	TMS011 1xTL-D18W IC R	Inductive parallel compensated	-	CONV	18 W	1 pc	Reflector
911400858780	TMS011 2xTL-D18W IC R	Inductive parallel compensated	-	CONV	18 W	2 pcs	Reflector
911400859180	TMS011 1xTL-D58W I	Inductive	-	CONV	58 W	1 pc	-
911400859280	TMS011 1xTL-D58W IC	Inductive parallel compensated	-	CONV	58 W	1 pc	-
911400859380	TMS011 2xTL-D58W I	Inductive	-	CONV	58 W	2 pcs	-
911400859480	TMS011 2xTL-D58W IC	Inductive parallel compensated	-	CONV	58 W	2 pcs	-
911400859580	TMS011 1xTL-D58W IC R	Inductive parallel compensated	-	CONV	58 W	1 pc	Reflector
911400859680	TMS011 2xTL-D58W I R	Inductive	-	CONV	58 W	2 pcs	Reflector
911400859780	TMS011 1xTL-D58W I R	Inductive	-	CONV	58 W	1 pc	Reflector
911400859880	TMS011 2xTL-D58W IC R	Inductive parallel compensated	-	CONV	58 W	2 pcs	Reflector
911400860180	TMS011 1xTL-D18W I P	Inductive	Prismatic refractor	CONV	18 W	1 pc	Asymmetrical mirror
911400860380	TMS011 1xTL-D18W IC P	Inductive parallel compensated	Prismatic refractor	CONV	18 W	1 pc	Asymmetrical mirror
911400860480	TMS011 1xTL-D36W I P	Inductive	Prismatic refractor	CONV	36 W	1 pc	Asymmetrical mirror
911400860580	TMS011 1xTL-D36W IC P	Inductive parallel compensated	Prismatic refractor	CONV	36 W	1 pc	Asymmetrical mirror
911400860780	TMS011 1xTL-D58W I 220V-50Hz P	Inductive	Prismatic refractor	CONV	58 W	1 pc	Asymmetrical mirror
911400860880	TMS011 1xTL-D58W IC P	Inductive parallel compensated	Prismatic refractor	CONV	58 W	1 pc	Asymmetrical mirror
911400861280	TMS011 2xTL-D36W HF 220V/50Hz	-	-	EBE	36 W	2 pcs	-

Order Code	Full Product Name	Compensation circuit	Optical cover/lens		Lamp power	Number of light sources	Optic type
			type	Gear			
911400864780	TMS011 1xTL-D36W HFS GKH 220V 50Hz	-	-	EBS	36 W	1 pc	Reflector
911400864880	TMS011 1xTL-D36W HFS GMP 220V 50Hz	-	Prismatic refractor	EBS	36 W	1 pc	-
911400864980	TMS011 1xTL-D18W HFS GMP 220V 50Hz	-	Prismatic refractor	EBS	18 W	1 pc	-
911400865080	TMS011 1xTL-D18W HFS GKH 220V 50Hz	-	-	HFS	18 W	1 pc	Reflector
911400865180	TMS011 1xTL-D36W HFS 220V 50Hz	-	-	EBS	36 W	1 pc	-
911400865680	TMS011 2xTL-D18W HFS 220V 50Hz	-	-	EBS	18 W	2 pcs	-
911400865780	TMS011 2xTL-D36W HFS 220V 50Hz	-	-	EBS	36 W	2 pcs	-
911400865880	TMS011 1xTL-D18W HFS 220V 50Hz	-	-	EBS	18 W	1 pc	-
911400865980	TMS011 2xTL-D36W HFS GKH 220V 50Hz	-	-	EBS	36 W	2 pcs	Reflector

Polar Wide Diagrams



IFPS_TMS011 1xTL-D36W HFE-Polar Normal
(separate)

