



Lineco TMS022 – an economical choice

Lineco TMS022 UK

Lineco TMS022 is a functional and economical surface-mounted batten for 1 or 2 TL-D fluorescent lamps. It offers a choice of two optics, for symmetrical and asymmetrical lighting. Installation is quick and tool-less and can be carried out single-handedly. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps). A wide range of snap-on attachments is available.

Benefits

- An economical choice, with a functional surface-mounted batten for 1 or 2 TL-D fluorescent lamps
- Choice of optics for symmetrical or asymmetrical light distribution
- Quick, tool-less installation can be carried out single-handedly

Features

- Choice of one or two TL-D fluorescent lamps
- Choice of symmetrical or asymmetrical optics
- Quick, tool-less installation
- Repositionable contact block
- Wide range of snap-on attachments

Application

- Retail
- Industry

Specifications

Type	TMS022
Light source	Fluorescent: - 1 x or 2 x MASTER TL-D / G13 / 18, 36, 58, 70 W

Lamp included	Yes (light color 35 in IC or 840 in HF version)
---------------	---


Gear	Electro magnetic (low loss), 230 V or 240 V / 50 Hz:
	- Parallel compensated (IC)
	Electronic, 220 - 240 V / 50 - 60 Hz:
	- High Frequency Performer (HFP)
	- High Frequency Regulator (HFR)
Connection	Screw-in connector (SI)
Option	Emergency lighting: 3 hours (EL3)
Material	Sheet steel, white

Installation	Individual; surface or BESA screw fixing with cable entry via central and BESA entry points or via endcap knockouts
	Possibility to reposition the contact block (2-lamp version)
Accessory	White one-piece trough and angled reflectors (for 1 and 2-lamp versions), wireguards, aluminum rack reflector, prismatic and opal diffusers (1 and 2-lamps) supplied with internal fixing brackets to batten
Main applications	Retail, industry


Versions



Dimensional drawing




Product
TMS022 2xTL-D58W/840 HFSUK
TMS022 2xTL-D58W HFSUK



Product
GMS022 1/2 58 R-A-UK

Dimensional drawing



Product
TMS022 1xTL-D58W HFSUK

Accessories



TMS 022 with GMS 022 R-A white asymmetric reflector.

Ordercode 11788199

Approval and Application	
Mech. impact protection code	IK02
Ingress protection code	IP20
Operating and Electrical	
Input Voltage	230 to 240 V
General Information	
CE mark	CE mark
Protection class IEC	Safety class I
Compensation circuit	-
Country version	UK
Emergency lighting	No
ENEC mark	ENEC mark
Flammability mark	F
Gear	HF Standard
Glow-wire test	Temperature 650 °C, duration 5 s
Lamp family code	TL-D
Lamp power	58 W
Optic type	No
Product Family Code	TMS022

Order Code	Full Product Name	Kombipack	Number of light sources
13566300	TMS022 1xTL-D58W HFSUK	-	1
13571700	TMS022 2xTL-D58W HFSUK	-	2
13572400	TMS022 2xTL-D58W/840 HFSUK	Lamp(s) included	2

