



TMS028 – functional and flexible

TMS028

TMS028 is a basic batten for 1 or 2 TL-D fluorescent lamps and includes optics for general lighting. It can be suspended or surface-mounted. A lamellae louver, end caps and inline couplers are available as accessories. The repositionable contact block enables flexible connection (with cable entry centrally or via the end caps).

Benefits

- Functional and flexible basic batten for 1 or 2 TL-D fluorescent lamps, including optics for general lighting
- Can be suspended or surface-mounted
- Glare-reducing lamellae louver, end-caps and inline couplers available as accessories

Features

- For 1 or 2 TL-D fluorescent lamps
- Optics for general lighting
- Lamellae louver, end caps and inline couplers available as accessories
- Repositionable contact block

Application

- Retail
- Industry

Specifications

Type	TMS028
Light source	Fluorescent: - 1 x or 2 x MASTER TL-D / G13 / 36, 58 W
Lamp included	No


Gear	Electro magnetic (low loss), 230 or 240 V / 50 Hz:
	- Inductive (I)
	- Inductive, parallel compensated (IC)
	Electronic, 220 - 240 V / 50 - 60 Hz:
	- High Frequency Performer (HFP) - Electronic Included (EI)

TMS028

Optic	High-gloss mirror
Connection	Push-in connector
Option	Feed-through wiring: 1-phase (TW1)
Material	Housing: lacquered steel, white Optic: aluminum or lacquered steel, white
Installation	Individual; screw fixing or suspension by chains or threaded rods Possibility to reposition the contact block (2 lamps version)


Accessory	Lamellea louver, coupling piece, end caps, spacers for suspension
Remark	Optional pre-equipped for mounting on Telemécanique power supply systems
Main applications	Retail, industry

Dimensional drawing




Product
TMS028 1xTL-D36W HFS
TMS028 2xTL-D58W HFS
TMS028 2xTL-D36W HFS

Accessories



TMS028 with GMS028 L white
lamellae louver

Ordercode 910400627918,
910400628018



End plates set/white

Ordercode 20827599

