



TMS028

TMS028

Basic industrial luminaire for TL-D fluorescent lamp(s) for general lighting. For surface and suspended mounting. A repositionable contact block makes a flexible connection possible and keeps the installation costs low. As option pre-equipped with possibility for mounting on Telemécanique kle/kla power supply systems. Reflector supplied with the luminaire. Attachment (lamellea louvre) available as accessory.

Benefits

- Functional and flexible basic batten for 1 or 2 TL-D fluorescent lamps, including optics for general lighting
- Can be suspended or surface-mounted
- Glare-reducing lamellae louver, end-caps and inline couplers available as accessories

Features

- For 1 or 2 TL-D fluorescent lamps
- Optics for general lighting
- Lamellae louver, end caps and inline couplers available as accessories
- Repositionable contact block

Application

- Retail
- Industry

Specifications

| | |
|---------------|---|
| Type | TMS028 |
| Light source | Fluorescent: - 1 x or 2 x MASTER TL-D / G13 / 36, 58 W |
| Lamp included | No |


| | |
|------------|--|
| Gear | Electro magnetic (low loss), 230 or 240 V / 50 Hz: |
| | - Inductive (I) |
| | - Inductive, parallel compensated (IC) |
| | Electronic, 220 - 240 V / 50 - 60 Hz: |
| | - High Frequency Performer (HFP) |
| | - Electronic Included (EI) |
| Optic | High-gloss mirror |
| Connection | Push-in connector |

TMS028

| | |
|--------------|---|
| Option | Feed-through wiring: 1-phase (TW1) |
| Material | Housing: lacquered steel, white |
| | Optic: aluminum or lacquered steel, white |
| Installation | Individual; screw fixing or suspension by chains or threaded rods |
| | Possibility to reposition the contact block (2 lamps version) |


| | |
|-------------------|--|
| Accessory | Lamellea louver, coupling piece, end caps, spacers for suspension |
| Remark | Optional pre-equipped for mounting on Telemécanique power supply systems |
| Main applications | Retail, industry |

Dimensional drawing




| Product |
|----------------------|
| TMS028 1xTL-D58W HF |
| TMS028 2xTL-D36W HF |
| TMS028 1xTL-D36W HF |
| TMS028 2xTL-D58W HFS |
| TMS028 2xTL-D36W HFS |
| TMS028 1xTL-D36W HFS |

Accessories



TMS028 with GMS028 L white
lamellae louver

Ordercode 910400627918,
910400628018



End plates set/white

Ordercode 20827599

