



TMS122

Pentura TMS122 C

A high-quality dedicated batten luminaire for single and twin TL5 fluorescent lamps. The luminaire is integrated with a slim HF electronic ballast for compactness. This batten is suitable for both direct and indirect lighting applications.

Features

- The batten is built on a base plate, to be easily fixed to the ceiling
- Contains all the electrical and mechanical components, and a white pre-lacquered housing, fixed to the base-plate via 2 screws with no mechanical functionality
- The batten includes two plastic end caps and is integrated with HK electronic ballast

Application


- Shops
- Offices
- Industries
- Coves

Versions



Pentura TMS122 C

Dimensional drawing



Product	A	B
TMS122 1xTL5-14W HFP	485 mm	573 mm
TMS122 1xTL5-28W HFS	1085 mm	1173 mm
TMS122 1xTL5-28W HFP	1085 mm	1173 mm
TMS122 1xTL5-28W EBC	1085 mm	1173 mm

Approval and Application

Ingress protection code	IP20
-------------------------	------

General Information

Protection class IEC	Safety class I (I)
Lamp family code	TL5
Number of light sources	1

General Information

Order Code	Full Product Name	Gear	Lamp power
910403358180	TMS122 1xTL5-28W EBC	EBE	28 W
911400863580	TMS122 1xTL5-28W HFS	EBS	28 W

Order Code	Full Product Name	Gear	Lamp power
911400863680	TMS122 1xTL5-14W HFP	EBP	14 W
911400863780	TMS122 1xTL5-28W HFP	EBP	28 W

Mechanical and Housing

Order Code	Full Product Name	Colour
910403358180	TMS122 1xTL5-28W EBC	-
911400863580	TMS122 1xTL5-28W HFS	-

Order Code	Full Product Name	Colour
911400863680	TMS122 1xTL5-14W HFP	-
911400863780	TMS122 1xTL5-28W HFP	-

