



TMS122

Pentura TMS122 C

A high-quality dedicated batten luminaire for single and twin TL5 fluorescent lamps. The luminaire is integrated with a slim HF electronic ballast for compactness. This batten is suitable for both direct and indirect lighting applications.

Features

- The batten is built on a base plate, to be easily fixed to the ceiling
- Contains all the electrical and mechanical components, and a white pre-lacquered housing, fixed to the base-plate via 2 screws with no mechanical functionality
- The batten includes two plastic end caps and is integrated with HK electronic ballast

Application

- Shops
- Offices
- Industries
- Coves

Pentura TMS122 C

Dimensional drawing

TMS122 C

Product	A	B
TMS122 1xTL5-14W HFP	485 mm	573 mm
TMS122 2xTL5-28W HFP	1085 mm	1173 mm
TMS122 1xTL5-28W HFS ALU	1085 mm	1173 mm
TMS122 2xTL5-14W HFP ALU	485 mm	573 mm
TMS122 1xTL5-28W HFP ALU	1085 mm	1173 mm
TMS122 2xTL5-28W EBC	1085 mm	1173 mm
TMS122 2xTL5-28W HFP ALU	1085 mm	1173 mm
TMS122 1xTL5-28W HFS	1085 mm	1173 mm
TMS122 1xTL5-14W EBC	485 mm	573 mm
TMS122 2xTL5-14W EBC	485 mm	573 mm
TMS122 1xTL5-14W HFS ALU	485 mm	573 mm
TMS122 1xTL5-14W HFP ALU	485 mm	573 mm
TMS122 2xTL5-14W HFS	485 mm	573 mm
TMS122 1xTL5-28W HFA		
TMS122 2xTL5-28W HFS	1085 mm	1173 mm
TMS122 1xTL5-28W HFP	1085 mm	1173 mm
TMS122 1xTL5-14W HFS	485 mm	573 mm
TMS122 2xTL5-28W HFS ALU	1085 mm	1173 mm
TMS122 1xTL5-28W EBC	1085 mm	1173 mm
TMS122 2xTL5-14W HFP	485 mm	573 mm
TMS122 2xTL5-14W HFS ALU	485 mm	573 mm

