



# EcoBATTEN – An economical choice

## EcoBATTEN

EcoBATTEN is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25, 28, 50 or 54 W TL5 fluorescent tube lamps and can be used at heights of between 2.5 and 12 m. Available in five versions with high performance.

### Benefits

- An economical choice for functional lighting with a batten surface fitting for two TL5 lamps
- Easy to install
- Wide variety of optical systems
- High performance

### Features

- Range of luminaires with five reflector options
- Aluminum reflector with metallic finish or painted white
- Suspended or surface-mounted luminaire
- Option with diffuser and reflector painted white
- Versions for direct and indirect lighting

### Application

- Industrial buildings
- Warehouses
- Schools
- Supermarkets
- Workshops
- Gas Stations
- Storage areas
- Garages

Specifications


Type	TMS940 / 941 / 942 / 943 / 944
Light source	2 x 25 W / 2 x 28 W / 2 x 50 W / 2 x 54 W / 2 x 73 W TL5
Mains voltage	Electronic 220 V / 50-60 Hz: (EB)
	Electronic Touch&Dim DALI (HFD)
Optical cover	Polycarbonate diffuser (TMS940)
	Materials and finishing
	White steel-plate fixture
	White steel-plate reflector
	Aluminum reflector

Installation	Suspended by means of rods mounted on slabs, ceilings, and tracks
--------------	---

Versions



Product details



## General Information

Lamp family code	TL5
Number of light sources	2 pcs

## General Information

Order Code	Full Product Name	Optical cover/ lens type	Gear	Lamp power	Optic type
919106027678	TMS943 2xTL5-28W/840 EB R- H	-	EB	28 W	Reflector high reflectance
919106027712	TMS943 2xTL5-25W/840 EB R- H	-	EB	25 W	Reflector high reflectance
919106029361	TMS943 2xTL5-54W/840 EB R- H	-	EB	54 W	Reflector high reflectance
919106031481	TMS943 2xTL5-50W/840 EB R- H	-	EB	50 W	Reflector high reflectance
919106031489	TMS943 2xTL5-50W/840 HFD C-H	-	HFD	50 W	High-gloss high reflectance
919106032431	TMS943 2xTL5-73W/840 EB R- H	-	EB	73 W	Reflector high reflectance
919106027882	TMS942 2xTL5-25W/840 EB WR	-	EB	25 W	White reflector without louver
919106027891	TMS942 2xTL5-28W/840 EB WR	-	EB	28 W	White reflector without louver
919106029321	TMS942 2xTL5-54W/840 EB WR	-	EB	54 W	White reflector without louver
919106031471	TMS942 2xTL5-50W/840 EB WR	-	EB	50 W	White reflector without louver
919106027922	TMS941 2xTL5-25W/840 EB WR-H	-	EB	25 W	Wide beam high reflectance
919106027931	TMS941 2xTL5-28W/840 EB WR-H	-	EB	28 W	Wide beam high reflectance
919106029308	TMS941 2xTL5-54W/840 EB WR-H	-	EB	54 W	Wide beam high reflectance
919106031461	TMS941 2xTL5-50W/840 EB WR-H	-	EB	50 W	Wide beam high reflectance
919106029382	TMS940 2xTL5-25W/840 EB WR PC	Polycarbonate bowl/cover	EB	25 W	White reflector without louver
919106029391	TMS940 2xTL5-28W/840 EB WR PC	Polycarbonate bowl/cover	EB	28 W	White reflector without louver
919106029401	TMS940 2xTL5-54W/840 EB WR PC	Polycarbonate bowl/cover	EB	54 W	White reflector without louver
919106031451	TMS940 2xTL5-50W/840 EB WR PC	Polycarbonate bowl/cover	EB	50 W	White reflector without louver
919106029442	TMS944 2xTL5-25W/840 EB D/I WR	-	EB	25 W	White reflector without louver
919106029451	TMS944 2xTL5-28W/840 EB D/I WR	-	EB	28 W	White reflector without louver
919106029461	TMS944 2xTL5-54W/840 EB D/I WR	-	EB	54 W	White reflector without louver
919106031491	TMS944 2xTL5-50W/840 EB D/I WR	-	EB	50 W	White reflector without louver

