



High Quality Industrial Lighting

EcoBATTEN 2

EcoBATTEN 2 is a range of luminaires for suspension or surface-mounting in indoor applications, ideal for industrial environments. It was developed especially for use with two 25 W or 50 W TL5 Eco fluorescent tube lamps. Available in 4 body versions and with dimmer-controlled drivers, it allows complete integration with building control systems.

Benefits

- High-performance optic with distribution specially designed for TL-5 ECO lamps
- Lighting available in neutral white with high color rendering index
- Luminaire in 4 different versions for perfect alignment with the project's cost and performance goals
- Optional DALI dimming control allows for complete integration with the most advanced building control systems

Features

- White Steel Plate Body
- Version with Shiny Aluminum Reflector
- Version with Transparent Acrylic Diffuser
- Electronic Driver (Optional DALI Dimming Control)
- Suspended or Surface-mounted Installation

EcoBATTEN 2

Application

- Ideal for lighting areas such as:
- Industrial buildings
- Warehouses
- Schools
- Supermarkets
- Workshops
- Storage areas
- Garages

Specifications

Type	Conventional Batten
Light source	2x25W / 2x50W / TL-5
Mains Voltage	Electronic Fixed 220 V - 60/50 Hz: (EB)
Materials and finishing	Phosphated steel body in white. White Steel Plate Optic (TMS950), Aluminum Reflector (TMS951/ TMS952) and Aluminum Reflector with Acrylic Diffuser (TMS953)

Installation	Suspended or surface-mounted
Approbation Signs	N/A

Versions



General Information

Lamp family code	TL5
Number of light sources	2 pcs

Mechanical and Housing

Color	White
--------------	-------

General Information

Order Code	Full Product Name	Optical cover/lens type	Gear	Kombipack	Lamp power	Optic type
919106020611	TMS950 2XTL5-25W WR	-	-	-	25 W	White reflector without louver
919106020621	TMS950 2XTL5-25W/840 EB WR	-	EB	Lamp(s) included	25 W	White reflector without louver
919106020631	TMS950 2XTL5-50W/840 EB WR	-	EB	Lamp(s) included	50 W	White reflector without louver
919106020641	TMS951 2XTL5-25W R-H	-	-	-	25 W	Reflector high reflectance
919106020651	TMS951 2XTL5-25W/840 EB R-H	-	EB	Lamp(s) included	25 W	Reflector high reflectance
919106020661	TMS951 2XTL5-50W/840 EB R-H	-	EB	Lamp(s) included	50 W	Reflector high reflectance
919106020671	TMS952 2XTL5-25W R-H WH	-	-	-	25 W	Reflector high reflectance
919106020681	TMS952 2XTL5-25W/840 EB R-H WH	-	EB	Lamp(s) included	25 W	Reflector high reflectance

EcoBATTEN 2

Order Code	Full Product Name	Optical cover/lens type	Gear	Kombipack	Lamp power	Optic type
919106020691	TMS952 2XTL5-50W/840 EB R-H WH	-	EB	Lamp(s) included	50 W	Reflector high reflectance
919106020701	TMS953 2XTL5-25W R-H WH AC	Acrylic bowl/cover	-	-	25 W	Reflector high reflectance
919106020711	TMS953 2XTL5-25W/840 EB R-H WH AC	Acrylic bowl/cover	EB	Lamp(s) included	25 W	Reflector high reflectance
919106020721	TMS953 2XTL5-50W/840 EB R-H WH AC	Acrylic bowl/cover	EB	Lamp(s) included	50 W	Reflector high reflectance

