



Excellent light distribution with maximum energy efficiency

TPS020

The TPS020 luminaire has a high-reflectance, high-gloss aluminum reflector. This guarantees high performance, making this system the best lighting solution for retail applications. It also features excellent light distribution, elegance, and advanced technology. This surface-mounted luminaire consists of two TL5 lamps of 50 or 54 W and can be used to replace systems with luminaires for 110 W HO lamps. The high-performance electronic ballast ensures a longer lamp life and is internally mounted in the luminaire, preventing any risk of the wiring being disconnected accidentally during installation.

Benefits

- Easy to install
- Very high performance
- Great finish on entire luminaire

Features

- Steel-plate body (0.5 mm) in white color and high-purity aluminum reflector
- Surface mounted
- For two TL5 lamps of 54/50 W

Application

- Ideal for general lighting of supermarkets, hypermarkets, department stores, and home centers

TPS020

Specifications

Type	TPS020
Light source	MASTER TL5 54 W
	MASTER TL5 Eco 50 W
Mains voltage	220-240 V / 50-60 Hz

Materials and finishing	Phosphated steel-plate body (0.5 mm) in white color and high-purity aluminum reflector
Installation	Superimposed on slabs or profiles, suspended

Versions



General Information

Lamp family code	TL5
Number of light sources	2 pcs
Optic type	Reflector high reflectance

General Information

Order Code	Full Product Name	Gear	Lamp power
919106027821	TPS020 2XTL5-54W R-H 5	-	54 W
919106027829	TPS020 2XTL5-54W/840 EB R-H 5	EB	54 W

Order Code	Full Product Name	Gear	Lamp power
919106031501	TPS020 2XTL5-50W/840 EB R-H	EB	50 W

