



ProLux – saving without impact

ProLux TPS550 C

In industry, the bottom line is affected by a whole host of factors – worker productivity, running costs and maintenance, to name just a few. In today's economic environment, with margins under pressure, all businesses operating high-bay facilities are faced with the pressing need to save energy. Our ProLux high-bay solution is a direct replacement for current HID high-bay systems and enables significant energy savings. The combination of robust housing, high-reflectance material and specially designed reflector add up to a high-efficiency luminaire that can help drive profitability by improving energy efficiency.

Benefits

- Maximum energy saving
- Easy maintenance
- Flexibility in design and installation

Features

- Saves 45% energy compared with HID
- High-output lamps and optics
- Uniform light levels for visual comfort
- Choice of three beams
- Pipe/surface/suspended versions
- Responsive system – on/off with no run-up times
- Integrated system – all Philips components
- Easy to maintain

Application

- Warehouses and distribution centers
- Light industry and assembly halls


Specifications

ProLux TPS550 C

Type	TPS550
Light source	Fluorescent: - 2 x or 4 x MASTER TL5 HO / G5 / 54 W - 2 x or 4 x MASTER TL5 HE / G5 / 28 W - 6 x MASTER TL5 HO TOP / G5 / 49 W
Lamp included	No
Ballast	Electronic, High Frequency 220-240 V / 50-60 Hz: Performer (HFP) Regulator, 1-10 V (HFR) Electronic Performer (EB-P) (for HE lamp version)
Reflector	Mirror high-gloss/specular (C)
Optic	Reflector medium beam (R-MB) Reflector narrow beam (R-NB) Reflector wide beam (R-WB)


Optical cover	Polycarbonate cover, clear (to be ordered separately)
Material	Housing: steel, white End cap: ABS, grey Reflector: mirror aluminum
Installation	Individual; suspended mounting with suspension hook or pipe mounted Individual; surface screw mounting by means of a mounting plate (to be ordered separately) Operating temperature: $-20^{\circ}\text{C} < T$
Accessories	PC clear cover, surface mounting plate

Versions



TPS550 4xTL5

Product details



IPDP_TPS550c_0001-Detail photo



ProLux TPS550 C

Product details

