



The right fit for your high-output applications

Centium T8HO

Centium T8 High Output Solution for Cold Environments

Avantages

- For use in cold environments
- Maximizes lamp life
- Higher Light Output
- Used with multiple lamp

Fonctions

- -30° F starting capability
- Programmed Start
- 1.0 Ballast Factor
- 1 or 2 Lamp Operation"

Application


- Industrial, Cold Storage, Manufacturing

Centium T8HO

Versions



Schéma dimensionnel



Product	A1	A2	B1	C1
CENTIUM ICN2S86SC35M	9,5 in	8,9 in	1,7 in	1,18 in

